














A	1	2	3	4
	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness 0.75 to 1.25 1.25 to 2 2 to 3	length of cut-out 19.2 -0.1 19.4 -0.1 19.8 -0.1	width of cut-out 21.9 +0.1 21.9 +0.1 21.9 +0.1
B				
C	  			
D	<p>Marking</p> <p>  1802.  05 8(8)/250 ~ 5E4 12(4)/250 ~ 5/70A 250V ~ T100/55 </p> <p> 15A 125-250V AC 3/4HP 125V AC 1 1/2HP 250V AC R149 </p> <p>   </p> <p>Code of manufacture: place/year/month</p> <p>On box: Customer Part No. see variant table</p>			
E	<p>DPST</p> <p>suitable for appliances of class II</p> 			

-		-				519081		1802.1126-XX																																						
Figure		Type				Customer Part No.		Art.No.-PI																																						
<div><div><div>Shape and location</div><div></div></div><div><div>Angle ± 2 °</div><div></div></div><div><div>Edge tolerance</div><div></div></div></div> <table><thead><tr><th colspan="2">Length</th><th colspan="2">Radii</th></tr></thead><tbody><tr><td>0-6</td><td>± 0.2</td><td>0-6</td><td>± 0.2</td></tr><tr><td>>6-15</td><td>± 0.4</td><td>>6-15</td><td>±</td></tr><tr><td>>15-30</td><td>± 0.4</td><td>>15-30</td><td>±</td></tr><tr><td>>30-70</td><td>±</td><td>>30-200</td><td>±</td></tr><tr><td>>70-120</td><td>±</td><td></td><td>±</td></tr><tr><td>>120-200</td><td>±</td><td></td><td>±</td></tr><tr><td></td><td>±</td><td></td><td>±</td></tr><tr><td></td><td>±</td><td></td><td>±</td></tr></tbody></table>						Length		Radii		0-6	± 0.2	0-6	± 0.2	>6-15	± 0.4	>6-15	±	>15-30	± 0.4	>15-30	±	>30-70	±	>30-200	±	>70-120	±		±	>120-200	±		±		±		±		±		±	Sheet 01		Ident.	Document number	Index
						Length		Radii																																						
						0-6	± 0.2	0-6	± 0.2																																					
						>6-15	± 0.4	>6-15	±																																					
						>15-30	± 0.4	>15-30	±																																					
						>30-70	±	>30-200	±																																					
						>70-120	±		±																																					
						>120-200	±		±																																					
							±		±																																					
							±		±																																					
Format DIN	Projection	Scale	K	18021126	e																																									
A4		1:1	Appliance Switch																																											
All dimensions are in millimetres																																														
System NX V1899																																														
Replacement of Zg.gl.Nr.v.23.07.1997																																														
e	137845	2023-02-14	MUT																																											
d	102505	2016-09-29	MUT																																											
c	86362	2013-09-27	MUT																																											
b	37630	2003-09-16	VOR																																											
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by																																											

 MARQUARDT | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[01802.1126-02](#)