











CONFIDENTIAL

VERTRAULICH

THIS DRAWING IS THE EXCLUSIVE PROPERTY  
OF MARQUARDT. WITHOUT THEIR CONSENT IT MAY  
NOT BE REPRODUCED OR GIVEN TO THIRD PARTIES.

Alle Rechte bei Marquardt, auch fuer den  
Fall von Schutzrechtsanmeldungen. Jede Veruegungs-  
befugnis, wie Kopier- und Weitergaberecht, bei uns.

A	1	2	3	4
	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness	length of cut-out	width of cut-out
		0.75 to 1.25	19.2-0.1	12.9+0.1
		1.25 to 2	19.4-0.1	12.9+0.1
B		2 to 3	19.8-0.1	12.9+0.1
C	 			
				
D	<p>Marking</p> <p>1803.</p> <p>6(4)/250~5E4</p> <p>10(4)250~ T100/55</p> 			
	<p>SPDT</p> <p>Suitable for appliances of class II</p> 			
E	<p>10A 125-250V AC</p> <p>1/3HP 125V AC</p> <p>1/2HP 250V AC</p> <p>R50  </p> <p>Code of manufacture: place/year/week</p>			
				

-	-	-	1803.1121-XX
Figure	Type	Customer Part No.	Art.No.-PI
Shape and location 	Angle $\pm 2^\circ$	Sheet 01	
	Edge tolerance	Ident.	Document number
		K	18031121
		Appliance Switch	
f	137892	2021-07-29	PANDHAREA
e	66315	2009-11-30	MUT
d	64510	2009-10-01	MUT
c	29281	2000-05-11	SIG
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by
All dimensions are in millimetres		Format DIN A4	Projection  Scale 1:1
System NX V1872		Replacement of	
Zg.gl.Nr.v.11.05.2000		MARQUARDT	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Marquardt:

1803.1121