





A	1	2	3	4
	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness	length of cut-out	width of cut-out
		0.75 to 1.25	30-0.1	6.8+0.1
		1.25 to 2	30.2 -0.1	6.8+0.1
		2 to 3	30.6 -0.1	6.8+0.1



SPST
Suitable for appliances of class II

Marking




1921.

4(1)/250~5E4

6(2)/250~

T80/55



Code of manufacture: place/year/week

-		-									1921.1102-XX					
Figure		Type						Customer Part No.			Art.No.-PI					
Shape and location 		Angle $\pm 2^\circ$ Edge tolerance 		Length			Radii			Sheet 01			Ident. K	Document number 19211102	Index i	
				0-6	± 0.2		$\pm$		$\pm$	± 0.2	Format DIN A4	Projection 				Scale 1:1
				>6-15	± 0.4		$\pm$		$\pm$	$\pm$						
				>15-30	± 0.4		$\pm$		$\pm$	$\pm$						
					$\pm$		$\pm$		$\pm$	$\pm$						
					$\pm$		$\pm$		$\pm$	$\pm$						
					$\pm$		$\pm$		$\pm$	$\pm$						
					$\pm$		$\pm$		$\pm$	$\pm$						
					$\pm$		$\pm$		$\pm$	$\pm$	All dimensions are in millimetres			Appliance Switch		
					$\pm$		$\pm$		$\pm$	$\pm$						
i	141238	2022-11-23			MOHITEN			System NX V1899 Replacement of Zg.gl.Nr.v.18.03.1991			 MARQUARDT					
h	102884	2016-06-22			HHE											
g	43248	2005-05-31			hhe											
f	25675	1998-03-23			SIG											
Index	MEC-No.	Date (YYYY-MM-DD)			Edited by											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[01921.1102-02](#)