



Flachstecker DIN 46244-A2.8-0.5
(EN 61058 / EN 61210)




Aufschrift

(M)
 1050 μ
 5/250~
 50E3 T100 
 5A 125-250V AC 1/10HP
 R 56  
 Herstelljahr/-woche
 nach DIN EN 60062

Schließer 1-polig

Schalt-Betätigungskraft ≤ 1.50 N
 Rückschaltkraft ≥ 0.50 N
 Differenzweg ≤ 0.20 mm

Schutzvermerk
 nach DIN 34 beachten
 COPYRIGHT RESERVED

Allgemeintoleranzen/UNTOLERANCED DIMENSIONS				PROJECTION		Pause COPY		Blatt von SHEET OF		Zeichn./DRAWING NO.	
Für Längen und Radien FOR LENGTHS AND RADII.		Abmaße in mm für Nennmaßbereich in mm ALL DIMENSIONS ARE IN MILLIMETRES						Original Maßstab DIN SCALE		S 1050.1122 Schnappschalter	
±		bis/UP TO 6	über/OVER 6 bis/UP TO 30	über/OVER 30	A4 2:1						
		0.2	0.3				gez./DRAWN BY 03.12.91 Ble		 Marquardt GmbH, D-78604 Rietheim-Weilheim		
d				i			Ersatz für/REPLACEMENT OF				
c				h							
b	29547	08.06.00	pfu	g							
a	22621	19.01.94	mk	f							
Ausg. ISSUE		Änderung REVISION		gez. DRAWN BY		Ausg. ISSUE		Änderung REVISION		gez. DRAWN BY	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[1050.1122](#)