

1		2		3		4	
A	Empfohlener Ausschnitt für Rastbefestigung (Grat gegenüber Bestueckungsseite) recommended cut-out for snap-in fixing (edge opposite to snap-in direction)			Wanddicke wall thickness		Ausschnittlänge length of cut-out	
				0.8 to / bis 5.0		27.2 ±0.1	
B	VERTRAULICH-CONFIDENTIAL Alle Rechte bei Marquardt, auch fuer den Fall von Schutzrechtsmeldungen. Jede Verfuegungsbefugnis, wie Kopier- und Weitergaberecht, bei uns. This document is the exclusive property of Marquardt. Without our consent, it may not be reproduced or given to third parties.						
	Top view dimensions: 27 -0.2, 6.5, 26, 2.4, 12, 23.4, 2, 10, 12.2, 17.8, 29.8, 0.8, 6, 12. Side view dimensions: 30, 15, R1. Labels: schwarz black, Wippe schwarz Zeichen weiß rocker black symbol white.						
C							
D	Aufschrift Marking ① 155.. 16(4)/250 ~ T100/55 T100 10(4)/250 ~ 5E4 5/100A 250V ~ 05 16A 125-250V AC 1 HP 125V AC 2 HP 250V AC R38						
	DPST suitable for appliances of class II Ausschalter 2-polig Fuer Gerate der Klasse II geeignet						
E							

Fur Form und Logo FOR SHAPE AND LOC.		Fur Winkel FOR ANGLE		Allgemeintoleranzen UNTOLERANCED DIMENSIONS		Pause COPY		Blatt SHEET		Typ		Zeichn./DRAWING NO.		Index																									
				Abmasse und Nennmassbereiche Angaben in mm <table border="1"> <tr> <td>0-6</td> <td>± 0.2</td> <td>Laengen LENGTH</td> <td>Radien RADII</td> </tr> <tr> <td>>6-15</td> <td>± 0.4</td> <td></td> <td></td> </tr> <tr> <td>>15-30</td> <td>± 0.4</td> <td></td> <td></td> </tr> <tr> <td>>30-70</td> <td>±</td> <td></td> <td></td> </tr> <tr> <td>>70-120</td> <td>±</td> <td></td> <td></td> </tr> <tr> <td>>120-200</td> <td>±</td> <td></td> <td></td> </tr> </table> ALL DIMENSIONS ARE IN MILLIMETRES		0-6	± 0.2	Laengen LENGTH	Radien RADII	>6-15	± 0.4			>15-30	± 0.4			>30-70	±			>70-120	±			>120-200	±			Original DIN Maßstab SCALE 1:1		0 10 20 30 mm		K		1552.0102		Geraeteschalter Appliance Switch	
0-6	± 0.2	Laengen LENGTH	Radien RADII																																				
>6-15	± 0.4																																						
>15-30	± 0.4																																						
>30-70	±																																						
>70-120	±																																						
>120-200	±																																						
c 35129 27.02.03 wj g b 23635 10.11.95 R5 f a 21323 23.04.92 Mut e		d 69572 29.09.10 hhe		CAD Medusa Z		gez./DRAWN BY 12.04.88 ZF gepr./CHECKED BY Lr		Ersatz für/REPLACEMENT OF		MARQUARDT Marquardt, D-78604 Rietheim-Weilheim																													
Ausg. ISSUE		Änderung REVISION		gez. DRAWN BY		Ausg. ISSUE		Änderung REVISION		gez. DRAWN BY																													

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[1552.0102](#)