




BIAS 4 Watt LED Drivers

Single, universal output

BPWXL 4-12U-035 (350mA constant current)

BPWXLD 4-12U-035 (350mA, 0-10 dimmable)



Benefits

- Highly reliable, rugged construction for indoor or outdoor applications
- True 0-10 volt dimming with 1000:1 range
- 1% current regulation and no flicker
- Color coded flying leads for simple assembly and installation
- AC line or DC load switching without overshoot on startup

Features

- Universal Input (100-308 VAC, 50/60Hz)
- Universal Output (3-12VDC), 350mA
- Ingress protection to IP66 (IP67 pending)
- -40 to +85°C ambient, 90°C maximum case temperature
- Flying Leads for AC and LED connections
- 3000 VAC Isolation
- 75% efficiency
- EN 55022, Class B; FCC Part 15, Class B
- Meets UL/CSA and EN Product Safety Requirements (UL 8750 Class 2)
- Overcurrent, short circuit (shorted string), open circuit (string break) and overload protected

Operating Specifications

(@120VAC / 60 Hz / 25°C unless otherwise specified)



Electrical	
Input Voltage Range	100-308 VAC (50/60Hz)
Output Power (Pmax)	4 W nom (50/60Hz)
String Voltage (Minimum)	3.0 VDC
Efficiency	75% nom.
Temperature Regulation I _o (Peak)	+/- 2%, P _o < P _{max}
Isolation	3000 VAC (meets UL/CSA & EN Product Safety)
Earth Leakage @ 120 VAC	< 10 uA
Short Circuit Protection	Continuous, Pin ≤ 0.7 w @ 120 VAC
Reliability @ 25° C, MIL HDBK-217F	> 500 Khr MTBF

Environmental	
Operating Temperature	-40 to 85° C
Case Temperature, maximum	90° C
Storage Temperature	-40 to 105° C
Ingress Protection	IP67
Mechanical	
Package Size (L x W x H)	1.9 x 1.74 x 0.94 inches
Lead Length	11", 18AWG
Safety	
Safety Compliance	UL 8750 Class 2/CAN/CSA c22.2
EMI Emissions	EN 55022, Class B, FCC Part 15, Class B

Model Number	BPWXL 4-12U-035	BPWXLD 4-12U-035
Output Voltage, max string Volts	12 VDC	12 VDC
Output Current	350 mA	350 mA
Dimming	N/A	0 to 10 VDC, V _d
Dimming Linearity	N/A	+/- 2%
Line Regulation, I _o (Peak)	+/- 1%, P _o < P _{max}	+/- 1%, P _o < P _{max}
Line Regulation, V _o (Peak)	N/A	N/A
AC Input Connections	Line - Black, Neutral -White	Line - Black, Neutral -White
DC Output Connections	Pos(+) - Red, Neg (-) - Blue	Pos(+) - Red, Neg (-) - Blue
Dimming (0-10 / Common)	N/A	Pos(+)-Orange / Neg(-) -Green




BIAS 4 Watt LED Drivers

Single, universal output



BPWXL 4-12U-035 (350mA constant current)

BPWXLD 4-12U-035 (350mA, 0-10 dimmable)

BPWXL 4-12U-035



BPWXLD 4-12U-035



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[BIAS Power:](#)

[BPWXLD4-12U-035](#)