


 Part Number Search

 Site Search

BUSINESS UNITS

NEWS

ABOUT US

DISTRIBUTORS & REPS

CONTACT US

Home

Part Number Search Results

The results below match possible part numbers you may have been searching for.

PART NUMBER	DESCRIPTION	ORDER SAMPLES	CHECK STOCK	DATASHEET	3D DRAWINGS	RoHS DOCS
<u>937-030</u>	Nylon Tubular, 0.030 in. Length, 0.125 OD, 0.090 ID, White					
<u>937-035</u>	Nylon Tubular, 0.035 in. Length, 0.125 OD, 0.090 ID, White					
<u>937-040</u>	Nylon Tubular, 0.040 in. Length, 0.125 OD, 0.090 ID, White					
<u>937-045</u>	Nylon Tubular, 0.045 in. Length, 0.125 OD, 0.090 ID, White					
<u>937-050</u>	Nylon Tubular, 0.050 in. Length, 0.125 OD, 0.090 ID, White					
<u>937-055</u>	Nylon Tubular, 0.055 in. Length, 0.125 OD, 0.090 ID, White					
<u>937-060</u>	Nylon Tubular, 0.060 in. Length, 0.125 OD, 0.090 ID, White					
<u>937-065</u>	Nylon Tubular, 0.065 in. Length, 0.125 OD, 0.090 ID, White					
<u>937-070</u>	Nylon Tubular, 0.070 in. Length, 0.125 OD, 0.090 ID, White					
<u>937-075</u>	Nylon Tubular, 0.075 in. Length, 0.125 OD, 0.090 ID, White					
<u>937-080</u>	Nylon Tubular, 0.080 in. Length, 0.125 OD, 0.090 ID, White					
<u>937-090</u>	Nylon Tubular, 0.090 in. Length, 0.125 OD, 0.090 ID, White					
<u>937-095</u>	Nylon Tubular, 0.095 in. Length, 0.125 OD, 0.090 ID, White					
<u>937-098</u>	Nylon Tubular, 0.098 in. Length, 0.125 OD, 0.090 ID, White					

	White					
937-1.000	Nylon Tubular, 1.000 in. Length, 0.125 OD, 0.090 ID, White					
937-100	Nylon Tubular, 0.100 in. Length, 0.125 OD, 0.090 ID, White					
937-105	Nylon Tubular, 0.105 in. Length, 0.125 OD, 0.090 ID, White					
937-10MM	Nylon Tubular, 10 mm Length, 0.125 OD, 0.090 ID, White					
937-110	Nylon Tubular, 0.110 in. Length, 0.125 OD, 0.090 ID, White					
937-115	Nylon Tubular, 0.115 in. Length, 0.125 OD, 0.090 ID, White					
937-11MM	Nylon Tubular, 11 mm Length, 0.125 OD, 0.090 ID, White					
937-120	Nylon Tubular, 0.120 in. Length, 0.125 OD, 0.090 ID, White					
937-125	Nylon Tubular, 0.125 in. Length, 0.125 OD, 0.090 ID, White					
937-12MM	Nylon Tubular, 12 mm Length, 0.125 OD, 0.090 ID, White					
937-130	Nylon Tubular, 0.130 in. Length, 0.125 OD, 0.090 ID, White					
937-135	Nylon Tubular, 0.135 in. Length, 0.125 OD, 0.090 ID, White					
937-140	Nylon Tubular, 0.140 in. Length, 0.125 OD, 0.090 ID, White					
937-145	Nylon Tubular, 0.145 in. Length, 0.125 OD, 0.090 ID, White					
937-150	Nylon Tubular, 0.150 in. Length, 0.125 OD, 0.090 ID, White					
937-155	Nylon Tubular, 0.155 in. Length, 0.125 OD, 0.090 ID, White					
937-160	Nylon Tubular, 0.160 in. Length, 0.125 OD, 0.090 ID, White					
937-165	Nylon Tubular, 0.165 in. Length, 0.125 OD, 0.090 ID, White					
937-170	Nylon Tubular, 0.170 in. Length, 0.125 OD, 0.090 ID, White					
937-175	Nylon Tubular, 0.175 in. Length, 0.125 OD, 0.090 ID, White					
937-17MM	Nylon Tubular, 17 mm Length, 0.125 OD, 0.090 ID, White					
937-180	Nylon Tubular, 0.180 in. Length, 0.125 OD, 0.090 ID, White					
937-185	Nylon Tubular, 0.185 in. Length, 0.125 OD, 0.090 ID, White					

937-190	Nylon Tubular, 0.190 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-195	Nylon Tubular, 0.195 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-1MM	Nylon Tubular, 1 mm Length, 0.125 OD, 0.090 ID, White					 RoHS
937-200	Nylon Tubular, 0.200 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-205	Nylon Tubular, 0.205 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-210	Nylon Tubular, 0.210 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-215	Nylon Tubular, 0.215 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-220	Nylon Tubular, 0.220 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-225	Nylon Tubular, 0.225 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-235	Nylon Tubular, 0.235 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-240	Nylon Tubular, 0.240 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-250	Nylon Tubular, 0.250 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-255	Nylon Tubular, 0.255 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-260	Nylon Tubular, 0.260 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-270	Nylon Tubular, 0.270 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-275	Nylon Tubular, 0.275 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-280	Nylon Tubular, 0.280 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-2MM	Nylon Tubular, 2 mm Length, 0.125 OD, 0.090 ID, White					 RoHS
937-300	Nylon Tubular, 0.300 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-310	Nylon Tubular, 0.310 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-315	Nylon Tubular, 0.315 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-320	Nylon Tubular, 0.320 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-325	Nylon Tubular, 0.325 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-330	Nylon Tubular, 0.330 in. Length, 0.125 OD, 0.090 ID, White					 RoHS

937-335	Nylon Tubular, 0.335 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-345	Nylon Tubular, 0.345 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-350	Nylon Tubular, 0.350 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-355	Nylon Tubular, 0.355 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-375	Nylon Tubular, 0.375 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-3MM	Nylon Tubular, 3 mm Length, 0.125 OD, 0.090 ID, White					 RoHS
937-400	Nylon Tubular, 0.400 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-410	Nylon Tubular, 0.410 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-415	Nylon Tubular, 0.415 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-420	Nylon Tubular, 0.420 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-435	Nylon Tubular, 0.435 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-437	Nylon Tubular, 0.437 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-440	Nylon Tubular, 0.440 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-4MM	Nylon Tubular, 4 mm Length, 0.125 OD, 0.090 ID, White					 RoHS
937-500	Nylon Tubular, 0.500 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-520	Nylon Tubular, 0.520 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-530	Nylon Tubular, 0.530 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-551	Nylon Tubular, 0.551 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-560	Nylon Tubular, 0.560 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-590	Nylon Tubular, 0.590 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-5MM	Nylon Tubular, 5 mm Length, 0.125 OD, 0.090 ID, White					 RoHS
937-600	Nylon Tubular, 0.600 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-625	Nylon Tubular, 0.625 in. Length, 0.125 OD, 0.090 ID, White					 RoHS
937-685	Nylon Tubular, 0.685 in. Length, 0.125 OD, 0.090 ID, White					 RoHS

937-690	Nylon Tubular, 0.690 in. Length, 0.125 OD, 0.090 ID, White					
937-6MM	Nylon Tubular, 6 mm Length, 0.125 OD, 0.090 ID, White					
937-750	Nylon Tubular, 0.750 in. Length, 0.125 OD, 0.090 ID, White					
937-7MM	Nylon Tubular, 7 mm Length, 0.125 OD, 0.090 ID, White					
937-800	Nylon Tubular, 0.800 in. Length, 0.125 OD, 0.090 ID, White					
937-810	Nylon Tubular, 0.810 in. Length, 0.125 OD, 0.090 ID, White					
937-875	Nylon Tubular, 0.875 in. Length, 0.125 OD, 0.090 ID, White					
937-8MM	Nylon Tubular, 8 mm Length, 0.125 OD, 0.090 ID, White					
937-925	Nylon Tubular, 0.925 in. Length, 0.125 OD, 0.090 ID, White					
937-935	Nylon Tubular, 0.935 in. Length, 0.125 OD, 0.090 ID, White					
937-9MM	Nylon Tubular, 9 mm Length, 0.125 OD, 0.090 ID, White					

News

[Latest News](#)
[Archives](#)

About Us

[Company Profile](#)
[Quality Assurance](#)
[Careers](#)

Distributors & Reps

Bivar Sites

[Bivar Corporate](#)
[Enclosure Hardware](#)
[LED Indication](#)
[LED Lighting](#)
[MyBivar](#)

© 2014 Bivar Inc., All Rights Reserved.

[Contact Us](#)

[Terms & Conditions](#) | [Privacy Policy](#) | [Sitemap](#)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[BIVAR:](#)

[937-098](#) [937-1.000](#) [937-10MM](#) [937-11MM](#) [937-12MM](#) [937-17MM](#) [937-1MM](#) [937-2MM](#) [937-3MM](#) [937-4MM](#) [937-5MM](#) [937-6MM](#) [937-7MM](#) [937-8MM](#) [937-9MM](#)