



CAPACITOR MOUNTS

Single In-Line Mounts

- Works with Capacitors, Resistor Networks and any other electrical component with in-line lead configurations



Material Specifications:

Natural Nylon, per ASTM D4066
PA111, UL Rated 94V-2


Oxygen Rating Index: Over 28%

Standard Drawing Tolerances:

(unless otherwise indicated)


Fractions: $\pm 1/64$ (0.4) .XX = ± 0.01 (0.25)

.X = ± 0.10 (2.5) .XXX = ± 0.005 (0.13)



3XX Series

Part No.	A	B	C	D	F	H	Price Code
330-200					.000	.030 (.76)	A
331-200	.076 (1.9)	.200 (5.1)	.235 (6.0)	.297 (7.5)	.030 (.76)	.060 (1.5)	
332-200					.060 (1.5)	.090 (2.3)	
335-300					.000	.030 (.76)	A
336-300	.176 (4.5)	.300 (7.6)	.335 (8.5)	.397 (10.1)	.030 (.76)	.060 (1.5)	
337-300					.060 (1.5)	.090 (2.3)	
340-400					.000	.030 (.76)	B
341-400	.276 (7.0)	.400 (10.2)	.435 (11.0)	.497 (12.6)	.030 (.76)	.060 (1.5)	
342-400					.060 (1.5)	.090 (2.3)	
345-500					.000	.030 (.76)	B
346-500	.376 (9.6)	.500 (12.7)	.535 (13.6)	.597 (15.2)	.030 (.76)	.060 (1.5)	
347-500					.060 (1.5)	.090 (2.3)	
350-600					.000	.030 (.76)	G
351-600	.476 (12.1)	.600 (15.2)	.635 (16.1)	.697 (17.7)	.030 (.76)	.060 (1.5)	
352-600					.060 (1.5)	.090 (2.3)	
355-700					.000	.030 (.76)	G
356-700	.576 (14.6)	.700 (17.8)	.735 (18.7)	.797 (20.2)	.030 (.76)	.060 (1.5)	
357-700					.060 (1.5)	.090 (2.3)	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[330-200](#) [331-200](#)