




REV.	DESCRIPTION	DATE	APPROVED
F	Production Release.	02/24/04	M. C.
G	Added Max. Allowable Draft Angle.	06/13/13	T. Y.
H	Added Notes 4, 5, 6 & Color Options Sheet #2	05/04/16	J. C.



PART NO.	COLOR	ROLL PIN	CARD THICK.
CP-36 NT	NATURAL	RP-250	1/16"(1.6mm)
CP-36 WE	WHITE	RP-250	
CP-36 XX	SEE S.#2	RP-250	
CP-39 NT	NATURAL	RP-250	3/32"(2.4mm)
CP-39 WE	WHITE	RP-250	
CP-39 XX	SEE S.#2	RP-250	



5. PRE-ASSEMBLED ROLL PINS AVAILABLE UPON REQUEST.
4. ROLL PINS INCLUDED. PACKAGED SEPARATELY.
3. MATERIAL: NYLON 6/6, 94V-2, WHITE.
2. MATERIAL: NYLON 6/6, 94V-2, NATURAL.
1. GENERAL SPECIFICATIONS: BIVAR MOLDED COMPONENT SPECIFICATION BV00-E101.

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°		TITLE: CIRCUIT BOARD CARD EJECTOR
.XX ± .01			PART NO: CP-3X
.XXX ± .005			REVISION: H
DESIGNED: S. Irving	DATE: 05/19/98	CAGE CODE : 32559 SHEET # 1 OF 2	
CHECKED: M. Chen	DATE: 09/09/03	CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.	

OTHER AVAILABLE COLORS
* SEE TABLE FOR ORDERING INFORMATION

REV.	DESCRIPTION	DATE	APPROVED
	SEE SHEET #1		

CP- 3 _ _ _

CP SERIES	ORDER CODE	COLOR
CP-36	AA	AQUA
CP-39	BK	BLACK
	BE	BLUE
	BN	BROWN
	FG	FOREST GREEN
	GY	GRAY
	GN	GREEN
	LE	LIME
	OE	ORANGE
	PK	PINK
	RD	RED
	VT	VIOLET
	YW	YELLOW

6. PARTS ARE DYED TO COLOR UPON REQUEST.

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED) DECIMALS ANGULAR		 4 THOMAS, IRVINE, CA. 92618 TEL.: (949) 951-8808 FAX: (949) 951-3974	
			
DESIGNED: S. Irving	DATE: 05/19/98	TITLE: CIRCUIT BOARD CARD EJECTOR	
CHECKED: M. Chen	DATE: 09/09/03	PART NO: CP-3X	REVISION: H
		CAGE CODE : 32559	SHEET # 2 OF 2
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[CP-36 YW](#) [CP-36 OE](#) [CP-36 LE](#) [CP-39 RD](#) [CP-36 GN](#) [CP-39 BE](#) [CP-39 YW](#) [CP-39 VT](#) [CP-3 BE](#) [CP-39 OE](#) [CP-39 GN](#) [CP-39 BN](#) [CP-3 RD](#) [CP-39 AA](#) [CP-36 BE](#) [CP-36 AA](#) [CP-36 BE/PA](#) [CP-36 BN](#) [CP-36 EB](#) [CP-36 FG](#) [CP-36 GN/PA](#) [CP-36 GY](#) [CP-36 NT/HS](#) [CP-36 PA](#) [CP-36 PK](#) [CP-36 RD/PA](#) [CP-36 VT/PA](#) [CP-36 WE/HS](#) [CP-36 WE/PA](#) [CP-36 WE/PA/HS](#) [CP-36 WE/PA1](#) [CP-36 WE/PA-F](#) [CP-36 WE-test](#) [CP-36 YW/PA](#) [CP-39 EB](#) [CP-39 FG](#) [CP-39 GY](#) [CP-39 LE](#) [CP-39 NT](#) [CP-39 PK](#) [CP-39 WE/PA](#) [CP-39 YW/HS](#)