



NOTES:
1. ALLOWABLE CUT LENGTH IS UP TO 3 DECIMAL PLACES.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
E	FLP LENGTH UPDATE	10/18/2005	M.C.
F	FLP LENGTH CLARIFICATION	1/11/2006	M.C.
G	UPDATED FIBER IN BOM	11/16/2012	T.Y.
H	ECO-1216 - UPDATED LENS DIMENSIONS	8/22/2023	A.V.
J	ECO-1242 - UPDATED DIMENSIONS & VIEWS	3/27/2024	A.V.



LENGTH (L)	TOLERANCE
0.750" ~ 16.000"	±0.050"
16.001" ~ 40.000"	±0.150"
40.001" ~ 80.000"	±0.300"
80.001" ~ 3,940.0"	±0.500"

CUSTOMER USE DRAWING

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		BIVAR [®] 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°		
.XX ± .02			
.XXX ± .010		TITLE: LENS CAP/FLP ASSEMBLY 7MM ROUND	
DESIGNED: S. IRVING	DATE: 5/22/2002	DRAWING NO: FLP5-XX.X	
REVISD: K. BARON	DATE: 3/27/2024	SHEET SIZE A	CAGE CODE: 32559
CHECKED: A. VALDEZ	DATE: 3/27/2024	SCALE: 2:1	SHEET # 1 OF 1
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[BIVAR:](#)

[FLP5-1.5](#) [FLP5-10.0](#) [FLP5-12.0](#) [FLP5-14.0](#) [FLP5-15.0](#) [FLP5-18.0](#) [FLP5-2.0](#) [FLP5-20.0](#) [FLP5-24.0](#) [FLP5-3.0](#)
[FLP5-30.0](#) [FLP5-36.0](#) [FLP5-39.5](#) [FLP5-4.0](#) [FLP5-48.0](#) [FLP5-5.0](#) [FLP5-6.0](#) [FLP5-6.5](#) [FLP5-7.5](#) [FLP5-72.21](#) [FLP5-](#)
[8.0](#) [FLP5-9.0](#) [FLP5-2.5](#) [FLP5-2.21](#) [FLP5-7.0](#) [FLP5-33.0](#) [FLP5-19.0](#) [FLP5-19.7](#) [FLP5-3.5](#) [FLP5-39.4](#) [FLP5-4.5](#)
[FLP5-5.5](#) [FLP5-6.7](#) [FLP5-72.0](#) [FLP5-79.0](#) [FLP5-9.5](#)