



ITEM	Q'TY	PART NUMBER	PART DESCRIPTION
1	1	FLP-LC-5-01	HOLDER CAP, FLEXIBLE LIGHT-PIPE, INSERT
2	1	FLP-LC-5-02	HOLDER CAP, FLEXIBLE LIGHT-PIPE, BODY
3	1	FLPS1022-X.XXX	LIGHT PIPE CABLE, CUT LENGTH IN INCHES

REV.	DESCRIPTION	DATE	APPROVED
C	Engineering Update w/o Changes	03/05/04	M. C.
D	Dimensioning Update w/o Changes	01/05/05	M. C.
E	FLP Length Update.	10/18/05	M. C.
F	FLP Length Clarification.	01/11/06	M. C.
G	Updated Fiber In BOM	11/16/12	T. Y.



" L "	Tolerance
0.750" ~ 16.000"	±0.050"
16.100" ~ 40.000"	±0.150"
40.100" ~ 80.000"	±0.300"
80.100" ~ 3,940.0"	±0.5%

*NOTE:
ALLOWABLE CUT LENGTH IS UP TO 3 DECIMAL PLACES.

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ±.1	X° ± 1°	 TITLE: LENS CAP / FLP ASSEMBLY, 7mm ROUND	
.XX ±.02			
.XXX ±.010		DESIGNED: Shane Irving	DATE: 05/22/02
		CHECKED: M. Chen	DATE: 05/22/02
		PART NO: FLP5-XX.X	REVISION: G
		CAGE CODE : 32559	SHEET # 1 OF 1

CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[FLP5-1.0](#) [FLP5-1.18](#) [FLP5-1.5](#) [FLP5-1.73](#) [FLP5-10.0](#) [FLP5-11.5](#) [FLP5-12.0](#) [FLP5-14.0](#) [FLP5-15.0](#) [FLP5-18.0](#)
[FLP5-2.0](#) [FLP5-2.50](#) [FLP5-2.75](#) [FLP5-20.0](#) [FLP5-24.0](#) [FLP5-26.0](#) [FLP5-3.0](#) [FLP5-30.0](#) [FLP5-36.0](#) [FLP5-360.0](#)
[FLP5-39.5](#) [FLP5-4.0](#) [FLP5-48.0](#) [FLP5-5.0](#) [FLP5-6.0](#) [FLP5-6.5](#) [FLP5-6.70](#) [FLP5-60.0](#) [FLP5-7.5](#) [FLP5-72.21](#) [FLP5-8.0](#) [FLP5-8.5](#) [FLP5-9.0](#)