




| REV. | DESCRIPTION         | DATE     | APPROVED |
|------|---------------------|----------|----------|
| A    | Engineering Release | 05/12/17 | J. C.    |
|      |                     |          |          |
|      |                     |          |          |
|      |                     |          |          |
|      |                     |          |          |

| *Length "X.XXX"    | Tolerance |
|--------------------|-----------|
| 2.000" ~ 16.000"   | ±0.050"   |
| 16.001" ~ 40.000"  | ±0.150"   |
| 40.001" ~ 80.000"  | ±0.300"   |
| 80.001" ~ 500.000" | ±0.5%     |



Part Number Configuration  
LC4-6.500-F9PX67PR

Lens Options:  
Z – Clear Fresnel  
D – Diffused  
Blank – Clear

Length in 0.001"  
Increments Only

#### NOTES:

1. SEALED TO IP67 RATING
2. ROHS COMPLIANT
3. MOUNTING HARDWARE SHIPPED NON-ASSEMBLED
4. MINIMUM BEND RADIUS OF FLEXIBLE LIGHT PIPE: 1.22" [31mm]

|                                                      |                          |                                                                                                                                                                 |  |
|------------------------------------------------------|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| STANDARD TOLERANCE<br>( UNLESS OTHERWISE SPECIFIED ) |                          | <br>4 THOMAS, IRVINE, CA. 92618<br>TEL: (949) 951-8808 FAX: (949) 951-3974 |  |
| <u>DECIMALS</u>                                      | <u>ANGULAR</u>           |                                                                                                                                                                 |  |
| .X ± .1                                              | X° ± 1°                  | <br><b>TITLE:</b> IP67 RATED PANEL MOUNT<br>FLEXIBLE LIGHT PIPE INDICATOR  |  |
| .XX ± .02                                            |                          |                                                                                                                                                                 |  |
| .XXX ± .010                                          |                          |                                                                                                                                                                 |  |
| DESIGNED:<br><b>TD. Nguyen</b>                       | DATE:<br><b>04/30/17</b> | <b>PART NO:</b><br>LC4-X.XXX-F9PX67PR                                                                                                                           |  |
|                                                      |                          | REVISION<br><b>A</b>                                                                                                                                            |  |
| CHECKED:<br><b>K. Baron</b>                          | DATE:<br><b>04/30/17</b> | <b>CAGE CODE :</b> 32559                                                                                                                                        |  |
|                                                      |                          | <b>SHEET # 1 OF 1</b>                                                                                                                                           |  |
| CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING       |                          |                                                                                                                                                                 |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## BIVAR:

[LC4-6.000-F9P67PR-2](#) [LC4-6.000-F9P67PR-4](#) [LC4-6.000-F9P67PR-5](#) [LC4-6.000-F9P67PR-6](#) [LC4-6.000-F9P67PR-9](#) [LC4-6.000-F9PD67PR-2](#) [LC4-6.000-F9PD67PR-4](#) [LC4-6.000-F9PD67PR-5](#) [LC4-6.000-F9PD67PR-6](#) [LC4-6.000-F9PD67PR-9](#) [LC4-6.000-F9PZ67PR-2](#) [LC4-6.000-F9PZ67PR-4](#) [LC4-6.000-F9PZ67PR-5](#) [LC4-6.000-F9PZ67PR-6](#) [LC4-6.000-F9PZ67PR-9](#)