


ITEM	Q'TY	PART NUMBER	PART DESCRIPTION
1	1	FLP-LC	HOLDER CAP, FLEXIBLE LIGHT-PIPE
2 1 FLPS1022-X.XXX LIGHT PIPE CABLE, CUT LENG		LIGHT PIPE CABLE, CUT LENGTH IN INCHES	



② FLPS1022-X.XXX





" L "	Tolerance
0.750" ~ 16.000"	±0.050"
16.100" ~ 40.000"	±0.150"
40.100" ~ 80.000"	±0.300"
80.100" ~ 3,940.0"	±0.5%

NOTE:

- 1. ALLOWABLE CUT LENGTH IS UP TO 3 DECIMAL PLACES.
- 2. MINIMUM BEND RADIUS OF FLEXIBLE LIGHT PIPE: 0.87" [22mm].

STANDARD TOI (UNLESS OTHERWIS		BIV	ΛD	®
DECIMALS	ANGULAR			410
.X ± .1 .XX ± .02	X° ± 1°	1° 4 THOMAS, IRVINE, CA TEL: (949) 951-8808 FAX: (949)		
.XXX ± .010		TITLE: LENS CAP	4mm F	EMBLY, ROUND
DESIGNED: S. Irving	DATE: 05/22/02	PART NO: LC-XX.X		REVISION:
CHECKED: M. Chen	DATE: 05/22/02	CAGE CODE: 32559	SHEET # 1	OF 1
w. Chen	05/22/02	CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

<u>LC-1.38 LC-1.395 LC-17.0 LC-19.7 LC-19.9 LC-2.1 LC-2.7 LC-2.8 LC-25.5 LC-3.12 LC-3.3 LC-37.0 LC-39.4 LC-4.12 LC-4.15 LC-5.25 LC-5.975 LC-6.125 LC-6.7</u>