






NOTES:

1. PARTS ARE SHIPPED NON-ASSEMBLED.
2. SEE SHEET 4 FOR PACKAGING PLAN.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
B	Engineering Release	7/11/2018	G.O.
C	ECO-1250 - Updated Component Views	5/3/2024	A.V.
D	ECO-1279 - Updated MFG Drawing	8/2/2024	A.V.



CUSTOMER USE DRAWING



STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X $\pm .1$	X° $\pm 1^\circ$	TITLE: BIVAR LIGHT PIPE SYSTEM	
.XX $\pm .02$		SAT VERTICAL, 3MM, SINGLE STATION	
.XXX $\pm .010$		DRAWING NO: LPV3-XXXXX-XXX	
DESIGNED: K. BARON	DATE: 7/11/2018	REVISION: D	
REVISED: K. BARON	DATE: 8/2/2024	SHEET SIZE A	CAGE CODE: 32559
CHECKED: D. ASHBY	DATE: 8/2/2024	SCALE: 2:1	SHEET # 1 OF 5
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING			

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
	See Sheet 1		


STANDARD ORDERING INFORMATION

TABLE A - FLAT FACE LENS	
PART NO.	H ± .01
LPV3-0350F-XXX	0.350 [8.9mm]
LPV3-0400F-XXX	0.400 [10.2mm]
LPV3-0450F-XXX	0.450 [11.4mm]
LPV3-0500F-XXX	0.500 [12.7mm]
LPV3-0550F-XXX	0.550 [14.0mm]
LPV3-0600F-XXX	0.600 [15.2mm]
LPV3-0750F-XXX	0.750 [19.1mm]
LPV3-1000F-XXX	1.000 [25.4mm]
LPV3-1250F-XXX	1.250 [31.8mm]
LPV3-1500F-XXX	1.500 [38.1mm]
LPV3-1750F-XXX	1.750 [44.5mm]
LPV3-2000F-XXX	2.000 [50.8mm]

TABLE B - DOME FACE LENS	
PART NO.	H ± .01
LPV3-0350D-XXX	0.350 [8.9mm]
LPV3-0400D-XXX	0.400 [10.2mm]
LPV3-0450D-XXX	0.450 [11.4mm]
LPV3-0500D-XXX	0.500 [12.7mm]
LPV3-0550D-XXX	0.550 [14.0mm]
LPV3-0600D-XXX	0.600 [15.2mm]
LPV3-0750D-XXX	0.750 [19.1mm]
LPV3-1000D-XXX	1.000 [25.4mm]
LPV3-1250D-XXX	1.250 [31.8mm]
LPV3-1500D-XXX	1.500 [38.1mm]
LPV3-1750D-XXX	1.750 [44.5mm]
LPV3-2000D-XXX	2.000 [50.8mm]

CUSTOMER USE DRAWING

		BIVAR[®]	
CAGE CODE:	32559	DRAWING NO: LPV3-XXXXX-XXX	REVISION: D
SHEET SIZE:	A	SCALE: 2:1	SHEET # 2 OF 5
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING			



Order Code XXX	Emitted Color	Peak Wave L.	Electro-Optical Data @20mA, 25°C				Polarity Diagram
		λ_p [nm]	V_f [V]			I_v [mcd]	
		Chroma	MIN	TYP	MAX	TYP	
		TYP					
R130	Red	640	1.7	2.0	2.5	130	FIGURE A
R480	Red	630	1.7	2.0	2.5	480	FIGURE B
A220	Amber	610	1.7	2.0	2.5	220	
O170	Orange	590	1.7	2.0	2.5	170	
Y50	Yellow	570	1.7	2.0	2.5	50	
G850	Green	520	2.8	3.2	3.7	850	
B150	Blue	465	2.8	3.2	3.7	150	
W305	White	X = 0.308 Y = 0.305	2.8	3.0	3.7	1750	
OY	Orange	590	1.7	2.0	2.5	190	FIGURE C
	Yellow	572	1.7	2.0	2.5	60	
RY	Red	640	1.7	2.0	2.5	110	FIGURE D
	Yellow	572	1.7	2.0	2.5	55	
RG	Red	640	1.7	2.0	2.5	200	FIGURE E
	Green	520	2.8	3.2	3.7	810	
RW	Red	630	1.7	2.0	2.5	130	FIGURE F
	White	X = 0.28 Y = 0.29	2.8	3.2	3.7	520	
RB	Red	650	1.7	2.0	2.5	80	FIGURE G
	Blue	465	2.8	3.2	3.7	150	
RGB	Red	643	1.7	2.0	2.5	95	FIGURE H
	Green	515	2.8	3.3	3.7	730	
	Blue	460	2.8	3.3	3.7	120	

Note: 10% Duty Cycle, Pulse Width ≤ 0.1 msec for Peak If.





FIG. A




FIG. B




FIG. C




FIG. D




FIG. E




FIG. F




FIG. G




FIG. H

CUSTOMER USE DRAWING

			
CAGE CODE:	32559	DRAWING NO: LPV3-XXXXX-XXX	REVISION: D
SHEET SIZE:	A	SCALE: 2:1	SHEET # 3 OF 5
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING			

BIVAR

PACKAGING PLAN

PARTS ARE SHIPPED IN QUANTITY OF 400 AS IN THE FOLLOWING:

- 1. ONE BAG CONTAINING FOUR LIGHT PIPE PACKAGES, 100 EACH, AND ONE LEVEL 4 MOISTURE SEALED TRAY WITH 400 SURFACE MOUNT ADAPTERS.
- 2. BAG SIZE IS APPROXIMATLY 16 X 18 INCHES (406.4 X 457.2 mm).
- 3. TRAY SIZE IS APPROXIMATELY 10 X 14 X 0.6 INCHES (254 X 355.6 X 15.2 mm), INCLUDING TOP COVER AND BOTTOM TRAY. ADAPTERS ARE ARRANGED AS SHOWN IN FIGURE 1.

10 ADAPTERS IN EACH POCKET





FIGURE 1
BOTTOM TRAY
4 X 10 POCKETS

CUSTOMER USE DRAWING

		BIVAR [®]	
CAGE CODE:	32559	DRAWING NO: LPV3-XXXXX-XXX	
		REVISION: D	
SHEET SIZE:	A	SCALE: 4:1	SHEET # 4 OF 5
		CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING	

RECOMMENDED REFLOW SOLDERING PROFILE



CUSTOMER USE DRAWING

NOTE:

1. DO NOT CLEAN AFTER SOLDERING. ONLY USE NO-CLEAN SOLDER PASTE.

		BIVAR [®]	
CAGE CODE:	32559	DRAWING NO: LPV3-XXXXX-XXX	REVISION: D
SHEET SIZE:	A	SCALE: 2:1	SHEET # 5 OF 5
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[BIVAR:](#)

[LPV3-0350F-R480](#) [LPV3-0400D-R480](#) [LPV3-0400F-B150](#) [LPV3-0400F-O170](#) [LPV3-0400D-G850](#) [LPV3-0400F-R130](#) [LPV3-0450D-RG](#) [LPV3-0450F-W305](#) [LPV3-0500D-Y50](#) [LPV3-0500F-B150](#) [LPV3-0550D-B150](#) [LPV3-0550D-G850](#) [LPV3-0600D-RG](#) [LPV3-0750D-Y50](#) [LPV3-0750F-A220](#) [LPV3-0750F-B150](#) [LPV3-1000D-G850](#) [LPV3-1000D-OY](#) [LPV3-1000F-R480](#) [LPV3-0350D-B150](#) [LPV3-0400D-RB](#) [LPV3-0400D-RGB](#) [LPV3-0350D-RB](#) [LPV3-0350D-RG](#) [LPV3-0350F-RB](#) [LPV3-0400D-Y50](#) [LPV3-0450F-B150](#) [LPV3-0500D-OY](#) [LPV3-0500D-R130](#) [LPV3-0500D-RB](#) [LPV3-0500F-RB](#) [LPV3-0550D-RW](#) [LPV3-0350D-A220](#) [LPV3-0350D-O170](#) [LPV3-0350D-W305](#) [LPV3-0350F-R130](#) [LPV3-0350F-W305](#) [LPV3-0400F-A220](#) [LPV3-0400F-RY](#) [LPV3-0450F-RG](#) [LPV3-0500D-B150](#) [LPV3-0500D-RG](#) [LPV3-0500D-RW](#) [LPV3-0500F-O170](#) [LPV3-0550F-RGB](#) [LPV3-0600D-OY](#) [LPV3-0600D-Y50](#) [LPV3-0600F-R480](#) [LPV3-0600F-RG](#) [LPV3-0600F-Y50](#) [LPV3-0750D-B150](#) [LPV3-0750D-RG](#) [LPV3-0750F-O170](#) [LPV3-0750F-RW](#) [LPV3-1000F-A220](#) [LPV3-0350D-R480](#) [LPV3-0400D-RW](#) [LPV3-0400D-W305](#) [LPV3-0400F-Y50](#) [LPV3-0450D-B150](#) [LPV3-0450F-G850](#) [LPV3-0450F-O170](#) [LPV3-0450F-OY](#) [LPV3-0500D-R480](#) [LPV3-0500F-RG](#) [LPV3-0500F-RGB](#) [LPV3-0550D-Y50](#) [LPV3-0550F-W305](#) [LPV3-0600D-B150](#) [LPV3-0600F-G850](#) [LPV3-0600F-OY](#) [LPV3-0750D-OY](#) [LPV3-0750F-RB](#) [LPV3-0750F-RG](#) [LPV3-0350D-RY](#) [LPV3-0350F-OY](#) [LPV3-0400D-RG](#) [LPV3-0450D-O170](#) [LPV3-0350D-RW](#) [LPV3-0350F-O170](#) [LPV3-0400D-A220](#) [LPV3-0400F-G850](#) [LPV3-0400F-RGB](#) [LPV3-0450D-OY](#) [LPV3-0450D-R480](#) [LPV3-0450D-RY](#) [LPV3-0450F-R480](#) [LPV3-0500D-O170](#) [LPV3-0550D-R130](#) [LPV3-0550D-RB](#) [LPV3-0550F-A220](#) [LPV3-0550F-G850](#) [LPV3-0550F-RY](#) [LPV3-0600D-G850](#) [LPV3-0750D-O170](#) [LPV3-0750D-RW](#) [LPV3-0750F-W305](#) [LPV3-1000D-A220](#) [LPV3-1000D-R130](#) [LPV3-1000D-RB](#)