





REV.	DESCRIPTION	DATE	APPROVED
F	Engineering Update w/o Changes	03/01/04	M. C.




SDC SERIES



SSD SERIES



PART NO.			A ±.032 (.8)	B ±.016 (.4)
SDC-250	SSD-250	SSD-250-102	2.5 (63.5)	1.5 (38.1)
SDC-300	SSD-300	SSD-300-102	3.0 (76.2)	2.0 (50.8)
SDC-350	SSD-350	SSD-350-102	3.5 (88.9)	2.5 (63.5)
SDC-400	SSD-400	SSD-400-102	4.0 (101.6)	3.0 (76.2)
N/A	SSD-450 3X	N/A	4.5 (114.3)	3.0 (76.2)
SDC-450	SSD-450	SSD-450-102	4.5 (114.3)	3.5 (88.9)
SDC-500	SSD-500	SSD-500-102	5.0 (127.0)	4.0 (101.6)
SDC-550	SSD-550	SSD-550-102	5.5 (139.7)	4.5 (114.3)
SDC-600	SSD-600	SSD-600-102	6.0 (152.4)	5.0 (127.0)
SDC-650	SSD-650	SSD-650-102	6.5 (165.1)	5.5 (139.7)
SDC-700	SSD-700	SSD-700-102	7.0 (177.8)	6.0 (152.4)
SDC-750	SSD-750	SSD-750-102	7.5 (190.5)	6.5 (165.1)
SDC-800	SSD-800	SSD-800-102	8.0 (203.2)	7.0 (177.8)
SW=0.075 (1.9)		SW=0.102 (2.6)		



2. MATERIAL: NYLON 6/6, 94V-2, NATURAL. BIVAR MATERIAL CODE 03-NL.
BASF ULTRAMID NYLON 6/6 A3K NATURAL.
1. GENERAL SPECIFICATIONS: BIVAR MOLDED COMPONENT SPECIFICATION BV00-E101.

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°	 TITLE: INTERCHANGEABLE SNAP-IN CARD GUIDE	
.XX ± .01			
.XXX ± .005			
DESIGNED: David Green	DATE: 11/26/02	PART NO: SDC-XXX SSD-XXX-XXX	REVISION: F
CHECKED: M. Chen	DATE: 11/26/02	CAGE CODE : 32559 SHEET # 1 OF 1 CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[SDC-250](#) [SDC-300](#) [SDC-400](#) [SDC-450](#) [SDC-500](#) [SDC-600](#) [SDC-650](#) [SDC-700](#) [SDC-800](#) [SSD-800-102](#) [SSD-250](#) [SSD-600](#) [SDC-250 BK](#) [SDC-300 BK](#) [SDC-350](#) [SDC-450 BK](#) [SDC-450 VT](#) [SDC-550](#) [SDC-650 BK](#) [SDC-750](#) [SSD-250 BK](#) [SSD-300](#) [SSD-300 BK](#) [SSD-300-CI](#) [SSD-350](#) [SSD-350-CI](#) [SSD-400](#) [SSD-450](#) [SSD-450-CI](#) [SSD-550](#) [SSD-550 BK](#) [SSD-550-CI](#) [SSD-650](#) [SSD-750](#) [SSD-800](#) [SSD-800-CI](#) [SSD-500](#) [SSD-750-102](#) [SSD-600-102](#) [SSD-400-CI](#) [SSD-600-CI](#)