




REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	05/12/17	J. C.



*Length "X.X"	Tolerance
2.0" ~ 16.0"	±0.05"
16.1" ~ 40.0"	±0.15"
40.1" ~ 80.0"	±0.30"
80.1" ~ 500.0"	±0.5%



Part Number Configuration
SF2-6.5-F6PX67PR

Lens Options:
Z – Clear Fresnel
D – Diffused
Blank – Clear

Length in 0.1"
Increments Only



NOTES:

1. SEALED TO IP67 RATING
2. ROHS COMPLIANT
3. MOUNTING HARDWARE AND ADAPTER SHIPPED NON-ASSEMBLED
4. MINIMUM BEND RADIUS OF FLEXIBLE LIGHT PIPE: 0.87" [22mm]

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
<u>DECIMALS</u>	<u>ANGULAR</u>		
.X ± .1	X° ± 1°		
.XX ± .02			
.XXX ± .010			
DESIGNED: TD. Nguyen	DATE: 04/30/17	TITLE: IP67 RATED PANEL MOUNT FLP INDICATOR, SMFLP	
		PART NO: SF2-X.X-F6PX67PR	
		REVISION A	
CHECKED: K. Baron	DATE: 04/30/17	CAGE CODE : 32559	
		SHEET # 1 OF 1	
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[SF2-6.0-F6P67PR-2](#) [SF2-6.0-F6P67PR-4](#) [SF2-6.0-F6P67PR-5](#) [SF2-6.0-F6P67PR-6](#) [SF2-6.0-F6P67PR-9](#) [SF2-6.0-F6PD67PR-2](#) [SF2-6.0-F6PD67PR-4](#) [SF2-6.0-F6PD67PR-5](#) [SF2-6.0-F6PD67PR-6](#) [SF2-6.0-F6PD67PR-9](#) [SF2-6.0-F6PZ67PR-2](#) [SF2-6.0-F6PZ67PR-4](#) [SF2-6.0-F6PZ67PR-5](#) [SF2-6.0-F6PZ67PR-6](#) [SF2-6.0-F6PZ67PR-9](#)