


| REV. | DESCRIPTION         | DATE     | APPROVED |
|------|---------------------|----------|----------|
| A    | Engineering Release | 05/12/17 | J. C.    |
|      |                     |          |          |
|      |                     |          |          |
|      |                     |          |          |

| *Length "X.X"  | Tolerance |
|----------------|-----------|
| 2.0" ~ 16.0"   | ±0.05"    |
| 16.1" ~ 40.0"  | ±0.15"    |
| 40.1" ~ 80.0"  | ±0.30"    |
| 80.1" ~ 500.0" | ±0.5%     |



Part Number Configuration  
SF3-6.5-F9PX67PR

Lens Options:  
Z – Clear Fresnel  
D – Diffused  
Blank – Clear

Length in 0.1"  
Increments Only

#### NOTES:

1. SEALED TO IP67 RATING
2. ROHS COMPLIANT
3. MOUNTING HARDWARE AND ADAPTER SHIPPED NON-ASSEMBLED
4. MINIMUM BEND RADIUS OF FLEXIBLE LIGHT PIPE: 1.06" [27mm]

|                                                    |                          |                                                                                                                                                                 |  |
|----------------------------------------------------|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| STANDARD TOLERANCE<br>(UNLESS OTHERWISE SPECIFIED) |                          | <br>4 THOMAS, IRVINE, CA. 92618<br>TEL: (949) 951-8808 FAX: (949) 951-3974 |  |
| DECIMALS                                           | ANGULAR                  |                                                                                                                                                                 |  |
| .X ± .1                                            | X° ± 1°                  |  <b>TITLE:</b> IP67 RATED PANEL MOUNT<br>FLP INDICATOR, SMFLP              |  |
| .XX ± .02                                          |                          |                                                                                                                                                                 |  |
| .XXX ± .010                                        |                          | <b>PART NO:</b> SF3-X.X-F9PX67PR                                                                                                                                |  |
| DESIGNED:<br><b>TD. Nguyen</b>                     | DATE:<br><b>04/30/17</b> | <b>CAGE CODE :</b> 32559 <b>SHEET # 1 OF 1</b>                                                                                                                  |  |
| CHECKED:<br><b>K. Baron</b>                        | DATE:<br><b>04/30/17</b> | CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.                                                                                                                 |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## BIVAR:

[SF3-6.0-F9P67PR-2](#) [SF3-6.0-F9P67PR-4](#) [SF3-6.0-F9P67PR-5](#) [SF3-6.0-F9P67PR-6](#) [SF3-6.0-F9P67PR-9](#) [SF3-6.0-F9PD67PR-2](#) [SF3-6.0-F9PD67PR-4](#) [SF3-6.0-F9PD67PR-5](#) [SF3-6.0-F9PD67PR-6](#) [SF3-6.0-F9PD67PR-9](#) [SF3-6.0-F9PZ67PR-2](#) [SF3-6.0-F9PZ67PR-4](#) [SF3-6.0-F9PZ67PR-5](#) [SF3-6.0-F9PZ67PR-6](#) [SF3-6.0-F9PZ67PR-9](#) [SF3-20.0-F9PD67PR](#)