


NOTES:





1. ALLOWABLE FLEXIBLE LIGHT PIPE CUT LENGTH AVAILABLE IN INCREMENTS OF 0.05".
2. MINIMUM BEND RADIUS OF FLEXIBLE LIGHT PIPE: 1.22" [31mm].
3. COMPONENTS SHIPPED NON-ASSEMBLED.
4. SEE SHEET 2 FOR DETAILED ASSEMBLY INSTRUCTIONS TO ACHIEVE OPTIMUM FUNCTION OF SPLASH GUARD

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	08/21/2019	A.V.




PART NUMBER CONFIGURATOR

SEE SHEET 2 FOR ORDERING INFORMATION



CUSTOMER USE DRAWING



STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°	TITLE: FLP ASSEMBLY WITH FIRM RETENTION ADAPTER, LC2	
.XX ± .02			
.XXX ± .010		DRAWING NO: SZ4-X.XX-F5PX-X	REVISION: A
DESIGNED: K. BARON	DATE: 08/21/19	SHEET SIZE: A	CAGE CODE: 32559
REVISED: N/A	DATE: N/A	SCALE: 2:1	SHEET # 1 OF 2
CHECKED: A. VALDEZ	DATE: 08/21/19	CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING	

TABLE 1 - LENGTH	
LENGTH (L)*	TOLERANCE
1.00" - 16.00"	±0.05"
16.05" - 40.00"	±0.15"
40.05" - 80.00"	±0.30"
80.05" - 3,940.00"	±0.5%

*AVAILABLE IN 0.05" INCREMENTS

TABLE 2 - LENS	
ORDER CODE	LENS APPEARANCE
(BLANK)	CLEAR
D	DIFFUSED
S	SMOKED
BE	TINTED BLUE
GN	TINTED GREEN
RD	TINTED RED
YW	TINTED YELLOW

TABLE 3 - CABLE	
ORDER CODE	CABLE COLOR
(BLANK)	BLACK
2	RED
4	YELLOW
5	GREEN
6	BLUE
9	WHITE

SAMPLE PART NUMBER:

SZ4-11.20-F5PD54-5

11.20" LENGTH ———

DIFFUSED LENS ———

GREEN CABLE

IP54 RATED SPLASH
GUARD INCLUDED

ASSEMBLY INSTRUCTIONS TO ACHIEVE OPTIMUM FUNCTION OF SPLASH GUARD:

- CLEAN PANEL SURFACE AROUND MOUNTING HOLE WITH ALCOHOL
- PEEL LINER OFF TOP OF THE SPLASH GUARD WHILE KEEPING SPLASH GUARD ON PLASTIC ROLL
- APPLY SPLASH GUARD TO PANEL HOLE AS CENTERED AS POSSIBLE AND PEEL PLASTIC LINER SLOWLY AWAY
- INSERT LIGHT PIPE INTO PANEL UNTIL SPLASH GUARD MATERIAL IS COMPRESSED BETWEEN LENS AND PANEL
- HOLD FOR A FEW SECONDS TO ENSURE ENTIRE SPLASH GUARD ADHERES TO PANEL AND LENS FLANGE SURFACE

CUSTOMER USE DRAWING

		BIVAR [®]	
CAGE CODE:	32559	DRAWING NO: SZ4-X.XX-F5PX-X	
		REVISION: A	
SHEET SIZE:	A	SCALE: 2:1	SHEET # 2 OF 2
		CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[SZ4-10.00-F5P](#) [SZ4-10.00-F5P-2](#) [SZ4-10.00-F5P-4](#) [SZ4-10.00-F5P-5](#) [SZ4-10.00-F5P54](#) [SZ4-10.00-F5P54-2](#) [SZ4-6.00-F5P](#) [SZ4-6.00-F5P-2](#) [SZ4-6.00-F5P-4](#) [SZ4-6.00-F5P-5](#) [SZ4-6.00-F5P54](#) [SZ4-6.00-F5P54-2](#) [SZ4-6.00-F5PRD54-6](#) [SZ4-6.00-F5PRD54-9](#) [SZ4-6.00-F5PRD-6](#) [SZ4-6.00-F5PRD-9](#) [SZ4-6.00-F5PS](#) [SZ4-6.00-F5PS-2](#) [SZ4-6.00-F5PRD-4](#) [SZ4-6.00-F5PRD-5](#) [SZ4-6.00-F5PRD54](#) [SZ4-6.00-F5PRD54-2](#) [SZ4-6.00-F5PRD54-4](#) [SZ4-6.00-F5PRD54-5](#) [SZ4-6.00-F5PYW54-9](#) [SZ4-6.00-F5PYW-6](#) [SZ4-6.00-F5PYW-9](#) [SZ4-6.00-F5PGN-9](#) [SZ4-6.00-F5PRD](#) [SZ4-6.00-F5PRD-2](#) [SZ4-6.00-F5PYW-5](#) [SZ4-6.00-F5PYW54](#) [SZ4-6.00-F5PYW54-2](#) [SZ4-6.00-F5PYW54-4](#) [SZ4-6.00-F5PYW54-5](#) [SZ4-6.00-F5PYW54-6](#) [SZ4-6.00-F5PS54-9](#) [SZ4-6.00-F5PS-6](#) [SZ4-6.00-F5PS-9](#) [SZ4-6.00-F5PYW](#) [SZ4-6.00-F5PYW-2](#) [SZ4-6.00-F5PYW-4](#) [SZ4-6.00-F5PS-5](#) [SZ4-6.00-F5PS54](#) [SZ4-6.00-F5PS54-2](#) [SZ4-6.00-F5PS54-4](#) [SZ4-6.00-F5PS54-5](#) [SZ4-6.00-F5PS54-6](#) [SZ4-6.00-F5PD54-2](#) [SZ4-6.00-F5PD54-4](#) [SZ4-6.00-F5PD54-5](#) [SZ4-6.00-F5PD54-6](#) [SZ4-6.00-F5PD54-9](#) [SZ4-6.00-F5PS-4](#) [SZ4-6.00-F5PBE-9](#) [SZ4-6.00-F5PD](#) [SZ4-6.00-F5PD-2](#) [SZ4-6.00-F5PD-4](#) [SZ4-6.00-F5PD-5](#) [SZ4-6.00-F5PD54](#) [SZ4-6.00-F5PBE54-2](#) [SZ4-6.00-F5PBE54-4](#) [SZ4-6.00-F5PBE54-5](#) [SZ4-6.00-F5PBE54-6](#) [SZ4-6.00-F5PBE54-9](#) [SZ4-6.00-F5PBE-6](#) [SZ4-6.00-F5P-9](#) [SZ4-6.00-F5PBE](#) [SZ4-6.00-F5PBE-2](#) [SZ4-6.00-F5PBE-4](#) [SZ4-6.00-F5PBE-5](#) [SZ4-6.00-F5PBE54](#) [SZ4-6.00-F5PGN54-6](#) [SZ4-6.00-F5PGN54-9](#) [SZ4-6.00-F5PGN-6](#) [SZ4-6.00-F5P54-6](#) [SZ4-6.00-F5P54-9](#) [SZ4-6.00-F5P-6](#) [SZ4-6.00-F5PGN-4](#) [SZ4-6.00-F5PGN-5](#) [SZ4-6.00-F5PGN54](#) [SZ4-6.00-F5PGN54-2](#) [SZ4-6.00-F5PGN54-4](#) [SZ4-6.00-F5PGN54-5](#) [SZ4-6.00-F5P54-4](#) [SZ4-6.00-F5P54-5](#) [SZ4-6.00-F5PD-6](#) [SZ4-6.00-F5PD-9](#) [SZ4-6.00-F5PGN](#) [SZ4-6.00-F5PGN-2](#) [SZ4-10.00-F5PD](#) [SZ4-10.00-F5PD-2](#) [SZ4-10.00-F5PD-4](#) [SZ4-10.00-F5PD-5](#) [SZ4-10.00-F5PD54](#) [SZ4-10.00-F5PD54-2](#) [SZ4-10.00-F5PBE54-4](#) [SZ4-10.00-F5PBE54-5](#) [SZ4-10.00-F5PBE54-6](#) [SZ4-10.00-F5PBE54-9](#)