




NOTES:

1. ALLOWABLE FLEXIBLE LIGHT PIPE CUT LENGTH AVAILABLE IN INCREMENTS OF 0.05".
2. MINIMUM BEND RADIUS OF FLEXIBLE LIGHT PIPE: 1.22" [31mm].
3. COMPONENTS SHIPPED NON-ASSEMBLED.
4. SEE SHEET 2 FOR DETAILED ASSEMBLY INSTRUCTIONS TO ACHIEVE OPTIMUM FUNCTION OF SEALING GASKET



PART NUMBER CONFIGURATOR
SEE SHEET 2 FOR ORDERING INFORMATION

Part Number: SZR4-X.XX-F5PX-X

LENGTH (L) (SEE TABLE 1): XX
LENS COLOR (SEE TABLE 2): F5
CABLE COLOR (SEE TABLE 3): X
IP RATING: 54

IP OPTION	CODE
NONE	(BLANK)
IP54	54

CUSTOMER USE DRAWING

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		BIVAR® 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°	TITLE: FLP ASSEMBLY WITH LOW PROFILE ADAPTER, LC2	
.XX ± .02		DRAWING NO: SZR4-X.XX-F5PX-X	REVISION: A
.XXX ± .010		SHEET SIZE: A	CAGE CODE: 32559
DESIGNED: K. BARON	DATE: 3/1/2022	SCALE: 2:1	SHEET # 1 OF 2
REVIS: N/A	DATE: N/A	CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING	
CHECKED: A. VALDEZ	DATE: 3/1/2022		





TABLE 1 - LENGTH	
LENGTH (L)*	TOLERANCE
1.00" - 16.00"	±0.05"
16.05" - 40.00"	±0.15"
40.05" - 80.00"	±0.30"
80.05" - 3,940.00"	±0.5%

*AVAILABLE IN 0.05" INCREMENTS

TABLE 2 - LENS	
ORDER CODE	LENS APPEARANCE
(BLANK)	CLEAR
D	DIFFUSED
S	SMOKED
BE	TINTED BLUE
GN	TINTED GREEN
RD	TINTED RED
YW	TINTED YELLOW

TABLE 3 - CABLE	
ORDER CODE	CABLE COLOR
(BLANK)	BLACK
2	RED
4	YELLOW
5	GREEN
6	BLUE
9	WHITE

SAMPLE PART NUMBER:

SZR4-11.20-F5PD54-5



ASSEMBLY INSTRUCTIONS TO ACHIEVE OPTIMUM FUNCTION OF SEALING GASKET:

- CLEAN PANEL SURFACE AROUND MOUNTING HOLE WITH ALCOHOL
- PEEL LINER OFF TOP OF THE SEALING GASKET WHILE KEEPING SEALING GASKET ON PLASTIC ROLL
- APPLY SEALING GASKET TO PANEL HOLE AS CENTERED AS POSSIBLE AND PEEL PLASTIC LINER SLOWLY AWAY
- INSERT LIGHT PIPE INTO PANEL UNTIL SEALING GASKET MATERIAL IS COMPRESSED BETWEEN LENS AND PANEL
- HOLD FOR A FEW SECONDS TO ENSURE ENTIRE SEALING GASKET ADHERES TO PANEL AND LENS FLANGE SURFACE

CUSTOMER USE DRAWING

		BIVAR[®]	
CAGE CODE:	32559	DRAWING NO: SZR4-X.XX-F5PX-X	
		REVISION: A	
SHEET SIZE:	A	SCALE: 2:1	SHEET # 2 OF 2
		CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[SZR4-10.00-F5PBE54-4](#) [SZR4-10.00-F5PGN54-2](#) [SZR4-10.00-F5PYW-5](#) [SZR4-10.00-F5PYW54-2](#) [SZR4-6.00-F5P](#)
[SZR4-6.00-F5PD-5](#) [SZR4-6.00-F5PD-6](#) [SZR4-6.00-F5PRD54-9](#) [SZR4-10.00-F5P54-5](#) [SZR4-10.00-F5P54-9](#) [SZR4-](#)
[10.00-F5PBE54](#) [SZR4-10.00-F5PGN54-5](#) [SZR4-10.00-F5PRD-4](#) [SZR4-10.00-F5PRD54](#) [SZR4-6.00-F5P-4](#) [SZR4-](#)
[6.00-F5PD-2](#) [SZR4-6.00-F5PD54-6](#) [SZR4-6.00-F5PRD-9](#) [SZR4-6.00-F5PS54-4](#) [SZR4-6.00-F5PS54-6](#) [SZR4-10.00-](#)
[F5PBE-5](#) [SZR4-10.00-F5PD54-2](#) [SZR4-10.00-F5PD54-4](#) [SZR4-10.00-F5PS54-2](#) [SZR4-10.00-F5PYW54-5](#) [SZR4-](#)
[10.00-F5PYW54-6](#) [SZR4-6.00-F5PD54-5](#) [SZR4-6.00-F5PGN54-9](#) [SZR4-6.00-F5PGN-6](#) [SZR4-6.00-F5PYW54-9](#)
[SZR4-10.00-F5PBE-4](#) [SZR4-10.00-F5PD54](#) [SZR4-10.00-F5PD54-5](#) [SZR4-10.00-F5PGN54-9](#) [SZR4-10.00-F5PYW54-](#)
[4](#) [SZR4-10.00-F5PYW-6](#) [SZR4-6.00-F5P-9](#) [SZR4-6.00-F5PBE](#) [SZR4-6.00-F5PD54-2](#) [SZR4-6.00-F5PS-4](#) [SZR4-](#)
[6.00-F5PYW54-5](#) [SZR4-6.00-F5PYW54-6](#) [SZR4-10.00-F5P-4](#) [SZR4-10.00-F5PD-5](#) [SZR4-10.00-F5PD54-6](#) [SZR4-](#)
[10.00-F5PGN](#) [SZR4-10.00-F5PRD54-9](#) [SZR4-10.00-F5PS-2](#) [SZR4-10.00-F5PS54-4](#) [SZR4-6.00-F5P54-5](#) [SZR4-](#)
[6.00-F5PBE54](#) [SZR4-6.00-F5PGN54-2](#) [SZR4-6.00-F5PRD-4](#) [SZR4-6.00-F5PYW-5](#) [SZR4-10.00-F5PBE-6](#) [SZR4-](#)
[10.00-F5PGN-2](#) [SZR4-10.00-F5PS-9](#) [SZR4-10.00-F5PYW-2](#) [SZR4-6.00-F5P54](#) [SZR4-6.00-F5PBE-9](#) [SZR4-6.00-](#)
[F5PGN-4](#) [SZR4-6.00-F5PRD54-2](#) [SZR4-10.00-F5P54](#) [SZR4-10.00-F5PBE54-9](#) [SZR4-10.00-F5PGN-4](#) [SZR4-10.00-](#)
[F5PRD54-5](#) [SZR4-10.00-F5PYW](#) [SZR4-6.00-F5P54-2](#) [SZR4-6.00-F5PBE-6](#) [SZR4-6.00-F5PGN-5](#) [SZR4-6.00-](#)
[F5PRD54-6](#) [SZR4-6.00-F5PYW-2](#) [SZR4-10.00-F5PBE54-5](#) [SZR4-10.00-F5PD-4](#) [SZR4-10.00-F5PD54-9](#) [SZR4-](#)
[10.00-F5PS54-9](#) [SZR4-10.00-F5PYW54](#) [SZR4-10.00-F5PYW-9](#) [SZR4-6.00-F5PD-9](#) [SZR4-6.00-F5PGN54-4](#) [SZR4-](#)
[6.00-F5PRD-2](#) [SZR4-10.00-F5P-2](#) [SZR4-10.00-F5P54-6](#) [SZR4-10.00-F5PGN54-6](#) [SZR4-10.00-F5PRD-5](#) [SZR4-](#)
[10.00-F5PRD-6](#) [SZR4-6.00-F5P-6](#) [SZR4-6.00-F5PBE54-2](#) [SZR4-6.00-F5PD](#) [SZR4-6.00-F5PS](#) [SZR4-6.00-F5PS54-5](#)
[SZR4-6.00-F5PYW-4](#) [SZR4-10.00-F5PBE-2](#) [SZR4-10.00-F5PGN-6](#) [SZR4-10.00-F5PS-5](#) [SZR4-10.00-F5PS54](#)
[SZR4-10.00-F5PYW54-9](#) [SZR4-6.00-F5PD54-4](#) [SZR4-6.00-F5PGN54-6](#) [SZR4-6.00-F5PGN-9](#)