


[Home](#) / [Products](#) / [Component Mounts & Spacers](#) / [Wash Away Spacers](#) / [Round Wash-Away Component Spacers](#)

Component Mounts & Spacers

[Component Mounts](#)
[Spacers](#)
[Wash Away Spacers](#)
[Crystal Insulators](#)

Card Guides & Ejectors

[Card Guides](#)
[PCB Ejectors](#)

Product Info Center

Round Wash-Away Component Spacers



The Popular Diss-O-Pad Spacer series of Wash-Away Spacers provide for accurate positioning of through-hole electronic components on PCBs then dissolve in hot or warm running water without a trace of residue. Circular water soluble spacers provide a problem solving approach to control production uniformity through the soldering process while eliminating scrap and rejects due to improper component placement or contaminant entrapment. Manufactured from organic materials, Wash-Away Spacers are an ecological solution to improved production yield with over 200 styles available from stock.

PART NUMBER	DESCRIPTION
TO-10-040	Diss-O-Pad, TO-10, Round, 0.085 OD, 0.04, ID, 0.04 Thick, Wax
TO-10-050	Diss-O-Pad, TO-10, Round, 0.085 OD, 0.04, ID, 0.05 Thick, Wax
TO-10-060	Diss-O-Pad, TO-10, Round, 0.085 OD, 0.04, ID, 0.06 Thick, Wax
TO-10-070	Diss-O-Pad, TO-10, Round, 0.085 OD, 0.04, ID, 0.07 Thick, Wax
TO-10-080	Diss-O-Pad, TO-10, Round, 0.085 OD, 0.04, ID, 0.08 Thick, Wax
TO-10-090	Diss-O-Pad, TO-10, Round, 0.085 OD, 0.04, ID, 0.09 Thick, Wax
TO-10-100	Diss-O-Pad, TO-10, Round, 0.085 OD, 0.04, ID, 0.10 Thick, Wax
TO-11-040	Diss-O-Pad, TO-11, Round, 0.1 OD, 0.045, ID, 0.04 Thick, Wax
TO-11-050	Diss-O-Pad, TO-11, Round, 0.1 OD, 0.045, ID, 0.05 Thick, Wax
TO-11-060	Diss-O-Pad, TO-11, Round, 0.1 OD, 0.045, ID, 0.06 Thick, Wax
TO-11-070	Diss-O-Pad, TO-11, Round, 0.1 OD, 0.045, ID, 0.07 Thick, Wax
TO-11-080	Diss-O-Pad, TO-11, Round, 0.1 OD, 0.045, ID, 0.08 Thick, Wax
TO-11-100	Diss-O-Pad, TO-11, Round, 0.1 OD, 0.045, ID, 0.10 Thick, Wax
TO-11-110	Diss-O-Pad, TO-11, Round, 0.1 OD, 0.045, ID, 0.11 Thick, Wax

Round Wash-Away Component Spacers

<u>TO-11-120</u>	Diss-O-Pad, TO-11, Round, 0.1 OD, 0.045, ID, 0.12 Thick, Wax
<u>TO-12-080</u>	Diss-O-Pad, TO-12, Round, w/Cavity, 0.31 OD, 0.125, ID, 0.08 Thick, Wax
<u>TO-12-090</u>	Diss-O-Pad, TO-12, Round, w/Cavity, 0.31 OD, 0.125, ID, 0.09 Thick, Wax
<u>TO-12-100</u>	Diss-O-Pad, TO-12, Round, w/Cavity, 0.31 OD, 0.125, ID, 0.10 Thick, Wax
<u>TO-12-120</u>	Diss-O-Pad, TO-12, Round, w/Cavity, 0.31 OD, 0.125, ID, 0.12 Thick, Wax
<u>TO-12-130</u>	Diss-O-Pad, TO-12, Round, w/Cavity, 0.31 OD, 0.125, ID, 0.13 Thick, Wax
<u>TO-12-180</u>	Diss-O-Pad, TO-12, Round, w/Cavity, 0.31 OD, 0.125, ID, 0.18 Thick, Wax
<u>TO-13-040</u>	Diss-O-Pad, TO-13, Round, 0.225 OD, 0.225, ID, 0.04 Thick, Wax
<u>TO-13-050</u>	Diss-O-Pad, TO-13, Round, 0.225 OD, 0.225, ID, 0.05 Thick, Wax
<u>TO-13-060</u>	Diss-O-Pad, TO-13, Round, 0.225 OD, 0.225, ID, 0.06 Thick, Wax
<u>TO-13-070</u>	Diss-O-Pad, TO-13, Round, 0.225 OD, 0.225, ID, 0.07 Thick, Wax
<u>TO-13-080</u>	Diss-O-Pad, TO-13, Round, 0.225 OD, 0.225, ID, 0.08 Thick, Wax
<u>TO-13-090</u>	Diss-O-Pad, TO-13, Round, 0.225 OD, 0.225, ID, 0.09 Thick, Wax
<u>TO-13-100</u>	Diss-O-Pad, TO-13, Round, 0.225 OD, 0.225, ID, 0.10 Thick, Wax
<u>TO-13-120</u>	Diss-O-Pad, TO-13, Round, 0.225 OD, 0.225, ID, 0.12 Thick, Wax
<u>TO-13-130</u>	Diss-O-Pad, TO-13, Round, 0.225 OD, 0.225, ID, 0.13 Thick, Wax
<u>TO-16-040</u>	Diss-O-Pad, TO-16, Round, 0.205 OD, 0.125, ID, 0.04 Thick, Wax
<u>TO-16-050</u>	Diss-O-Pad, TO-16, Round, 0.205 OD, 0.125, ID, 0.05 Thick, Wax
<u>TO-16-060</u>	Diss-O-Pad, TO-16, Round, 0.205 OD, 0.125, ID, 0.06 Thick, Wax
<u>TO-16-070</u>	Diss-O-Pad, TO-16, Round, 0.205 OD, 0.125, ID, 0.07 Thick, Wax
<u>TO-16-080</u>	Diss-O-Pad, TO-16, Round, 0.205 OD, 0.125, ID, 0.08 Thick, Wax
<u>TO-16-090</u>	Diss-O-Pad, TO-16, Round, 0.205 OD, 0.125, ID, 0.09 Thick, Wax
<u>TO-16-100</u>	Diss-O-Pad, TO-16, Round, 0.205 OD, 0.125, ID, 0.10 Thick, Wax
<u>TO-16-120</u>	Diss-O-Pad, TO-16, Round, 0.205 OD, 0.125, ID, 0.12 Thick, Wax
<u>TO-16-130</u>	Diss-O-Pad, TO-16, Round, 0.205 OD, 0.125, ID, 0.13 Thick, Wax
<u>TO-16-150</u>	Diss-O-Pad, TO-16, Round, 0.205 OD, 0.125, ID, 0.15 Thick, Wax
<u>TO-16-200</u>	Diss-O-Pad, TO-16, Round, 0.205 OD, 0.125, ID, 0.20 Thick, Wax
<u>TO-17-040</u>	Diss-O-Pad, TO-17, Round, 0.25 OD, 0.17, ID, 0.04 Thick, Wax
<u>TO-17-050</u>	Diss-O-Pad, TO-17, Round, 0.25 OD, 0.17, ID, 0.05 Thick, Wax
<u>TO-17-060</u>	Diss-O-Pad, TO-17, Round, 0.25 OD, 0.17, ID, 0.06 Thick, Wax

Round Wash-Away Component Spacers

<u>TO-17-070</u>	Diss-O-Pad, TO-17, Round, 0.25 OD, 0.17, ID, 0.07 Thick, Wax
<u>TO-17-090</u>	Diss-O-Pad, TO-17, Round, 0.25 OD, 0.17, ID, 0.09 Thick, Wax
<u>TO-17-100</u>	Diss-O-Pad, TO-17, Round, 0.25 OD, 0.17, ID, 0.10 Thick, Wax
<u>TO-17-120</u>	Diss-O-Pad, TO-17, Round, 0.25 OD, 0.17, ID, 0.12 Thick, Wax
<u>TO-17-130</u>	Diss-O-Pad, TO-17, Round, 0.25 OD, 0.17, ID, 0.13 Thick, Wax
<u>TO-17-140</u>	Diss-O-Pad, TO-17, Round, 0.25 OD, 0.17, ID, 0.14 Thick, Wax
<u>TO-17-150</u>	Diss-O-Pad, TO-17, Round, 0.25 OD, 0.17, ID, 0.15 Thick, Wax
<u>TO-17-170</u>	Diss-O-Pad, TO-17, Round, 0.25 OD, 0.17, ID, 0.17 Thick, Wax
<u>TO-17-180</u>	Diss-O-Pad, TO-17, Round, 0.25 OD, 0.17, ID, 0.18 Thick, Wax
<u>TO-17-200</u>	Diss-O-Pad, TO-17, Round, 0.25 OD, 0.17, ID, 0.20 Thick, Wax
<u>TO-18-040</u>	Diss-O-Pad, TO-18, Round, 0.25 OD, 0.125, ID, 0.04 Thick, Wax
<u>TO-18-050</u>	Diss-O-Pad, TO-18, Round, 0.25 OD, 0.125, ID, 0.05 Thick, Wax
<u>TO-18-060</u>	Diss-O-Pad, TO-18, Round, 0.25 OD, 0.125, ID, 0.06 Thick, Wax
<u>TO-18-070</u>	Diss-O-Pad, TO-18, Round, 0.25 OD, 0.125, ID, 0.07 Thick, Wax
<u>TO-18-080</u>	Diss-O-Pad, TO-18, Round, 0.25 OD, 0.125, ID, 0.08 Thick, Wax
<u>TO-18-090</u>	Diss-O-Pad, TO-18, Round, 0.25 OD, 0.125, ID, 0.09 Thick, Wax
<u>TO-18-100</u>	Diss-O-Pad, TO-18, Round, 0.25 OD, 0.125, ID, 0.10 Thick, Wax
<u>TO-18-120</u>	Diss-O-Pad, TO-18, Round, 0.25 OD, 0.125, ID, 0.12 Thick, Wax
<u>TO-18-130</u>	Diss-O-Pad, TO-18, Round, 0.25 OD, 0.125, ID, 0.13 Thick, Wax
<u>TO-18-150</u>	Diss-O-Pad, TO-18, Round, 0.25 OD, 0.125, ID, 0.15 Thick, Wax
<u>TO-18-170</u>	Diss-O-Pad, TO-18, Round, 0.25 OD, 0.125, ID, 0.17 Thick, Wax
<u>TO-18-190</u>	Diss-O-Pad, TO-18, Round, 0.25 OD, 0.125, ID, 0.19 Thick, Wax
<u>TO-18-200</u>	Diss-O-Pad, TO-18, Round, 0.25 OD, 0.125, ID, 0.20 Thick, Wax
<u>TO-18-250</u>	Diss-O-Pad, TO-18, Round, 0.25 OD, 0.125, ID, 0.25 Thick, Wax
<u>TO-19-040</u>	Diss-O-Pad, TO-19, Round, 0.48 OD, 0.25, ID, 0.04 Thick, Wax
<u>TO-19-050</u>	Diss-O-Pad, TO-19, Round, 0.48 OD, 0.25, ID, 0.05 Thick, Wax
<u>TO-19-060</u>	Diss-O-Pad, TO-19, Round, 0.48 OD, 0.25, ID, 0.06 Thick, Wax
<u>TO-19-070</u>	Diss-O-Pad, TO-19, Round, 0.48 OD, 0.25, ID, 0.07 Thick, Wax
<u>TO-19-090</u>	Diss-O-Pad, TO-19, Round, 0.48 OD, 0.25, ID, 0.09 Thick, Wax
<u>TO-19-100</u>	Diss-O-Pad, TO-19, Round, 0.48 OD, 0.25, ID, 0.10 Thick, Wax

Round Wash-Away Component Spacers

<u>TO-19-120</u>	Diss-O-Pad, TO-19, Round, 0.48 OD, 0.25, ID, 0.12 Thick, Wax
<u>TO-19-130</u>	Diss-O-Pad, TO-19, Round, 0.48 OD, 0.25, ID, 0.13 Thick, Wax
<u>TO-19-150</u>	Diss-O-Pad, TO-19, Round, 0.48 OD, 0.25, ID, 0.15 Thick, Wax
<u>TO-19-190</u>	Diss-O-Pad, TO-19, Round, 0.48 OD, 0.25, ID, 0.19 Thick, Wax
<u>TO-19-200</u>	Diss-O-Pad, TO-19, Round, 0.48 OD, 0.25, ID, 0.20 Thick, Wax
<u>TO-19-230</u>	Diss-O-Pad, TO-19, Round, 0.48 OD, 0.25, ID, 0.23 Thick, Wax
<u>TO-19-250</u>	Diss-O-Pad, TO-19, Round, 0.48 OD, 0.25, ID, 0.25 Thick, Wax
<u>TO-20-090</u>	Diss-O-Pad, TO-20, Round, w/Cavity, 0.29 OD, 0.125, ID, 0.09 Thick, Wax
<u>TO-20-100</u>	Diss-O-Pad, TO-20, Round, w/Cavity, 0.29 OD, 0.125, ID, 0.10 Thick, Wax
<u>TO-20-120</u>	Diss-O-Pad, TO-20, Round, w/Cavity, 0.29 OD, 0.125, ID, 0.12 Thick, Wax
<u>TO-20-130</u>	Diss-O-Pad, TO-20, Round, w/Cavity, 0.29 OD, 0.125, ID, 0.13 Thick, Wax
<u>TO-20-150</u>	Diss-O-Pad, TO-20, Round, w/Cavity, 0.29 OD, 0.125, ID, 0.15 Thick, Wax
<u>TO-21-050</u>	Diss-O-Pad, TO-21, Round, Grooved, 0.25 OD, 0.125, ID, 0.05 Thick, Wax
<u>TO-21-070</u>	Diss-O-Pad, TO-21, Round, Grooved, 0.25 OD, 0.125, ID, 0.07 Thick, Wax
<u>TO-21-080</u>	Diss-O-Pad, TO-21, Round, Grooved, 0.25 OD, 0.125, ID, 0.08 Thick, Wax
<u>TO-21-090</u>	Diss-O-Pad, TO-21, Round, Grooved, 0.25 OD, 0.125, ID, 0.09 Thick, Wax
<u>TO-21-100</u>	Diss-O-Pad, TO-21, Round, Grooved, 0.25 OD, 0.125, ID, 0.10 Thick, Wax
<u>TO-21-120</u>	Diss-O-Pad, TO-21, Round, Grooved, 0.25 OD, 0.125, ID, 0.12 Thick, Wax
<u>TO-21-130</u>	Diss-O-Pad, TO-21, Round, Grooved, 0.25 OD, 0.125, ID, 0.13 Thick, Wax
<u>TO-21-150</u>	Diss-O-Pad, TO-21, Round, Grooved, 0.25 OD, 0.125, ID, 0.15 Thick, Wax
<u>TO-21-170</u>	Diss-O-Pad, TO-21, Round, Grooved, 0.25 OD, 0.125, ID, 0.17 Thick, Wax
<u>TO-21-200</u>	Diss-O-Pad, TO-21, Round, Grooved, 0.25 OD, 0.125, ID, 0.20 Thick, Wax
<u>TO-22-040</u>	Diss-O-Pad, TO-22, Round, 0.437 OD, 0.225, ID, 0.04 Thick, Wax
<u>TO-22-050</u>	Diss-O-Pad, TO-22, Round, 0.437 OD, 0.225, ID, 0.05 Thick, Wax
<u>TO-22-060</u>	Diss-O-Pad, TO-22, Round, 0.437 OD, 0.225, ID, 0.06 Thick, Wax
<u>TO-22-070</u>	Diss-O-Pad, TO-22, Round, 0.437 OD, 0.225, ID, 0.07 Thick, Wax
<u>TO-22-080</u>	Diss-O-Pad, TO-22, Round, 0.437 OD, 0.225, ID, 0.08 Thick, Wax
<u>TO-22-090</u>	Diss-O-Pad, TO-22, Round, 0.437 OD, 0.225, ID, 0.09 Thick, Wax
<u>TO-22-100</u>	Diss-O-Pad, TO-22, Round, 0.437 OD, 0.225, ID, 0.10 Thick, Wax
<u>TO-22-110</u>	Diss-O-Pad, TO-22, Round, 0.437 OD, 0.225, ID, 0.11 Thick, Wax

Round Wash-Away Component Spacers

<u>TO-22-120</u>	Diss-O-Pad, TO-22, Round, 0.437 OD, 0.225, ID, 0.12 Thick, Wax
<u>TO-22-130</u>	Diss-O-Pad, TO-22, Round, 0.437 OD, 0.225, ID, 0.13 Thick, Wax
<u>TO-22-150</u>	Diss-O-Pad, TO-22, Round, 0.437 OD, 0.225, ID, 0.15 Thick, Wax
<u>TO-22-190</u>	Diss-O-Pad, TO-22, Round, 0.437 OD, 0.225, ID, 0.19 Thick, Wax
<u>TO-22-200</u>	Diss-O-Pad, TO-22, Round, 0.437 OD, 0.225, ID, 0.20 Thick, Wax
<u>TO-22-250</u>	Diss-O-Pad, TO-22, Round, 0.437 OD, 0.225, ID, 0.25 Thick, Wax
<u>TO-23-040</u>	Diss-O-Pad, TO-23, Round, 0.31 OD, 0.09, ID, 0.04 Thick, Wax
<u>TO-23-050</u>	Diss-O-Pad, TO-23, Round, 0.31 OD, 0.09, ID, 0.05 Thick, Wax
<u>TO-23-060</u>	Diss-O-Pad, TO-23, Round, 0.31 OD, 0.09, ID, 0.06 Thick, Wax
<u>TO-23-070</u>	Diss-O-Pad, TO-23, Round, 0.31 OD, 0.09, ID, 0.07 Thick, Wax
<u>TO-23-100</u>	Diss-O-Pad, TO-23, Round, 0.31 OD, 0.09, ID, 0.10 Thick, Wax
<u>TO-23-120</u>	Diss-O-Pad, TO-23, Round, 0.31 OD, 0.09, ID, 0.12 Thick, Wax
<u>TO-23-130</u>	Diss-O-Pad, TO-23, Round, 0.31 OD, 0.09, ID, 0.13 Thick, Wax
<u>TO-23-150</u>	Diss-O-Pad, TO-23, Round, 0.31 OD, 0.09, ID, 0.15 Thick, Wax
<u>TO-23-180</u>	Diss-O-Pad, TO-23, Round, 0.31 OD, 0.09, ID, 0.18 Thick, Wax
<u>TO-23-190</u>	Diss-O-Pad, TO-23, Round, 0.31 OD, 0.09, ID, 0.19 Thick, Wax
<u>TO-23-200</u>	Diss-O-Pad, TO-23, Round, 0.31 OD, 0.09, ID, 0.20 Thick, Wax
<u>TO-23-250</u>	Diss-O-Pad, TO-23, Round, 0.31 OD, 0.09, ID, 0.25 Thick, Wax
<u>TO-24-040</u>	Diss-O-Pad, TO-24, Round, 0.34 OD, 0.09, ID, 0.04 Thick, Wax
<u>TO-24-050</u>	Diss-O-Pad, TO-24, Round, 0.34 OD, 0.09, ID, 0.05 Thick, Wax
<u>TO-24-060</u>	Diss-O-Pad, TO-24, Round, 0.34 OD, 0.09, ID, 0.06 Thick, Wax
<u>TO-24-070</u>	Diss-O-Pad, TO-24, Round, 0.34 OD, 0.09, ID, 0.07 Thick, Wax
<u>TO-24-090</u>	Diss-O-Pad, TO-24, Round, 0.34 OD, 0.09, ID, 0.09 Thick, Wax
<u>TO-24-100</u>	Diss-O-Pad, TO-24, Round, 0.34 OD, 0.09, ID, 0.10 Thick, Wax
<u>TO-24-130</u>	Diss-O-Pad, TO-24, Round, 0.34 OD, 0.09, ID, 0.13 Thick, Wax
<u>TO-24-150</u>	Diss-O-Pad, TO-24, Round, 0.34 OD, 0.09, ID, 0.15 Thick, Wax
<u>TO-25-040</u>	Diss-O-Pad, TO-25, Round, 0.48 OD, 0.18, ID, 0.04 Thick, Wax
<u>TO-25-050</u>	Diss-O-Pad, TO-25, Round, 0.48 OD, 0.18, ID, 0.05 Thick, Wax
<u>TO-25-060</u>	Diss-O-Pad, TO-25, Round, 0.48 OD, 0.18, ID, 0.06 Thick, Wax
<u>TO-25-070</u>	Diss-O-Pad, TO-25, Round, 0.48 OD, 0.18, ID, 0.07 Thick, Wax

Round Wash-Away Component Spacers

<u>TO-25-090</u>	Diss-O-Pad, TO-25, Round, 0.48 OD, 0.18, ID, 0.09 Thick, Wax
<u>TO-25-100</u>	Diss-O-Pad, TO-25, Round, 0.48 OD, 0.18, ID, 0.10 Thick, Wax
<u>TO-25-120</u>	Diss-O-Pad, TO-25, Round, 0.48 OD, 0.18, ID, 0.12 Thick, Wax
<u>TO-25-130</u>	Diss-O-Pad, TO-25, Round, 0.48 OD, 0.18, ID, 0.13 Thick, Wax
<u>TO-26-040</u>	Diss-O-Pad, TO-26, Round, 0.187 OD, 0.07, ID, 0.04 Thick, Wax
<u>TO-26-050</u>	Diss-O-Pad, TO-26, Round, 0.187 OD, 0.07, ID, 0.05 Thick, Wax
<u>TO-26-060</u>	Diss-O-Pad, TO-26, Round, 0.187 OD, 0.07, ID, 0.06 Thick, Wax
<u>TO-26-070</u>	Diss-O-Pad, TO-26, Round, 0.187 OD, 0.07, ID, 0.07 Thick, Wax
<u>TO-26-090</u>	Diss-O-Pad, TO-26, Round, 0.187 OD, 0.07, ID, 0.09 Thick, Wax
<u>TO-26-100</u>	Diss-O-Pad, TO-26, Round, 0.187 OD, 0.07, ID, 0.10 Thick, Wax
<u>TO-26-120</u>	Diss-O-Pad, TO-26, Round, 0.187 OD, 0.07, ID, 0.12 Thick, Wax
<u>TO-26-150</u>	Diss-O-Pad, TO-26, Round, 0.187 OD, 0.07, ID, 0.15 Thick, Wax
<u>TO-27-050</u>	Diss-O-Pad, TO-27, Round, 0.29 OD, 0.125, ID, 0.05 Thick, Wax
<u>TO-27-060</u>	Diss-O-Pad, TO-27, Round, 0.29 OD, 0.125, ID, 0.06 Thick, Wax
<u>TO-27-070</u>	Diss-O-Pad, TO-27, Round, 0.29 OD, 0.125, ID, 0.07 Thick, Wax
<u>TO-27-100</u>	Diss-O-Pad, TO-27, Round, 0.29 OD, 0.125, ID, 0.10 Thick, Wax
<u>TO-27-120</u>	Diss-O-Pad, TO-27, Round, 0.29 OD, 0.125, ID, 0.12 Thick, Wax
<u>TO-27-130</u>	Diss-O-Pad, TO-27, Round, 0.29 OD, 0.125, ID, 0.13 Thick, Wax
<u>TO-28-040</u>	Diss-O-Pad, TO-28, Round, 0.343 OD, 0.172, ID, 0.04 Thick, Wax
<u>TO-28-050</u>	Diss-O-Pad, TO-28, Round, 0.343 OD, 0.172, ID, 0.05 Thick, Wax
<u>TO-28-060</u>	Diss-O-Pad, TO-28, Round, 0.343 OD, 0.172, ID, 0.06 Thick, Wax
<u>TO-28-070</u>	Diss-O-Pad, TO-28, Round, 0.343 OD, 0.172, ID, 0.07 Thick, Wax
<u>TO-28-100</u>	Diss-O-Pad, TO-28, Round, 0.343 OD, 0.172, ID, 0.10 Thick, Wax
<u>TO-28-120</u>	Diss-O-Pad, TO-28, Round, 0.343 OD, 0.172, ID, 0.12 Thick, Wax
<u>TO-28-130</u>	Diss-O-Pad, TO-28, Round, 0.343 OD, 0.172, ID, 0.13 Thick, Wax
<u>TO-28-180</u>	Diss-O-Pad, TO-28, Round, 0.343 OD, 0.172, ID, 0.18 Thick, Wax
<u>TO-28-190</u>	Diss-O-Pad, TO-28, Round, 0.343 OD, 0.172, ID, 0.19 Thick, Wax
<u>TO-29-040</u>	Diss-O-Pad, TO-29, Disk, 0.156 OD, ID, 0.04 Thick, Wax
<u>TO-29-050</u>	Diss-O-Pad, TO-29, Disk, 0.156 OD, ID, 0.05 Thick, Wax
<u>TO-29-060</u>	Diss-O-Pad, TO-29, Disk, 0.156 OD, ID, 0.06 Thick, Wax

Round Wash-Away Component Spacers

<u>TO-29-070</u>	Diss-O-Pad, TO-29, Disk, 0.156 OD, ID, 0.07 Thick, Wax
<u>TO-29-090</u>	Diss-O-Pad, TO-29, Disk, 0.156 OD, ID, 0.09 Thick, Wax
<u>TO-29-100</u>	Diss-O-Pad, TO-29, Disk, 0.156 OD, ID, 0.10 Thick, Wax
<u>TO-29-130</u>	Diss-O-Pad, TO-29, Disk, 0.156 OD, ID, 0.13 Thick, Wax
<u>TO-30-040</u>	Diss-O-Pad, TO-30, Round, 0.397 OD, 0.275, ID, 0.04 Thick, Wax
<u>TO-30-050</u>	Diss-O-Pad, TO-30, Round, 0.397 OD, 0.275, ID, 0.05 Thick, Wax
<u>TO-30-060</u>	Diss-O-Pad, TO-30, Round, 0.397 OD, 0.275, ID, 0.06 Thick, Wax
<u>TO-30-070</u>	Diss-O-Pad, TO-30, Round, 0.397 OD, 0.275, ID, 0.07 Thick, Wax
<u>TO-30-090</u>	Diss-O-Pad, TO-30, Round, 0.397 OD, 0.275, ID, 0.09 Thick, Wax
<u>TO-30-100</u>	Diss-O-Pad, TO-30, Round, 0.397 OD, 0.275, ID, 0.10 Thick, Wax
<u>TO-30-130</u>	Diss-O-Pad, TO-30, Round, 0.397 OD, 0.275, ID, 0.13 Thick, Wax
<u>TO-31-040</u>	Diss-O-Pad, TO-31, Disk, 0.125 OD, ID, 0.04 Thick, Wax
<u>TO-31-050</u>	Diss-O-Pad, TO-31, Disk, 0.125 OD, ID, 0.05 Thick, Wax
<u>TO-31-060</u>	Diss-O-Pad, TO-31, Disk, 0.125 OD, ID, 0.06 Thick, Wax
<u>TO-31-070</u>	Diss-O-Pad, TO-31, Disk, 0.125 OD, ID, 0.07 Thick, Wax
<u>TO-31-090</u>	Diss-O-Pad, TO-31, Disk, 0.125 OD, ID, 0.09 Thick, Wax
<u>TO-31-100</u>	Diss-O-Pad, TO-31, Disk, 0.125 OD, ID, 0.10 Thick, Wax
<u>TO-31-120</u>	Diss-O-Pad, TO-31, Disk, 0.125 OD, ID, 0.12 Thick, Wax
<u>TO-31-130</u>	Diss-O-Pad, TO-31, Disk, 0.125 OD, ID, 0.13 Thick, Wax
<u>TO-32-040</u>	Diss-O-Pad, TO-32, Disk, 0.187 OD, ID, 0.04 Thick, Wax
<u>TO-32-050</u>	Diss-O-Pad, TO-32, Disk, 0.187 OD, ID, 0.05 Thick, Wax
<u>TO-32-060</u>	Diss-O-Pad, TO-32, Disk, 0.187 OD, ID, 0.06 Thick, Wax
<u>TO-32-070</u>	Diss-O-Pad, TO-32, Disk, 0.187 OD, ID, 0.07 Thick, Wax
<u>TO-32-080</u>	Diss-O-Pad, TO-32, Disk, 0.187 OD, ID, 0.08 Thick, Wax
<u>TO-32-090</u>	Diss-O-Pad, TO-32, Disk, 0.187 OD, ID, 0.09 Thick, Wax
<u>TO-32-100</u>	Diss-O-Pad, TO-32, Disk, 0.187 OD, ID, 0.10 Thick, Wax
<u>TO-32-130</u>	Diss-O-Pad, TO-32, Disk, 0.187 OD, ID, 0.13 Thick, Wax
<u>TO-33-040</u>	Diss-O-Pad, TO-33, Disk, 0.25 OD, ID, 0.04 Thick, Wax
<u>TO-33-050</u>	Diss-O-Pad, TO-33, Disk, 0.25 OD, ID, 0.05 Thick, Wax
<u>TO-33-060</u>	Diss-O-Pad, TO-33, Disk, 0.25 OD, ID, 0.06 Thick, Wax

Round Wash-Away Component Spacers

<u>TO-33-070</u>	Diss-O-Pad, TO-33, Disk, 0.25 OD, ID, 0.07 Thick, Wax
<u>TO-33-080</u>	Diss-O-Pad, TO-33, Disk, 0.25 OD, ID, 0.08 Thick, Wax
<u>TO-33-090</u>	Diss-O-Pad, TO-33, Disk, 0.25 OD, ID, 0.09 Thick, Wax
<u>TO-33-100</u>	Diss-O-Pad, TO-33, Disk, 0.25 OD, ID, 0.10 Thick, Wax
<u>TO-33-120</u>	Diss-O-Pad, TO-33, Disk, 0.25 OD, ID, 0.12 Thick, Wax
<u>TO-33-130</u>	Diss-O-Pad, TO-33, Disk, 0.25 OD, ID, 0.13 Thick, Wax
<u>TO-35-100</u>	Diss-O-Pad, TO-35, Round, Grooved, 0.44 OD, ID, 0.10 Thick, Wax
<u>TO-35-120</u>	Diss-O-Pad, TO-35, Round, Grooved, 0.44 OD, ID, 0.12 Thick, Wax
<u>TO-35-13</u>	Diss-O-Pad, TO-35, Round, Grooved, 0.44 OD, ID, 0.13 Thick, Wax
<u>TO-35-130</u>	Diss-O-Pad, TO-35, Round, Grooved, 0.44 OD, ID, 0.13 Thick, Wax
<u>TO-35-140</u>	Diss-O-Pad, TO-35, Round, Grooved, 0.44 OD, ID, 0.14 Thick, Wax
<u>TO-35-150</u>	Diss-O-Pad, TO-35, Round, Grooved, 0.44 OD, ID, 0.15 Thick, Wax
<u>TO-35-170</u>	Diss-O-Pad, TO-35, Round, Grooved, 0.44 OD, ID, 0.17 Thick, Wax
<u>TO-35-180</u>	Diss-O-Pad, TO-35, Round, Grooved, 0.44 OD, ID, 0.18 Thick, Wax
<u>TO-35-190</u>	Diss-O-Pad, TO-35, Round, Grooved, 0.44 OD, ID, 0.19 Thick, Wax
<u>TO-35-220</u>	Diss-O-Pad, TO-35, Round, Grooved, 0.44 OD, ID, 0.22 Thick, Wax
<u>TO-35-230</u>	Diss-O-Pad, TO-35, Round, Grooved, 0.44 OD, ID, 0.23 Thick, Wax
<u>TO-36-060</u>	Diss-O-Pad, TO-36, Round, Grooved, 0.187 OD, ID, 0.06 Thick, Wax
<u>TO-36-070</u>	Diss-O-Pad, TO-36, Round, Grooved, 0.187 OD, ID, 0.07 Thick, Wax
<u>TO-36-080</u>	Diss-O-Pad, TO-36, Round, Grooved, 0.187 OD, ID, 0.08 Thick, Wax
<u>TO-36-090</u>	Diss-O-Pad, TO-36, Round, Grooved, 0.187 OD, ID, 0.09 Thick, Wax
<u>TO-36-100</u>	Diss-O-Pad, TO-36, Round, Grooved, 0.187 OD, ID, 0.10 Thick, Wax
<u>TO-36-120</u>	Diss-O-Pad, TO-36, Round, Grooved, 0.187 OD, ID, 0.12 Thick, Wax
<u>TO-36-130</u>	Diss-O-Pad, TO-36, Round, Grooved, 0.187 OD, ID, 0.13 Thick, Wax
<u>TO-36-150</u>	Diss-O-Pad, TO-36, Round, Grooved, 0.187 OD, ID, 0.15 Thick, Wax
<u>TO-37-050</u>	Diss-O-Pad, TO-37, Round, Grooved, 0.156 OD, ID, 0.05 Thick, Wax
<u>TO-37-070</u>	Diss-O-Pad, TO-37, Round, Grooved, 0.156 OD, ID, 0.07 Thick, Wax
<u>TO-37-090</u>	Diss-O-Pad, TO-37, Round, Grooved, 0.156 OD, ID, 0.09 Thick, Wax
<u>TO-37-100</u>	Diss-O-Pad, TO-37, Round, Grooved, 0.156 OD, ID, 0.10 Thick, Wax
<u>TO-37-120</u>	Diss-O-Pad, TO-37, Round, Grooved, 0.156 OD, ID, 0.12 Thick, Wax

Round Wash-Away Component Spacers

<u>TO-40-040</u>	Diss-O-Pad, TO-40, Round, 0.156 OD, 0.045, ID, 0.04 Thick, Wax
<u>TO-40-050</u>	Diss-O-Pad, TO-40, Round, 0.156 OD, 0.045, ID, 0.05 Thick, Wax
<u>TO-40-060</u>	Diss-O-Pad, TO-40, Round, 0.156 OD, 0.045, ID, 0.06 Thick, Wax
<u>TO-40-070</u>	Diss-O-Pad, TO-40, Round, 0.156 OD, 0.045, ID, 0.07 Thick, Wax
<u>TO-40-090</u>	Diss-O-Pad, TO-40, Round, 0.156 OD, 0.045, ID, 0.09 Thick, Wax
<u>TO-40-100</u>	Diss-O-Pad, TO-40, Round, 0.156 OD, 0.045, ID, 0.10 Thick, Wax
<u>TO-40-120</u>	Diss-O-Pad, TO-40, Round, 0.156 OD, 0.045, ID, 0.12 Thick, Wax
<u>TO-40-130</u>	Diss-O-Pad, TO-40, Round, 0.156 OD, 0.045, ID, 0.13 Thick, Wax
<u>TO-40-150</u>	Diss-O-Pad, TO-40, Round, 0.156 OD, 0.045, ID, 0.15 Thick, Wax
<u>TO-40-160</u>	Diss-O-Pad, TO-40, Round, 0.156 OD, 0.045, ID, 0.16 Thick, Wax
<u>TO-41-040</u>	Diss-O-Pad, TO-41, Round, 0.36 OD, 0.156, ID, 0.04 Thick, Wax
<u>TO-41-050</u>	Diss-O-Pad, TO-41, Round, 0.36 OD, 0.156, ID, 0.05 Thick, Wax
<u>TO-41-060</u>	Diss-O-Pad, TO-41, Round, 0.36 OD, 0.156, ID, 0.06 Thick, Wax
<u>TO-41-070</u>	Diss-O-Pad, TO-41, Round, 0.36 OD, 0.156, ID, 0.07 Thick, Wax
<u>TO-41-090</u>	Diss-O-Pad, TO-41, Round, 0.36 OD, 0.156, ID, 0.09 Thick, Wax
<u>TO-41-100</u>	Diss-O-Pad, TO-41, Round, 0.36 OD, 0.156, ID, 0.10 Thick, Wax
<u>TO-41-120</u>	Diss-O-Pad, TO-41, Round, 0.36 OD, 0.156, ID, 0.12 Thick, Wax
<u>TO-41-130</u>	Diss-O-Pad, TO-41, Round, 0.36 OD, 0.156, ID, 0.13 Thick, Wax
<u>TO-41-140</u>	Diss-O-Pad, TO-41, Round, 0.36 OD, 0.156, ID, 0.14 Thick, Wax
<u>TO-42-040</u>	Diss-O-Pad, TO-42, Round, 0.438 OD, 0.25, ID, 0.04 Thick, Wax
<u>TO-42-050</u>	Diss-O-Pad, TO-42, Round, 0.438 OD, 0.25, ID, 0.05 Thick, Wax
<u>TO-42-060</u>	Diss-O-Pad, TO-42, Round, 0.438 OD, 0.25, ID, 0.06 Thick, Wax
<u>TO-42-070</u>	Diss-O-Pad, TO-42, Round, 0.438 OD, 0.25, ID, 0.07 Thick, Wax
<u>TO-42-090</u>	Diss-O-Pad, TO-42, Round, 0.438 OD, 0.25, ID, 0.09 Thick, Wax
<u>TO-42-100</u>	Diss-O-Pad, TO-42, Round, 0.438 OD, 0.25, ID, 0.10 Thick, Wax
<u>TO-42-120</u>	Diss-O-Pad, TO-42, Round, 0.438 OD, 0.25, ID, 0.12 Thick, Wax
<u>TO-42-130</u>	Diss-O-Pad, TO-42, Round, 0.438 OD, 0.25, ID, 0.13 Thick, Wax
<u>TO-46-040</u>	Diss-O-Pad, TO-46, Round, 0.25 OD, 0.09, ID, 0.04 Thick, Wax
<u>TO-46-050</u>	Diss-O-Pad, TO-46, Round, 0.25 OD, 0.09, ID, 0.05 Thick, Wax
<u>TO-46-060</u>	Diss-O-Pad, TO-46, Round, 0.25 OD, 0.09, ID, 0.06 Thick, Wax

Round Wash-Away Component Spacers

<u>TO-46-070</u>	Diss-O-Pad, TO-46, Round, 0.25 OD, 0.09, ID, 0.07 Thick, Wax
<u>TO-46-090</u>	Diss-O-Pad, TO-46, Round, 0.25 OD, 0.09, ID, 0.09 Thick, Wax
<u>TO-46-090E</u>	Diss-O-Pad, TO-46, Round, 0.25 OD, 0.09, ID, 0.09 Thick, Effervescent
<u>TO-46-100</u>	Diss-O-Pad, TO-46, Round, 0.25 OD, 0.09, ID, 0.10 Thick, Wax
<u>TO-46-120</u>	Diss-O-Pad, TO-46, Round, 0.25 OD, 0.09, ID, 0.12 Thick, Wax
<u>TO-46-130</u>	Diss-O-Pad, TO-46, Round, 0.25 OD, 0.09, ID, 0.13 Thick, Wax
<u>TO-46-150</u>	Diss-O-Pad, TO-46, Round, 0.25 OD, 0.09, ID, 0.15 Thick, Wax
<u>TO-46-200</u>	Diss-O-Pad, TO-46, Round, 0.25 OD, 0.09, ID, 0.20 Thick, Wax
<u>TO-46-240</u>	Diss-O-Pad, TO-46, Round, 0.25 OD, 0.09, ID, 0.24 Thick, Wax
<u>TO-5-040</u>	Diss-O-Pad, TO-5, Round, 0.375 OD, 0.225, ID, 0.04 Thick, Wax
<u>TO-5-050</u>	Diss-O-Pad, TO-5, Round, 0.375 OD, 0.225, ID, 0.05 Thick, Wax
<u>TO-5-050E</u>	Diss-O-Pad, TO-5, Round, 0.375 OD, 0.225, ID, 0.05 Thick, Effervescent
<u>TO-5-060</u>	Diss-O-Pad, TO-5, Round, 0.375 OD, 0.225, ID, 0.06 Thick, Wax
<u>TO-5-070</u>	Diss-O-Pad, TO-5, Round, 0.375 OD, 0.225, ID, 0.07 Thick, Wax
<u>TO-5-090</u>	Diss-O-Pad, TO-5, Round, 0.375 OD, 0.225, ID, 0.09 Thick, Wax
<u>TO-5-100</u>	Diss-O-Pad, TO-5, Round, 0.375 OD, 0.225, ID, 0.10 Thick, Wax
<u>TO-5-120</u>	Diss-O-Pad, TO-5, Round, 0.375 OD, 0.225, ID, 0.12 Thick, Wax
<u>TO-5-120E</u>	Diss-O-Pad, TO-5, Round, 0.375 OD, 0.225, ID, 0.12 Thick, Effervescent
<u>TO-5-130</u>	Diss-O-Pad, TO-5, Round, 0.375 OD, 0.225, ID, 0.13 Thick, Wax
<u>TO-5-150</u>	Diss-O-Pad, TO-5, Round, 0.375 OD, 0.225, ID, 0.15 Thick, Wax
<u>TO-5-170</u>	Diss-O-Pad, TO-5, Round, 0.375 OD, 0.225, ID, 0.17 Thick, Wax
<u>TO-5-200</u>	Diss-O-Pad, TO-5, Round, 0.375 OD, 0.225, ID, 0.20 Thick, Wax
<u>TO-6-040</u>	Diss-O-Pad, TO-6, Round, 0.375 OD, 0.25, ID, 0.04 Thick, Wax
<u>TO-6-050</u>	Diss-O-Pad, TO-6, Round, 0.375 OD, 0.25, ID, 0.05 Thick, Wax
<u>TO-6-060</u>	Diss-O-Pad, TO-6, Round, 0.375 OD, 0.25, ID, 0.06 Thick, Wax
<u>TO-6-070</u>	Diss-O-Pad, TO-6, Round, 0.375 OD, 0.25, ID, 0.07 Thick, Wax
<u>TO-6-090</u>	Diss-O-Pad, TO-6, Round, 0.375 OD, 0.25, ID, 0.09 Thick, Wax
<u>TO-6-100</u>	Diss-O-Pad, TO-6, Round, 0.375 OD, 0.25, ID, 0.10 Thick, Wax
<u>TO-6-120</u>	Diss-O-Pad, TO-6, Round, 0.375 OD, 0.25, ID, 0.12 Thick, Wax
<u>TO-6-130</u>	Diss-O-Pad, TO-6, Round, 0.375 OD, 0.25, ID, 0.13 Thick, Wax

Round Wash-Away Component Spacers

<u>TO-6-150</u>	Diss-O-Pad, TO-6, Round, 0.375 OD, 0.25, ID, 0.15 Thick, Wax
<u>TO-6-160</u>	Diss-O-Pad, TO-6, Round, 0.375 OD, 0.25, ID, 0.16 Thick, Wax
<u>TO-6-180</u>	Diss-O-Pad, TO-6, Round, 0.375 OD, 0.25, ID, 0.18 Thick, Wax
<u>TO-64-040</u>	Diss-O-Pad, TO-64, Round, 0.14 OD, 0.045, ID, 0.04 Thick, Wax
<u>TO-64-050</u>	Diss-O-Pad, TO-64, Round, 0.14 OD, 0.045, ID, 0.05 Thick, Wax
<u>TO-64-060</u>	Diss-O-Pad, TO-64, Round, 0.14 OD, 0.045, ID, 0.06 Thick, Wax
<u>TO-64-070</u>	Diss-O-Pad, TO-64, Round, 0.14 OD, 0.045, ID, 0.07 Thick, Wax
<u>TO-64-090</u>	Diss-O-Pad, TO-64, Round, 0.14 OD, 0.045, ID, 0.09 Thick, Wax
<u>TO-64-100</u>	Diss-O-Pad, TO-64, Round, 0.14 OD, 0.045, ID, 0.10 Thick, Wax
<u>TO-64-120</u>	Diss-O-Pad, TO-64, Round, 0.14 OD, 0.045, ID, 0.12 Thick, Wax
<u>TO-64-130</u>	Diss-O-Pad, TO-64, Round, 0.14 OD, 0.045, ID, 0.13 Thick, Wax
<u>TO-64-140</u>	Diss-O-Pad, TO-64, Round, 0.14 OD, 0.045, ID, 0.14 Thick, Wax
<u>TO-64-150</u>	Diss-O-Pad, TO-64, Round, 0.14 OD, 0.045, ID, 0.15 Thick, Wax
<u>TO-64-160</u>	Diss-O-Pad, TO-64, Round, 0.14 OD, 0.045, ID, 0.16 Thick, Wax
<u>TO-65-050</u>	Diss-O-Pad, TO-65, Round, 0.14 OD, 0.075, ID, 0.05 Thick, Wax
<u>TO-65-060</u>	Diss-O-Pad, TO-65, Round, 0.14 OD, 0.075, ID, 0.06 Thick, Wax
<u>TO-65-070</u>	Diss-O-Pad, TO-65, Round, 0.14 OD, 0.075, ID, 0.07 Thick, Wax
<u>TO-65-080</u>	Diss-O-Pad, TO-65, Round, 0.14 OD, 0.075, ID, 0.08 Thick, Wax
<u>TO-65-090</u>	Diss-O-Pad, TO-65, Round, 0.14 OD, 0.075, ID, 0.09 Thick, Wax
<u>TO-65-100</u>	Diss-O-Pad, TO-65, Round, 0.14 OD, 0.075, ID, 0.10 Thick, Wax
<u>TO-65-120</u>	Diss-O-Pad, TO-65, Round, 0.14 OD, 0.075, ID, 0.12 Thick, Wax
<u>TO-65-130</u>	Diss-O-Pad, TO-65, Round, 0.14 OD, 0.075, ID, 0.13 Thick, Wax
<u>TO-65-150</u>	Diss-O-Pad, TO-65, Round, 0.14 OD, 0.075, ID, 0.15 Thick, Wax
<u>TO-67-050</u>	Diss-O-Pad, TO-67, Round, 0.14 OD, 0.045, ID, 0.05 Thick, Wax
<u>TO-67-060</u>	Diss-O-Pad, TO-67, Round, 0.14 OD, 0.045, ID, 0.06 Thick, Wax
<u>TO-67-070</u>	Diss-O-Pad, TO-67, Round, 0.14 OD, 0.045, ID, 0.07 Thick, Wax
<u>TO-67-090</u>	Diss-O-Pad, TO-67, Round, 0.14 OD, 0.045, ID, 0.09 Thick, Wax
<u>TO-67-100</u>	Diss-O-Pad, TO-67, Round, 0.14 OD, 0.045, ID, 0.10 Thick, Wax
<u>TO-67-120</u>	Diss-O-Pad, TO-67, Round, 0.14 OD, 0.045, ID, 0.12 Thick, Wax
<u>TO-67-130</u>	Diss-O-Pad, TO-67, Round, 0.14 OD, 0.045, ID, 0.13 Thick, Wax

Round Wash-Away Component Spacers

<u>TO-68-040</u>	Diss-O-Pad, TO-68, Round, 0.11 OD, 0.045, ID, 0.04 Thick, Wax
<u>TO-68-050</u>	Diss-O-Pad, TO-68, Round, 0.11 OD, 0.045, ID, 0.05 Thick, Wax
<u>TO-68-060</u>	Diss-O-Pad, TO-68, Round, 0.11 OD, 0.045, ID, 0.06 Thick, Wax
<u>TO-68-070</u>	Diss-O-Pad, TO-68, Round, 0.11 OD, 0.045, ID, 0.07 Thick, Wax
<u>TO-68-090</u>	Diss-O-Pad, TO-68, Round, 0.11 OD, 0.045, ID, 0.09 Thick, Wax
<u>TO-68-100</u>	Diss-O-Pad, TO-68, Round, 0.11 OD, 0.045, ID, 0.10 Thick, Wax
<u>TO-68-120</u>	Diss-O-Pad, TO-68, Round, 0.11 OD, 0.045, ID, 0.12 Thick, Wax
<u>TO-68-130</u>	Diss-O-Pad, TO-68, Round, 0.11 OD, 0.045, ID, 0.13 Thick, Wax
<u>TO-68-150</u>	Diss-O-Pad, TO-68, Round, 0.11 OD, 0.045, ID, 0.15 Thick, Wax
<u>TO-68-160</u>	Diss-O-Pad, TO-68, Round, 0.11 OD, 0.045, ID, 0.16 Thick, Wax
<u>TO-7-040</u>	Diss-O-Pad, TO-7, Round, 0.175 OD, 0.075, ID, 0.04 Thick, Wax
<u>TO-7-050</u>	Diss-O-Pad, TO-7, Round, 0.175 OD, 0.075, ID, 0.05 Thick, Wax
<u>TO-7-060</u>	Diss-O-Pad, TO-7, Round, 0.175 OD, 0.075, ID, 0.06 Thick, Wax
<u>TO-7-070</u>	Diss-O-Pad, TO-7, Round, 0.175 OD, 0.075, ID, 0.07 Thick, Wax
<u>TO-7-090</u>	Diss-O-Pad, TO-7, Round, 0.175 OD, 0.075, ID, 0.09 Thick, Wax
<u>TO-7-100</u>	Diss-O-Pad, TO-7, Round, 0.175 OD, 0.075, ID, 0.10 Thick, Wax
<u>TO-7-120</u>	Diss-O-Pad, TO-7, Round, 0.175 OD, 0.075, ID, 0.12 Thick, Wax
<u>TO-7-130</u>	Diss-O-Pad, TO-7, Round, 0.175 OD, 0.075, ID, 0.13 Thick, Wax
<u>TO-7-150</u>	Diss-O-Pad, TO-7, Round, 0.175 OD, 0.075, ID, 0.15 Thick, Wax
<u>TO-7-180</u>	Diss-O-Pad, TO-7, Round, 0.175 OD, 0.075, ID, 0.18 Thick, Wax
<u>TO-7-210</u>	Diss-O-Pad, TO-7, Round, 0.175 OD, 0.075, ID, 0.21 Thick, Wax
<u>TO-8-040</u>	Diss-O-Pad, TO-8, Round, 0.156 OD, 0.062, ID, 0.04 Thick, Wax
<u>TO-8-050</u>	Diss-O-Pad, TO-8, Round, 0.156 OD, 0.062, ID, 0.05 Thick, Wax
<u>TO-8-060</u>	Diss-O-Pad, TO-8, Round, 0.156 OD, 0.062, ID, 0.06 Thick, Wax
<u>TO-8-070</u>	Diss-O-Pad, TO-8, Round, 0.156 OD, 0.062, ID, 0.07 Thick, Wax
<u>TO-8-090</u>	Diss-O-Pad, TO-8, Round, 0.156 OD, 0.062, ID, 0.09 Thick, Wax
<u>TO-8-100</u>	Diss-O-Pad, TO-8, Round, 0.156 OD, 0.062, ID, 0.10 Thick, Wax
<u>TO-8-120</u>	Diss-O-Pad, TO-8, Round, 0.156 OD, 0.062, ID, 0.12 Thick, Wax
<u>TO-8-130</u>	Diss-O-Pad, TO-8, Round, 0.156 OD, 0.062, ID, 0.13 Thick, Wax
<u>TO-8-150</u>	Diss-O-Pad, TO-8, Round, 0.156 OD, 0.062, ID, 0.15 Thick, Wax

Round Wash-Away Component Spacers

<u>TO-8-160</u>	Diss-O-Pad, TO-8, Round, 0.156 OD, 0.062, ID, 0.16 Thick, Wax
<u>TO-8-190</u>	Diss-O-Pad, TO-8, Round, 0.156 OD, 0.062, ID, 0.19 Thick, Wax
<u>TO-8-200</u>	Diss-O-Pad, TO-8, Round, 0.156 OD, 0.062, ID, 0.20 Thick, Wax
<u>TO-8-210</u>	Diss-O-Pad, TO-8, Round, 0.156 OD, 0.062, ID, 0.21 Thick, Wax
<u>TO-9-040</u>	Diss-O-Pad, TO-9, Round, 0.437 OD, 0.3, ID, 0.04 Thick, Wax
<u>TO-9-050</u>	Diss-O-Pad, TO-9, Round, 0.437 OD, 0.3, ID, 0.05 Thick, Wax
<u>TO-9-070</u>	Diss-O-Pad, TO-9, Round, 0.437 OD, 0.3, ID, 0.07 Thick, Wax
<u>TO-9-080</u>	Diss-O-Pad, TO-9, Round, 0.437 OD, 0.3, ID, 0.08 Thick, Wax
<u>TO-9-090</u>	Diss-O-Pad, TO-9, Round, 0.437 OD, 0.3, ID, 0.09 Thick, Wax
<u>TO-9-100</u>	Diss-O-Pad, TO-9, Round, 0.437 OD, 0.3, ID, 0.10 Thick, Wax
<u>TO-9-120</u>	Diss-O-Pad, TO-9, Round, 0.437 OD, 0.3, ID, 0.12 Thick, Wax
<u>TO-9-130</u>	Diss-O-Pad, TO-9, Round, 0.437 OD, 0.3, ID, 0.13 Thick, Wax
<u>TO-9-150</u>	Diss-O-Pad, TO-9, Round, 0.437 OD, 0.3, ID, 0.15 Thick, Wax
<u>TO-9-180</u>	Diss-O-Pad, TO-9, Round, 0.437 OD, 0.3, ID, 0.18 Thick, Wax
<u>TO-9-200</u>	Diss-O-Pad, TO-9, Round, 0.437 OD, 0.3, ID, 0.20 Thick, Wax

Products

Component Mounts &
Spacers
Card Guides & Ejectors
Product Info Center

Applications

Audio Video
Communication
Industrial
Medical
Security
Transportation

News

Latest News
Archives

Distributors & Reps

About Us

Company Profile
Quality Assurance
Corporate Terms
& Conditions

Bivar Sites

Bivar Corporate
Enclosure
Hardware
LED Indication
LED Lighting
MyBivar

© 2014 Bivar Inc., All Rights Reserved.

Contact Us

Terms & Conditions | Privacy Policy | Sitemap



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[TO-6-070](#) [TO-11-100](#) [TO-10-050](#) [TO-16-100](#) [TO-17-070](#) [TO-18-060](#) [TO-7-050](#) [TO-8-050](#) [TO-67-130](#) [TO-10-040](#)
[TO-10-060](#) [TO-10-070](#) [TO-10-080](#) [TO-10-090](#) [TO-10-100](#) [TO-11-040](#) [TO-11-050](#) [TO-11-060](#) [TO-11-070](#) [TO-11-](#)
[080](#) [TO-11-110](#) [TO-12-080](#) [TO-12-090](#) [TO-12-100](#) [TO-12-120](#) [TO-12-130](#) [TO-12-180](#) [TO-13-040](#) [TO-13-050](#) [TO-](#)
[13-060](#) [TO-13-070](#) [TO-13-080](#) [TO-13-090](#) [TO-13-100](#) [TO-13-120](#) [TO-13-130](#) [TO-16-040](#) [TO-16-050](#) [TO-16-060](#)
[TO-16-070](#) [TO-16-080](#) [TO-16-090](#) [TO-16-120](#) [TO-16-130](#) [TO-16-150](#) [TO-16-200](#) [TO-17-040](#) [TO-17-050](#) [TO-17-](#)
[060](#) [TO-17-090](#) [TO-17-100](#) [TO-17-120](#) [TO-17-130](#) [TO-17-140](#) [TO-17-150](#) [TO-17-170](#) [TO-17-180](#) [TO-17-200](#) [TO-](#)
[18-040](#) [TO-18-050](#) [TO-18-070](#) [TO-18-080](#) [TO-18-090](#) [TO-18-100](#) [TO-18-120](#) [TO-18-130](#) [TO-18-150](#) [TO-18-170](#)
[TO-18-190](#) [TO-18-200](#) [TO-19-040](#) [TO-19-050](#) [TO-19-060](#) [TO-19-070](#) [TO-19-090](#) [TO-19-100](#) [TO-19-120](#) [TO-19-](#)
[130](#) [TO-19-150](#) [TO-19-190](#) [TO-19-200](#) [TO-19-230](#) [TO-19-250](#) [TO-20-090](#) [TO-20-100](#) [TO-20-120](#) [TO-20-130](#) [TO-](#)
[20-150](#) [TO-21-050](#) [TO-21-070](#) [TO-21-080](#) [TO-21-090](#) [TO-21-100](#) [TO-21-120](#) [TO-21-130](#) [TO-21-170](#) [TO-21-200](#)
[TO-22-040](#) [TO-22-050](#) [TO-22-060](#)