


[Home](#) / [Products](#) / [Component Mounts & Spacers](#) / [Wash Away Spacers](#) / [Rectangular and Square Wash-Away Component Spacers](#)

Component Mounts & Spacers

[Component Mounts](#)
[Spacers](#)
[Wash Away Spacers](#)
[Crystal Insulators](#)

Card Guides & Ejectors

[Card Guides](#)
[PCB Ejectors](#)

Product Info Center

Rectangular and Square Wash-Away Component Spacers



The Popular Diss-O-Pad Spacer series of Wash-Away Spacers provide for accurate positioning of through-hole electronic components on PCBs then dissolve in hot or warm running water without a trace of residue. Rectangular and square water soluble spacers provide a problem solving approach to control production uniformity through the soldering process while eliminating scrap and rejects due to improper component placement or contaminant entrapment. Manufactured from organic materials, Wash-Away Spacers are ecological solution to improved production yield with over 200 styles available from stock.

PART NUMBER	DESCRIPTION
TO-100-040	Diss-O-Pad, TO-100, Rectangle, 0.67 Length, 0.1 Width, 0.04 Thick, Wax
TO-100-050	Diss-O-Pad, TO-100, Rectangle, 0.67 Length, 0.1 Width, 0.05 Thick, Wax
TO-100-060	Diss-O-Pad, TO-100, Rectangle, 0.67 Length, 0.1 Width, 0.06 Thick, Wax
TO-100-070	Diss-O-Pad, TO-100, Rectangle, 0.67 Length, 0.1 Width, 0.07 Thick, Wax
TO-100-080	Diss-O-Pad, TO-100, Rectangle, 0.67 Length, 0.1 Width, 0.08 Thick, Wax
TO-100-090	Diss-O-Pad, TO-100, Rectangle, 0.67 Length, 0.1 Width, 0.09 Thick, Wax
TO-100-100	Diss-O-Pad, TO-100, Rectangle, 0.67 Length, 0.1 Width, 0.10 Thick, Wax
TO-100-120	Diss-O-Pad, TO-100, Rectangle, 0.67 Length, 0.1 Width, 0.12 Thick, Wax
TO-100-130	Diss-O-Pad, TO-100, Rectangle, 0.67 Length, 0.1 Width, 0.13 Thick, Wax
TO-100-150	Diss-O-Pad, TO-100, Rectangle, 0.67 Length, 0.1 Width, 0.15 Thick, Wax
TO-100-200	Diss-O-Pad, TO-100, Rectangle, 0.67 Length, 0.1 Width, 0.20 Thick, Wax
TO-101-040	Diss-O-Pad, TO-101, Rectangle, 0.562 Length, 0.185 Width, 0.04 Thick, Wax
TO-101-050	Diss-O-Pad, TO-101, Rectangle, 0.562 Length, 0.185 Width, 0.05 Thick, Wax
TO-101-060	Diss-O-Pad, TO-101, Rectangle, 0.562 Length, 0.185 Width, 0.06 Thick, Wax

Rectangular and Square Wash-Away Component Spacers

<u>TO-101-070</u>	Diss-O-Pad, TO-101, Rectangle, 0.562 Length, 0.185 Width, 0.07 Thick, Wax
<u>TO-101-080</u>	Diss-O-Pad, TO-101, Rectangle, 0.562 Length, 0.185 Width, 0.08 Thick, Wax
<u>TO-101-090</u>	Diss-O-Pad, TO-101, Rectangle, 0.562 Length, 0.185 Width, 0.09 Thick, Wax
<u>TO-101-100</u>	Diss-O-Pad, TO-101, Rectangle, 0.562 Length, 0.185 Width, 0.10 Thick, Wax
<u>TO-101-120</u>	Diss-O-Pad, TO-101, Rectangle, 0.562 Length, 0.185 Width, 0.12 Thick, Wax
<u>TO-101-130</u>	Diss-O-Pad, TO-101, Rectangle, 0.562 Length, 0.185 Width, 0.13 Thick, Wax
<u>TO-101-150</u>	Diss-O-Pad, TO-101, Rectangle, 0.562 Length, 0.185 Width, 0.15 Thick, Wax
<u>TO-102-040</u>	Diss-O-Pad, TO-102, Rectangle, 0.505 Length, 0.16 Width, 0.04 Thick, Wax
<u>TO-102-050</u>	Diss-O-Pad, TO-102, Rectangle, 0.505 Length, 0.16 Width, 0.05 Thick, Wax
<u>TO-102-060</u>	Diss-O-Pad, TO-102, Rectangle, 0.505 Length, 0.16 Width, 0.06 Thick, Wax
<u>TO-102-070</u>	Diss-O-Pad, TO-102, Rectangle, 0.505 Length, 0.16 Width, 0.07 Thick, Wax
<u>TO-102-090</u>	Diss-O-Pad, TO-102, Rectangle, 0.505 Length, 0.16 Width, 0.09 Thick, Wax
<u>TO-102-100</u>	Diss-O-Pad, TO-102, Rectangle, 0.505 Length, 0.16 Width, 0.10 Thick, Wax
<u>TO-102-120</u>	Diss-O-Pad, TO-102, Rectangle, 0.505 Length, 0.16 Width, 0.12 Thick, Wax
<u>TO-102-130</u>	Diss-O-Pad, TO-102, Rectangle, 0.505 Length, 0.16 Width, 0.13 Thick, Wax
<u>TO-116-040</u>	Diss-O-Pad, TO-116, Rectangle, 0.666 Length, 0.3 Width, 0.04 Thick, Wax
<u>TO-116-050</u>	Diss-O-Pad, TO-116, Rectangle, 0.666 Length, 0.3 Width, 0.05 Thick, Wax
<u>TO-116-060</u>	Diss-O-Pad, TO-116, Rectangle, 0.666 Length, 0.3 Width, 0.06 Thick, Wax
<u>TO-116-070</u>	Diss-O-Pad, TO-116, Rectangle, 0.666 Length, 0.3 Width, 0.07 Thick, Wax
<u>TO-116-080</u>	Diss-O-Pad, TO-116, Rectangle, 0.666 Length, 0.3 Width, 0.08 Thick, Wax
<u>TO-116-090</u>	Diss-O-Pad, TO-116, Rectangle, 0.666 Length, 0.3 Width, 0.09 Thick, Wax
<u>TO-116-100</u>	Diss-O-Pad, TO-116, Rectangle, 0.666 Length, 0.3 Width, 0.10 Thick, Wax
<u>TO-116-110</u>	Diss-O-Pad, TO-116, Rectangle, 0.666 Length, 0.3 Width, 0.11 Thick, Wax
<u>TO-116-120</u>	Diss-O-Pad, TO-116, Rectangle, 0.666 Length, 0.3 Width, 0.12 Thick, Wax
<u>TO-116-130</u>	Diss-O-Pad, TO-116, Rectangle, 0.666 Length, 0.3 Width, 0.13 Thick, Wax
<u>TO-116-150</u>	Diss-O-Pad, TO-116, Rectangle, 0.666 Length, 0.3 Width, 0.15 Thick, Wax
<u>TO-116-180</u>	Diss-O-Pad, TO-116, Rectangle, 0.666 Length, 0.3 Width, 0.18 Thick, Wax
<u>TO-116-200</u>	Diss-O-Pad, TO-116, Rectangle, 0.666 Length, 0.3 Width, 0.20 Thick, Wax
<u>TO-117-040</u>	Diss-O-Pad, TO-117, Rectangle, 0.666 Length, 0.281 Width, 0.04 Thick, Wax
<u>TO-117-050</u>	Diss-O-Pad, TO-117, Rectangle, 0.666 Length, 0.281 Width, 0.05 Thick, Wax

Rectangular and Square Wash-Away Component Spacers

<u>TO-117-060</u>	Diss-O-Pad, TO-117, Rectangle, 0.666 Length, 0.281 Width, 0.06 Thick, Wax
<u>TO-117-070</u>	Diss-O-Pad, TO-117, Rectangle, 0.666 Length, 0.281 Width, 0.07 Thick, Wax
<u>TO-117-080</u>	Diss-O-Pad, TO-117, Rectangle, 0.666 Length, 0.281 Width, 0.08 Thick, Wax
<u>TO-117-090</u>	Diss-O-Pad, TO-117, Rectangle, 0.666 Length, 0.281 Width, 0.09 Thick, Wax
<u>TO-117-100</u>	Diss-O-Pad, TO-117, Rectangle, 0.666 Length, 0.281 Width, 0.10 Thick, Wax
<u>TO-117-120</u>	Diss-O-Pad, TO-117, Rectangle, 0.666 Length, 0.281 Width, 0.12 Thick, Wax
<u>TO-117-130</u>	Diss-O-Pad, TO-117, Rectangle, 0.666 Length, 0.281 Width, 0.13 Thick, Wax
<u>TO-117-140</u>	Diss-O-Pad, TO-117, Rectangle, 0.666 Length, 0.281 Width, 0.14 Thick, Wax
<u>TO-117-150</u>	Diss-O-Pad, TO-117, Rectangle, 0.666 Length, 0.281 Width, 0.15 Thick, Wax
<u>TO-117-160</u>	Diss-O-Pad, TO-117, Rectangle, 0.666 Length, 0.281 Width, 0.16 Thick, Wax
<u>TO-118-040</u>	Diss-O-Pad, TO-118, Rectangle, 0.705 Length, 0.26 Width, 0.04 Thick, Wax
<u>TO-118-050</u>	Diss-O-Pad, TO-118, Rectangle, 0.705 Length, 0.26 Width, 0.05 Thick, Wax
<u>TO-118-060</u>	Diss-O-Pad, TO-118, Rectangle, 0.705 Length, 0.26 Width, 0.06 Thick, Wax
<u>TO-118-070</u>	Diss-O-Pad, TO-118, Rectangle, 0.705 Length, 0.26 Width, 0.07 Thick, Wax
<u>TO-118-080</u>	Diss-O-Pad, TO-118, Rectangle, 0.705 Length, 0.26 Width, 0.08 Thick, Wax
<u>TO-118-090</u>	Diss-O-Pad, TO-118, Rectangle, 0.705 Length, 0.26 Width, 0.09 Thick, Wax
<u>TO-118-100</u>	Diss-O-Pad, TO-118, Rectangle, 0.705 Length, 0.26 Width, 0.10 Thick, Wax
<u>TO-118-110</u>	Diss-O-Pad, TO-118, Rectangle, 0.705 Length, 0.26 Width, 0.11 Thick, Wax
<u>TO-118-120</u>	Diss-O-Pad, TO-118, Rectangle, 0.705 Length, 0.26 Width, 0.12 Thick, Wax
<u>TO-118-130</u>	Diss-O-Pad, TO-118, Rectangle, 0.705 Length, 0.26 Width, 0.13 Thick, Wax
<u>TO-118-150</u>	Diss-O-Pad, TO-118, Rectangle, 0.705 Length, 0.26 Width, 0.15 Thick, Wax
<u>TO-118-160</u>	Diss-O-Pad, TO-118, Rectangle, 0.705 Length, 0.26 Width, 0.16 Thick, Wax
<u>TO-118-170</u>	Diss-O-Pad, TO-118, Rectangle, 0.705 Length, 0.26 Width, 0.17 Thick, Wax
<u>TO-118-200</u>	Diss-O-Pad, TO-118, Rectangle, 0.705 Length, 0.26 Width, 0.20 Thick, Wax
<u>TO-120-040</u>	Diss-O-Pad, TO-120, Square, 0.085 Length, 0.085 Width, 0.04 Thick, Wax
<u>TO-120-050</u>	Diss-O-Pad, TO-120, Square, 0.085 Length, 0.085 Width, 0.05 Thick, Wax
<u>TO-120-060</u>	Diss-O-Pad, TO-120, Square, 0.085 Length, 0.085 Width, 0.06 Thick, Wax
<u>TO-120-070</u>	Diss-O-Pad, TO-120, Square, 0.085 Length, 0.085 Width, 0.07 Thick, Wax
<u>TO-120-090</u>	Diss-O-Pad, TO-120, Square, 0.085 Length, 0.085 Width, 0.09 Thick, Wax
<u>TO-120-100</u>	Diss-O-Pad, TO-120, Square, 0.085 Length, 0.085 Width, 0.10 Thick, Wax

Rectangular and Square Wash-Away Component Spacers

<u>TO-120-120</u>	Diss-O-Pad, TO-120, Square, 0.085 Length, 0.085 Width, 0.12 Thick, Wax
<u>TO-121-040</u>	Diss-O-Pad, TO-121, Square, 0.095 Length, 0.095 Width, 0.04 Thick, Wax
<u>TO-121-050</u>	Diss-O-Pad, TO-121, Square, 0.095 Length, 0.095 Width, 0.05 Thick, Wax
<u>TO-121-060</u>	Diss-O-Pad, TO-121, Square, 0.095 Length, 0.095 Width, 0.06 Thick, Wax
<u>TO-121-070</u>	Diss-O-Pad, TO-121, Square, 0.095 Length, 0.095 Width, 0.07 Thick, Wax
<u>TO-121-090</u>	Diss-O-Pad, TO-121, Square, 0.095 Length, 0.095 Width, 0.09 Thick, Wax
<u>TO-121-100</u>	Diss-O-Pad, TO-121, Square, 0.095 Length, 0.095 Width, 0.10 Thick, Wax
<u>TO-121-120</u>	Diss-O-Pad, TO-121, Square, 0.095 Length, 0.095 Width, 0.12 Thick, Wax
<u>TO-200-040</u>	Diss-O-Pad, TO-200, Rectangle, Notched, 0.19 Length, 0.095 Width, 0.04 Thick, Wax
<u>TO-200-050</u>	Diss-O-Pad, TO-200, Rectangle, Notched, 0.19 Length, 0.095 Width, 0.05 Thick, Wax
<u>TO-200-060</u>	Diss-O-Pad, TO-200, Rectangle, Notched, 0.19 Length, 0.095 Width, 0.06 Thick, Wax
<u>TO-200-080</u>	Diss-O-Pad, TO-200, Rectangle, Notched, 0.19 Length, 0.095 Width, 0.08 Thick, Wax
<u>TO-200-090</u>	Diss-O-Pad, TO-200, Rectangle, Notched, 0.19 Length, 0.095 Width, 0.09 Thick, Wax
<u>TO-200-100</u>	Diss-O-Pad, TO-200, Rectangle, Notched, 0.19 Length, 0.095 Width, 0.10 Thick, Wax
<u>TO-200-120</u>	Diss-O-Pad, TO-200, Rectangle, Notched, 0.19 Length, 0.095 Width, 0.12 Thick, Wax
<u>TO-200-130</u>	Diss-O-Pad, TO-200, Rectangle, Notched, 0.19 Length, 0.095 Width, 0.13 Thick, Wax
<u>TO-200-150</u>	Diss-O-Pad, TO-200, Rectangle, Notched, 0.19 Length, 0.095 Width, 0.15 Thick, Wax
<u>TO-201-040</u>	Diss-O-Pad, TO-201, Rectangle, Notched, 0.24 Length, 0.095 Width, 0.04 Thick, Wax
<u>TO-201-050</u>	Diss-O-Pad, TO-201, Rectangle, Notched, 0.24 Length, 0.095 Width, 0.05 Thick, Wax
<u>TO-201-050E</u>	Diss-O-Pad, TO-201, Rectangle, Notched, 0.24 Length, 0.095 Width, 0.05 Thick, Effervescent
<u>TO-201-070</u>	Diss-O-Pad, TO-201, Rectangle, Notched, 0.24 Length, 0.095 Width, 0.07 Thick, Wax
<u>TO-201-090</u>	Diss-O-Pad, TO-201, Rectangle, Notched, 0.24 Length, 0.095 Width, 0.09 Thick, Wax
<u>TO-201-100</u>	Diss-O-Pad, TO-201, Rectangle, Notched, 0.24 Length, 0.095 Width, 0.10 Thick, Wax
<u>TO-201-120</u>	Diss-O-Pad, TO-201, Rectangle, Notched, 0.24 Length, 0.095 Width, 0.12 Thick, Wax
<u>TO-201-120E</u>	Diss-O-Pad, TO-201, Rectangle, Notched, 0.24 Length, 0.095 Width, 0.12 Thick, Effervescent
<u>TO-201-130</u>	Diss-O-Pad, TO-201, Rectangle, Notched, 0.24 Length, 0.095 Width, 0.13 Thick, Wax
<u>TO-201-150</u>	Diss-O-Pad, TO-201, Rectangle, Notched, 0.24 Length, 0.095 Width, 0.15 Thick, Wax
<u>TO-203-040</u>	Diss-O-Pad, TO-203, Rectangle, Notched, 0.29 Length, 0.095 Width, 0.04 Thick, Wax
<u>TO-203-050</u>	Diss-O-Pad, TO-203, Rectangle, Notched, 0.29 Length, 0.095 Width, 0.05 Thick, Wax
<u>TO-203-060</u>	Diss-O-Pad, TO-203, Rectangle, Notched, 0.29 Length, 0.095 Width, 0.06 Thick, Wax

Rectangular and Square Wash-Away Component Spacers

<u>TO-203-070</u>	Diss-O-Pad, TO-203, Rectangle, Notched, 0.29 Length, 0.095 Width, 0.07 Thick, Wax
<u>TO-203-090</u>	Diss-O-Pad, TO-203, Rectangle, Notched, 0.29 Length, 0.095 Width, 0.09 Thick, Wax
<u>TO-203-100</u>	Diss-O-Pad, TO-203, Rectangle, Notched, 0.29 Length, 0.095 Width, 0.10 Thick, Wax
<u>TO-203-120</u>	Diss-O-Pad, TO-203, Rectangle, Notched, 0.29 Length, 0.095 Width, 0.12 Thick, Wax
<u>TO-203-130</u>	Diss-O-Pad, TO-203, Rectangle, Notched, 0.29 Length, 0.095 Width, 0.13 Thick, Wax
<u>TO-203-140</u>	Diss-O-Pad, TO-203, Rectangle, Notched, 0.29 Length, 0.095 Width, 0.14 Thick, Wax
<u>TO-203-150</u>	Diss-O-Pad, TO-203, Rectangle, Notched, 0.29 Length, 0.095 Width, 0.15 Thick, Wax
<u>TO-204-040</u>	Diss-O-Pad, TO-204, Rectangle, Notched, 0.34 Length, 0.145 Width, 0.04 Thick, Wax
<u>TO-204-050</u>	Diss-O-Pad, TO-204, Rectangle, Notched, 0.34 Length, 0.145 Width, 0.05 Thick, Wax
<u>TO-204-060</u>	Diss-O-Pad, TO-204, Rectangle, Notched, 0.34 Length, 0.145 Width, 0.06 Thick, Wax
<u>TO-204-070</u>	Diss-O-Pad, TO-204, Rectangle, Notched, 0.34 Length, 0.145 Width, 0.07 Thick, Wax
<u>TO-204-080</u>	Diss-O-Pad, TO-204, Rectangle, Notched, 0.34 Length, 0.145 Width, 0.08 Thick, Wax
<u>TO-204-090</u>	Diss-O-Pad, TO-204, Rectangle, Notched, 0.34 Length, 0.145 Width, 0.09 Thick, Wax
<u>TO-204-100</u>	Diss-O-Pad, TO-204, Rectangle, Notched, 0.34 Length, 0.145 Width, 0.10 Thick, Wax
<u>TO-204-120</u>	Diss-O-Pad, TO-204, Rectangle, Notched, 0.34 Length, 0.145 Width, 0.12 Thick, Wax
<u>TO-204-130</u>	Diss-O-Pad, TO-204, Rectangle, Notched, 0.34 Length, 0.145 Width, 0.13 Thick, Wax
<u>TO-204-150</u>	Diss-O-Pad, TO-204, Rectangle, Notched, 0.34 Length, 0.145 Width, 0.15 Thick, Wax
<u>TO-205-040</u>	Diss-O-Pad, TO-205, Rectangle, Notched, 0.39 Length, 0.145 Width, 0.04 Thick, Wax
<u>TO-205-040E</u>	Diss-O-Pad, TO-205, Rectangle, Notched, 0.39 Length, 0.145 Width, 0.04 Thick, Effervescent
<u>TO-205-060</u>	Diss-O-Pad, TO-205, Rectangle, Notched, 0.39 Length, 0.145 Width, 0.06 Thick, Wax
<u>TO-205-070</u>	Diss-O-Pad, TO-205, Rectangle, Notched, 0.39 Length, 0.145 Width, 0.07 Thick, Wax
<u>TO-205-090</u>	Diss-O-Pad, TO-205, Rectangle, Notched, 0.39 Length, 0.145 Width, 0.09 Thick, Wax
<u>TO-205-100</u>	Diss-O-Pad, TO-205, Rectangle, Notched, 0.39 Length, 0.145 Width, 0.10 Thick, Wax
<u>TO-205-120</u>	Diss-O-Pad, TO-205, Rectangle, Notched, 0.39 Length, 0.145 Width, 0.12 Thick, Wax
<u>TO-205-130</u>	Diss-O-Pad, TO-205, Rectangle, Notched, 0.39 Length, 0.145 Width, 0.13 Thick, Wax
<u>TO-205-150</u>	Diss-O-Pad, TO-205, Rectangle, Notched, 0.39 Length, 0.145 Width, 0.15 Thick, Wax
<u>TO-206-040</u>	Diss-O-Pad, TO-206, Rectangle, Notched, 0.49 Length, 0.195 Width, 0.04 Thick, Wax
<u>TO-206-050</u>	Diss-O-Pad, TO-206, Rectangle, Notched, 0.49 Length, 0.195 Width, 0.05 Thick, Wax
<u>TO-206-060</u>	Diss-O-Pad, TO-206, Rectangle, Notched, 0.49 Length, 0.195 Width, 0.06 Thick, Wax
<u>TO-206-070</u>	Diss-O-Pad, TO-206, Rectangle, Notched, 0.49 Length, 0.195 Width, 0.07 Thick, Wax

Rectangular and Square Wash-Away Component Spacers

<u>TO-206-080</u>	Diss-O-Pad, TO-206, Rectangle, Notched, 0.49 Length, 0.195 Width, 0.08 Thick, Wax
<u>TO-206-090</u>	Diss-O-Pad, TO-206, Rectangle, Notched, 0.49 Length, 0.195 Width, 0.09 Thick, Wax
<u>TO-206-100</u>	Diss-O-Pad, TO-206, Rectangle, Notched, 0.49 Length, 0.195 Width, 0.10 Thick, Wax
<u>TO-206-120</u>	Diss-O-Pad, TO-206, Rectangle, Notched, 0.49 Length, 0.195 Width, 0.12 Thick, Wax
<u>TO-206-130</u>	Diss-O-Pad, TO-206, Rectangle, Notched, 0.49 Length, 0.195 Width, 0.13 Thick, Wax
<u>TO-206-150</u>	Diss-O-Pad, TO-206, Rectangle, Notched, 0.49 Length, 0.195 Width, 0.15 Thick, Wax
<u>TO-207-040</u>	Diss-O-Pad, TO-207, Rectangle, Notched, 0.59 Length, 0.195 Width, 0.04 Thick, Wax
<u>TO-207-050</u>	Diss-O-Pad, TO-207, Rectangle, Notched, 0.59 Length, 0.195 Width, 0.05 Thick, Wax
<u>TO-207-060</u>	Diss-O-Pad, TO-207, Rectangle, Notched, 0.59 Length, 0.195 Width, 0.06 Thick, Wax
<u>TO-207-070</u>	Diss-O-Pad, TO-207, Rectangle, Notched, 0.59 Length, 0.195 Width, 0.07 Thick, Wax
<u>TO-207-090</u>	Diss-O-Pad, TO-207, Rectangle, Notched, 0.59 Length, 0.195 Width, 0.09 Thick, Wax
<u>TO-207-100</u>	Diss-O-Pad, TO-207, Rectangle, Notched, 0.59 Length, 0.195 Width, 0.10 Thick, Wax
<u>TO-207-120</u>	Diss-O-Pad, TO-207, Rectangle, Notched, 0.59 Length, 0.195 Width, 0.12 Thick, Wax
<u>TO-207-130</u>	Diss-O-Pad, TO-207, Rectangle, Notched, 0.59 Length, 0.195 Width, 0.13 Thick, Wax
<u>TO-207-150</u>	Diss-O-Pad, TO-207, Rectangle, Notched, 0.59 Length, 0.195 Width, 0.15 Thick, Wax

Products

Component Mounts &
Spacers
Card Guides & Ejectors
Product Info Center

Applications

Audio Video
Communication
Industrial
Medical
Security
Transportation

News

Latest News
Archives

Distributors & Reps

About Us

Company Profile
Quality Assurance
Corporate Terms
& Conditions

Bivar Sites

Bivar Corporate
Enclosure
Hardware
LED Indication
LED Lighting
MyBivar

© 2014 Bivar Inc., All Rights Reserved.

Contact Us

Terms & Conditions | Privacy Policy | Sitemap



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[TO-206-050](#) [TO-100-040](#) [TO-100-050](#) [TO-100-060](#) [TO-100-070](#) [TO-100-080](#) [TO-100-090](#) [TO-100-100](#) [TO-100-120](#) [TO-100-130](#) [TO-100-150](#) [TO-100-200](#) [TO-101-040](#) [TO-101-050](#) [TO-101-060](#) [TO-101-070](#) [TO-101-080](#) [TO-101-090](#) [TO-101-100](#) [TO-101-120](#) [TO-101-130](#) [TO-101-150](#) [TO-102-040](#) [TO-102-050](#) [TO-102-060](#) [TO-102-070](#) [TO-102-090](#) [TO-102-100](#) [TO-102-120](#) [TO-102-130](#) [TO-116-040](#) [TO-116-050](#) [TO-116-060](#) [TO-116-070](#) [TO-116-080](#) [TO-116-090](#) [TO-116-100](#) [TO-116-110](#) [TO-116-120](#) [TO-116-130](#) [TO-116-150](#) [TO-116-180](#) [TO-116-200](#) [TO-117-040](#) [TO-117-050](#) [TO-117-060](#) [TO-117-070](#) [TO-117-080](#) [TO-117-090](#) [TO-117-100](#) [TO-117-120](#) [TO-117-130](#) [TO-117-140](#) [TO-117-150](#) [TO-117-160](#) [TO-118-040](#) [TO-118-050](#) [TO-118-060](#) [TO-118-070](#) [TO-118-080](#) [TO-118-090](#) [TO-118-100](#) [TO-118-110](#) [TO-118-120](#) [TO-118-130](#) [TO-118-150](#) [TO-118-160](#) [TO-118-170](#) [TO-118-200](#) [TO-120-040](#) [TO-120-050](#) [TO-120-060](#) [TO-120-070](#) [TO-120-090](#) [TO-120-100](#) [TO-120-120](#) [TO-121-040](#) [TO-121-050](#) [TO-121-060](#) [TO-121-070](#) [TO-121-090](#) [TO-121-100](#) [TO-121-120](#) [TO-200-040](#) [TO-200-050](#) [TO-200-060](#) [TO-200-080](#) [TO-200-090](#) [TO-200-100](#) [TO-200-120](#) [TO-200-130](#) [TO-200-150](#) [TO-201-040](#) [TO-201-050](#) [TO-201-050E](#) [TO-201-070](#) [TO-201-090](#) [TO-201-100](#) [TO-201-120](#) [TO-201-120E](#)