





ITEM	Q'TY	PART NUMBER	PART DESCRIPTION
1	1	FLP-P4-F	LENS CAP, FLEXIBLE LIGHT-PIPE, FLAT FACE
2	1	FLPS2031-X.XXX	2mm LIGHT PIPE CABLE, CUT LENGTH IN INCHES

REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	09/14/09	T. Y.
B	Updated Fiber In BOM	11/16/12	T. Y.



" L "	Tolerance
0.750" ~ 16.000"	±0.050"
16.100" ~ 40.000"	±0.150"
40.100" ~ 80.000"	±0.300"
80.100" ~ 3,940.0"	±0.5%

\*NOTE:  
ALLOWABLE CUT LENGTH IS UP TO 3 DECIMAL PLACES.

STANDARD TOLERANCE ( UNLESS OTHERWISE SPECIFIED )		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
<u>DECIMALS</u>	<u>ANGULAR</u>		
.X ± .1	X° ± 1°	 <b>TITLE:</b> LENS CAP / FLP ASSEMBLY, FLAT FACE	
.XX ± .02			
.XXX ± .010		<b>PART NO:</b> FLPF-XX.X	
<b>DESIGNED:</b> Brian Oliver	<b>DATE:</b> 09/14/09	<b>REVISION:</b> B	
<b>CHECKED:</b> Fred Jensen	<b>DATE:</b> 09/14/09	<b>CAGE CODE :</b> 32559   <b>SHEET #</b> 1 <b>OF</b> 1	
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[FLPF-6.0](#) [FLPF-0.750](#) [FLPF-24.0](#)