

Full or partial part number

Home / LED Indication / Flexible Light Pipes / FLP System



Flexible Light Pipes, LED Indication

FLP System

Available Options:

Adapter LED Color/Wavelength

Yellow 585nm/Green 565nm

Adapter Optical Fiber Diameter

2mm

Lens Size

5.1mm

Lens Profile

Low Profile

Panel Cutout

Round

Luminous Intensity

15/5 mcd

Optical Fiber Length

3.9 in.

Optical Fiber Color

Red

clear



Part Number:

FR4-3.9-SYG-F5P-2

Categories: FLEXIBLE LIGHT PIPES ,

LED INDICATION

Request Sample

Check Stock

Download Data Sheet

Download 3D Drawing

Download RoHS Docs

View List →

Additional information

|                                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
|--------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Adapter LED Color/Wavelength   | Amber/605nm, Amber/620nm, Blue/466nm, Blue/470nm, Green/563nm, Green/568nm, Green/570nm, Green568nm, N/A, Orange/620nm, Red 625nm / Green 568nm, Red 625nm/Green 568nm, Red 645nm / Green 568nm, Red/625nm, Red/640nm, Red/640nmnm, Red/645nm, Red/660nm, Turquoise/500nm, White/6000K, White/6500K, Yellow 585nm / Green 565nm, Yellow 585nm/Green 565nm, Yellow 590nm / Green 568nm, Yellow 590nm/Green 515nm, Yellow 590nm/Green 568nm, Yellow 590nm/Green568nm, Yellow/585nm, Yellow/588nm, Yellow/590nm |
| Adapter Optical Fiber Diameter | 1mm, 2mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Lens Size                      | 3.2 x 6.4 mm, 3.2mm x 6.4mm, 4.0mm, 4.2mm, 5.1mm, 6.0mm IP67, 6.7mm x 4.2mm, 7.0mm, 9.0mm IP67, N/A                                                                                                                                                                                                                                                                                                                                                                                                          |
| Lens Profile                   | Dome, Flat, Low Profile, Low Profile Diffused, Low Profile Fresnel, N/A                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Panel Cutout                   | N/A, Oval, Rectangular, Round                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Luminous Intensity             | 100mcd/60mcd, 120mcd, 15/5 mcd, 1500mcd, 15mcd/5mcd, 200mcd, 2200mcd, 250mcd, 300mcd, 350mcd, 400/80 mcd, 400mcd, 50mcd, 50mcd/50mcd, 6000mcd, 600mcd, 60mcd, 65mcd, 6mcd/8mcd, 70mcd, 800mcd, 8mcd/8mcd, 900mcd, N/A                                                                                                                                                                                                                                                                                        |
| Optical Fiber Length           | 1.0 in., 1.5 in., 10.0 in., 100.0 in., 118.0 in., 12.0 in., 12.3 in., 13.0 in., 14.0 in., 15.0 in., 18.0 in., 2.0 in., 2.1 in., 2.3 in., 2.5 iin., 2.5 in., 2.9 in., 24.0 in., 3.0 in., 3.25 in., 3.28 in., 3.5 in., 3.9 in., 36.0 in., 4.0 in., 4.1 in., 4.5 in., 5.0 in., 6.0 in., 6.5 in., 6.7 in., 8.0 in., 9.0 in., 9.5 in., N/A                                                                                                                                                                        |
| Optical Fiber Color            | Black, Blue, Green, N/A, Red, White, Yellow                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |



Keep up with Bivar

Email\*

Subscribe

- Products
- LED Indication
- Positioning Components
- Securing Circuit Cards
- Linear LED Lighting
- Smart Technology

- Solutions
- Engineered Solutions
- Industries
- Security & Surveillance
- Communication
- Industry 4.0

- Company
- Contact Us
- About Us
- How to Buy

BIVAR CORPORATE OFFICE

4 Thomas  
Irvine, CA 92618

TEL: 800-767-3652  
FAX: 949-951-3974

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[FR4-3.9-SYG-F5P-2](#)