
		REVISIONS			
		REV.	DESCRIPTION	DATE	APPROVED
		A	INITIAL RELEASE	03/02/17	D.N.



NOTES:

MATERIALS:

1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
2. CONTACT & SPRING = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
3. LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
4. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

1. CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50μin MIN, GRADE C, OVER 100 TO 200μin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.
2. SPRING = NICKEL PLATE PER AMS-QQ-N-290, CLASS 1, GRADE G, EXCEPT 100 TO 200μin THICK OVER 50 TO 100μin THICK COPPER PER AMS 2418.
3. ALL OTHER METAL PARTS = GOLD PLATE PER ASTM B488-11, TYPE II, 30μin MIN, GRADE C OVER 100 TO 200μin COPPER STRIKE PER AMS 2418.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN:	DATE		Property of Radiall					
		D.N.	03/02/17		This document cannot be reproduced or communicated to a third party without prior written permission of RADIALL.					
DECIMAL		CHKD:	DATE	SLB STRAIGHT FEMALE PLUG BULKHEAD FLOAT MOUNT CLAMP TYPE FOR .085 S/R & SIMILAR CABLES						
		N.D.	03/02/17							
ANGLE		APVD:	DATE	SIZE				FSCM NO.	DWG NO.	REV
		J.M.	03/02/17							
REFERENCE:		MATERIALS & FINISHES:		3028-1541-610						
ORIGINATED: D.N.		SEE NOTES		A						
DATE: 03/02/17				19505						
				6:1						
				THIRD ANGLE PROJECTION						
				SHEET 1 OF 1						

3028-1541-610

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[3028-1541-610](tel:3028-1541-610)