



PANEL CUT OUT



inches		
	Maxi	mini
A	.505	.509
B	.471	.475

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	05/03/18	D.N.



NOTES:

MATERIALS:

1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
2. CONTACTS = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
3. GASKET = SILICONE RUBBER 45-55 DUROMETER DOW CORNING SILASTIC 250.
4. LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
5. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

1. CONTACTS = GOLD PLATE PER ASTM B488-11, TYPE II, 50μin MIN, GRADE C, OVER 100 TO 200μin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.
2. ALL OTHER METAL PARTS = GOLD PLATE PER ASTM B488-11, TYPE II, 30μin MIN, GRADE C OVER 100 TO 200μin COPPER STRIKE PER AMS 2418.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN:	DATE	Property of Radiall This document cannot be reproduced or communicated to a third party without prior a RADIALl company written permission of RADIALl. 				
		D.N.	05/03/18					
DECIMAL	ANGLE	CHKD:	DATE	BNC STRAIGHT JACK BULKHEAD FRONT MOUNT TO 75 OHM SCREW-ON FEMALE PLUG				
		C.E.	05/03/18					
		APVD:	DATE					
		J.M.	05/03/18					
REFERENCE: ORIGINATED: D.N. DATE: 05/03/18		MATERIALS & FINISHES: SEE NOTES		SIZE	FSCM NO.	DWG NO.	REV	
				A	19505	5515-1501-000	A	
				SCALE 3:1		THIRD ANGLE PROJECTION		SHEET 1 OF 1

5515-1501-000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[5515-1501-000](#)