


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06/20/12	J.S.




NOTES:

MATERIALS:

1. BODIES & NUT = STAINLESS STEEL PER ASTM A582, ALLOY 303, CONDITION "A".
2. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
3. CONTACT = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
4. LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
5. CAP = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

1. CONTACT = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 1, GRADE C, OVER .00010 TO .00020 STRESS FREE SULFAMATE NICKEL PER QQ-N-290.
2. CAP & LOCKWASHER = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 0, GRADE C, OVER .00010 TO .00020 COPPER STRIKE PER MIL-C-14550.
3. ALL OTHER METAL PARTS = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 0, GRADE C, OVER .000050 TO .00010 STRESS FREE NICKEL PER QQ-N-290.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: J.S.	DATE 06/20/12	 Property of Radiall This document cannot be reproduced or communicated to a third party without prior written permission of RADIALL.			
		CHKD: M.J.	DATE 06/20/12				
DECIMAL	ANGLE	APVD: J.M.	DATE 06/20/12	SMA RIGHT ANGLE JACK BULKHEAD DIRECT SOLDER TYPE FOR .141 S/R & SIMILAR CABLES			
REFERENCE:		MATERIALS & FINISHES: SEE NOTES					
ORIGINATED: J.S. DATE: 06/20/12		SIZE A	FSCM NO. 19505	DWG NO. 9613-1563-009	REV A	THIRD ANGLE PROJECTION	
		SCALE 6:1					
						SHEET 1 OF 1	

9613-1563-009

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

9613-1563-009