



REMOVABLE CONTACT

PACKAGING PER 100

R280.473.100

Series :
ACCESSOIRE



—
SCALE : 1/1

All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
BODY	-	-
CENTER CONTACT	DILVER P1	.GOLD 1.3 OVER NICKEL 2
OUTER CONTACT	-	-
INSULATOR	-	-
GASKET	-	-
OTHERS PARTS	-	-
-	-	-
-	-	-

Issue : 0741 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary



RADIALL®

REMOVABLE CONTACT

PACKAGING PER 100

R280.473.100Series :
ACCESSOIREPACKAGING

Standard	Unit	Other
	'W' option	Contact us

SPECIFICATIONCABLE ASSEMBLY

Stripping	a	b	c	d	e	f
mm						

ELECTRICAL CHARACTERISTICS

Impedance		Ω
Frequency		GHz
VSWR	+	x F(GHz) Maxi
Insertion loss		$\sqrt{F}$ (GHz) dB Maxi
RF leakage	- (	-F(GHz)) dB Maxi
Voltage rating		Veff Maxi
Dielectric withstanding voltage		Veff mini
Insulation resistance		M Ω mini

Assembly instruction :

Recommended cable(s)

MECHANICAL CHARACTERISTICS

Recommended torque		
Panel nut		N.cm
Clamp nut		N.cm
A/F clamp nut		mm
Mating life		Cycles mini
Weight	0,0016	g

Cable retention

- pull off

N mini

- torque

N.cm

TOOLING

Part Number	Description	Hexagon
.	.	.

OTHER CHARACTERISTICSENVIRONMENTAL

Operating temperature	-65/+165 °C
Panel leakage	

Issue : 0741 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary

**RADIALL**®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[R280473100W](#)