




TWO INSULATED WASHERS


PACKAGING PER 100

R280.902.000

Series : **ACC-COAX**



Scale 1/1



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (µm)
BODY	white Nylon 20% glass fiber	-
CENTER CONTACT	-	-
OUTER CONTACT	-	-
INSULATOR	-	-
GASKET	-	-
OTHERS PARTS	-	-
-	-	-
-	-	-

Issue : 0726 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary



TWO INSULATED WASHERS**PACKAGING PER 100****R280.902.000**

Series : ACC-COAX

PACKAGING

Standard	Unit	Other
	‘W’ option	Contact us

ELECTRICAL CHARACTERISTICS

Impedance		Ω
Frequency		GHz
VSWR	+	x F(GHz) Maxi
Insertion loss		\sqrt{F} (GHz) dB Maxi
RF leakage	- (-F(GHz)) dB Maxi
Voltage rating		Veff Maxi
Dielectric withstanding voltage		Veff mini
Insulation resistance		M Ω mini

MECHANICAL CHARACTERISTICS

Recommended torque		
Panel nut		N.cm
Clamp nut		N.cm
A/F clamp nut		mm
Mating life		Cycles mini
Weight	0,5300	g

ENVIRONMENTAL

Operating temperature	- °C
Panel leakage	

SPECIFICATION**CABLE ASSEMBLY**

Stripping	a	b	c	d	e	f
mm						

Assembly instruction :

Recommended cable(s)

Cable retention

- pull off

N mini

- torque

N.cm

TOOLING

Part Number	Description	Hexagon
.	.	.

OTHER CHARACTERISTICS

-

Issue : 0726 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[R280902000](#)