


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	ECO #6681	05/25/07	A.D.M.



NOTES:

MATERIALS:

1. BODY = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.
2. INSULATOR = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
3. CONTACT = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.

FINISHES:

1. BODY = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 0, GRADE C, OVER .00010 TO .00020 COPPER STRIKE PER MIL-C-14550.
2. CONTACT = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 1, GRADE C, OVER .00010 TO .00020 STRESS FREE SULFAMATE NICKEL PER QQ-N-290.

Property of Radiall Incorporated
This document cannot be reproduced or
communicated to a third party without prior
written permission of RADIALl Incorporated.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: A.D.M.	DATE 05/25/07	 APPLIED ENGINEERING PRODUCTS 104 John W. Murphy Dr. New Haven, CT 06513	
		CHKD: D.N.	DATE 05/25/07		
DECIMAL	ANGLE	APVD: J.M.	DATE 05/25/07	SSMB STRAIGHT JACK P.C.B. MOUNT RECEPTACLE	
REFERENCE:		MATERIALS & FINISHES: SEE NOTES			
ORIGINATED: D.N. DATE: 08/15/90		SIZE A	FSCM NO. 19505	DWG NO. 7209-1511-000	REV A
		SCALE 8:1		THIRD ANGLE PROJECTION	SHEET 1 OF 1

7209-1511-000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[7209-1511-000](#)