



Cable assemblies available from stock

BNC




Part number	Length (cm)	Cable Type (mm/Ω)	Connector type	Operating Temperature(°C)	Frequency range(GHz)
R 285 414	50	RG58	2 Straight plugs R 141 082 + 2 Black sleeves	-40 + 85	DC - 3
R 285 415	100	or		-40 + 85	DC - 3
R 285 416	150	KX15		-40 + 85	DC - 3
R 285 417	200	(5/50)		-40 + 85	DC - 3

BNC commercial



Part number	Length (cm)	Cable Type (mm/Ω)	Connector type	Operating Temperature(°C)	Frequency range(GHz)
R 285 424	50	RG 58	2 Straight plugs R 141 082 161 + 2 Black sleeves	-25 + 70	DC - 1
R 285 425	100	or		-25 + 70	DC - 1
R 285 426	150	KX15		-25 + 70	DC - 1
R 285 427	200	(5/50)		-25 + 70	DC - 1
R 285 434	50	RG 59 (6/75)	2 Straight plugs R 142 085 161 + 2 Black sleeves	-25 + 70	DC - 1
R 285 435	100			-25 + 70	DC - 1
R 285 436	150			-25 + 70	DC - 1
R 285 437	200			-25 + 70	DC - 1
R 285 405	100	RG 62 (6/93)	2 Straight plugs R 142 085 161 + 2 Black sleeves	-25 + 70	DC - 1
R 285 407	200			-25 + 70	DC - 1
R 285 408	300			-25 + 70	DC - 1
R 285 409	400			-25 + 70	DC - 1
R 285 410	500			-25 + 70	DC - 1

1.6/5.6



Part number	Length (cm)	Cable Type (mm/Ω)	Connector type	Operating Temperature(°C)	Frequency range(GHz)
R 285 344	50	(6/75 green)	2 Straight plugs R 129 084 + 2 Black sleeves	-40 + 85	DC - 1.5
R 285 345	100			-40 + 85	DC - 1.5
R 285 346	150			-40 + 85	DC - 1.5
R 285 347	200			-40 + 85	DC - 1.5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[R285417000](#) [R285415000](#)