



DESIGNED & DIMENSIONED  
IN MILLIMETERS[INCHES]

## -01 LEAD STYLE

MS-01-02-L SHOWN  
(SEE NOTE 8)"A"±0.05 [.002] REF  
(SEE TABLE 1)FIG 1  
SO-XXXX-01-01-02-L SHOWN

- NOTES:
1. DELETED
  2. DELETED
  3. DELETED
  4. STANDOFFS TO BE USED WITH 1.57[.062]MIN THICK BOARDS.
  5. NOTE DELETED..
  6. -01 LEAD STYLE ONLY AVAILABLE FOR BOARD STACK HEIGHTS -0515 THRU -0965.
  7. -02 LEAD STYLE ONLY AVAILABLE FOR TOOLED BOARD STACK HEIGHTS, SEE TABLE 3, SHT 2 FOR TOOLED STACKS.
  8. COMPONENTS ARE TO BE PACKAGED IN SEPARATE BAGS UNASSEMBLED AND NOT LABELED. COMBINE SEPARATE BAGS IN ONE LARGER BAG WITH PART NUMBER AND QUANTITY.
  9. -04 LEAD STYLE ONLY AVAILABLE FOR BOARD STACK HEIGHT -0165, -0175, -0310 AND -0318.
  10. -03 LEAD STYLE ONLY AVAILABLE FOR TOOLED BOARD STACK HEIGHTS, SEE TABLE 4, SHT 3.
  11. NOTE DELETED.
  12. REPRESENTS A CRITICAL DIMENSION.
  13. STANDOFFS ARE DESIGNED .15MM LONGER THAN CONNECTOR STACK HEIGHTS TO ALLOW FOR PROCESSING VARIABLES.
  14. TORQUE TO 2.5 – 3.5 IN\*LBS TO SECURE FASTENER IN A STATIC ENVIRONMENT ASSUMING RECOMMENDED BOARD TO BOARD DISTANCES ARE ACHIEVED WITHOUT DAMAGE TO THE PCB, HARDWARE OR OTHER COMPONENTS.
  15. FOR -L OPTION, SPREAD LOCKING COMPOUND OVER 5 THREADS OR AT LEAST 0.105".

## BOARD STACK HEIGHT

-0165,-0175,-0310,-0318,-0515,-0690,  
-0715,-0815,-0865,-0915,-0965,-1015,  
-1115,-1215,-1315,-1415,-1515,-1524,  
-1615,-1715,-1890,-1915,-2015,-2200,  
-2215,-2515,-3015

## LEAD STYLE

- 01: FEMALE THREAD/PRESS-IN  
(SEE FIG. 1, SHT. 1)  
SEE NOTE 6
- 02: MALE/MALE THREADED  
(SEE FIG 2, SHT. 2)  
SEE NOTE 7
- 03: MALE/FEMALE THREADED  
(SEE FIG. 3, SHT. 3)  
SEE NOTE 10
- 04: FEMALE/PRESS-IN  
(SEE FIG.4, SHT.4)  
SEE NOTE 9
- 05: FEMALE/FEMALE  
THREADED  
(SEE FIG. 5 SHT. 5)
- 06: MALE/MALE THREADED  
(SEE FIG 6, SHT. 6)

TABLE 7

| STYLE | THREADING    |
|-------|--------------|
| -01   | #4-40 UNC 2A |
|       | #4-40 UNC 2B |
| -02   | M3 x 0.5 6g  |
|       | M3 x 0.5 6H  |
| -03   | M2 x 0.4 6g  |
|       | M2 x 0.4 6H  |

TABLE 1

| 01 LEAD STYLE AVAILABILITY |              |
|----------------------------|--------------|
| BOARD STACK HEIGHT         | "A"          |
| -0515                      | 5.15 [.0203] |
| -0575                      | 5.75 [.0226] |
| -0600                      | 6.00 [.0236] |
| -0690                      | 6.90 [.0272] |
| -0715                      | 7.15 [.0281] |
| -0815                      | 8.15 [.0321] |
| -0865                      | 8.65 [.0341] |

## SO-XXXX-XX-XX-XX-X-X

## KIT OPTION

-N: NO HARDWARE  
(STANDOFF ONLY; SEE TABLE 2)  
LEAVE BLANK FOR KIT

## LOCKING OPTION

-L: LOCKING COMPOUND  
(NOT AVAILABLE WITH -04 OR -N OPTION  
ON -01 AND -05 LEAD STYLES)

## MATERIAL

-01: 6061 ALUMINUM  
-02: 303 STAINLESS STEEL

## THREADING

-01: #4-40  
-02: M3 x 0.5 x 4.76mm  
-03: M2 x 0.4 x 4.76mm


RECOMMENDED BOARD  
CUTOUT (PRESS-IN)

TABLE 2 - BOM

| FINISHED GOOD        | STANDOFF               | QTY | SCREW      | QTY | NUT      | QTY |
|----------------------|------------------------|-----|------------|-----|----------|-----|
| SO-XXXX-01-01-XX     | SUB-SO-XXXX-01-01-XX   | 1   | MS-01-XX   | 1   | N/A      |     |
| SO-XXXX-01-01-XX-N   | SUB-SO-XXXX-01-01-XX   | 1   | N/A        |     | N/A      |     |
| SO-XXXX-01-01-XX-L   | SUB-SO-XXXX-01-01-XX   | 1   | MS-01-XX-L | 1   | N/A      |     |
| SO-XXXX-02-01-XX     | SUB-SO-XXXX-02-01-XX   | 1   | N/A        |     | SN-01-XX | 2   |
| SO-XXXX-02-01-XX-N   | SUB-SO-XXXX-02-01-XX   | 1   | N/A        |     | N/A      |     |
| SO-XXXX-02-01-XX-L   | SUB-SO-XXXX-02-01-XX-L | 1   | N/A        |     | SN-01-XX | 2   |
| SO-XXXX-02-01-XX-L-N | SUB-SO-XXXX-02-01-XX-L | 1   | N/A        |     | N/A      |     |
| SO-XXXX-03-01-XX     | SUB-SO-XXXX-03-01-XX   | 1   | MS-01-XX   | 1   | SN-01-XX | 1   |
| SO-XXXX-03-01-XX-N   | SUB-SO-XXXX-03-01-XX   | 1   | N/A        |     | N/A      |     |
| SO-XXXX-03-01-XX-L   | SUB-SO-XXXX-03-01-XX-L | 1   | MS-01-XX-L | 1   | SN-01-XX | 1   |
| SO-XXXX-03-01-XX-L-N | SUB-SO-XXXX-03-01-XX-L | 1   | N/A        |     | N/A      |     |
| SO-XXXX-05-01-XX     | SUB-SO-XXXX-05-01-XX   | 1   | MS-01-XX   | 2   | N/A      |     |
| SO-XXXX-05-01-XX-N   | SUB-SO-XXXX-05-01-XX   | 1   | N/A        |     | N/A      |     |
| SO-XXXX-05-01-XX-L   | SUB-SO-XXXX-05-01-XX   | 1   | MS-01-XX-L | 2   | N/A      |     |
| SO-XXXX-01-02-XX     | SUB-SO-XXXX-01-02-XX   | 1   | MS-02-XX   | 1   | N/A      |     |
| SO-XXXX-01-02-XX-N   | SUB-SO-XXXX-01-02-XX   | 1   | N/A        |     | N/A      |     |
| SO-XXXX-01-02-XX-L   | SUB-SO-XXXX-01-02-XX   | 1   | MS-02-XX-L | 1   | N/A      |     |
| SO-XXXX-02-02-XX     | SUB-SO-XXXX-02-02-XX   | 1   | N/A        |     | SN-02-XX | 2   |
| SO-XXXX-02-02-XX-N   | SUB-SO-XXXX-02-02-XX   | 1   | N/A        |     | N/A      |     |
| SO-XXXX-02-02-XX-L   | SUB-SO-XXXX-02-02-XX-L | 1   | N/A        |     | SN-02-XX | 2   |
| SO-XXXX-02-02-XX-L-N | SUB-SO-XXXX-02-02-XX-L | 1   | N/A        |     | N/A      |     |
| SO-XXXX-02-03-XX-L   | SUB-SO-XXXX-02-03-XX-L | 1   | N/A        |     | SN-03-XX | 2   |
| SO-XXXX-03-02-XX     | SUB-SO-XXXX-03-02-XX   | 1   | MS-02-XX   | 1   | SN-02-XX | 1   |
| SO-XXXX-03-02-XX-N   | SUB-SO-XXXX-03-02-XX   | 1   | N/A        |     | N/A      |     |
| SO-XXXX-03-02-XX-L   | SUB-SO-XXXX-03-02-XX-L | 1   | MS-02-XX-L | 1   | SN-02-XX | 1   |
| SO-XXXX-03-02-XX-L-N | SUB-SO-XXXX-03-02-XX-L | 1   | N/A        |     | N/A      |     |
| SO-XXXX-05-02-XX     | SUB-SO-XXXX-05-02-XX   | 1   | MS-02-XX   | 2   | N/A      |     |
| SO-XXXX-05-02-XX-N   | SUB-SO-XXXX-05-02-XX   | 1   | N/A        |     | N/A      |     |
| SO-XXXX-05-02-XX-L   | SUB-SO-XXXX-05-02-XX   | 1   | MS-02-XX-L | 2   | N/A      |     |
| SO-XXXX-05-03-XX     | SUB-SO-XXXX-05-03-XX   | 1   | MS-06-XX   | 2   | N/A      |     |
| SO-XXXX-05-03-XX-L   | SUB-SO-XXXX-05-03-XX   | 1   | MS-06-XX-L | 2   | N/A      |     |

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN MILLIMETERS

TOLERANCES ARE:

DECIMALS

X.X: ±0.25 [.01]

X.XX: ±0.05 [.002]

ANGLES

2°

## \* PROPRIETARY NOTE \*

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL:

SEE PART CALL OUT FOR MATERIAL

DO NOT SCALE DRAWING

SHEET SCALE: 1:0.333333

DESCRIPTION:

BOARD TO BOARD STANDOFF

DWG. NO.

SO-XXXX-XX-XX-XX-X

BY: T.NEWTON 12/6/2007

SHEET 1 OF 6





FIG 2  
SO-XXXX-02-01-02-X SHOWN



| TABLE 3                    |              |
|----------------------------|--------------|
| 02 LEAD STYLE AVAILABILITY |              |
| BOARD STACK HEIGHT         | "B"          |
| -0515                      | 5.15[.203]   |
| -0715                      | 7.15[.282]   |
| -0865                      | 8.65[.341]   |
| -1015                      | 10.15[.400]  |
| -1115                      | 11.15[.439]  |
| -1215                      | 12.15[.478]  |
| -1315                      | 13.15[.518]  |
| -1415                      | 14.15[.557]  |
| -1515                      | 15.15[.597]  |
| -1524                      | 15.24[.600]  |
| -1615                      | 16.15[.636]  |
| -1715                      | 17.15[.675]  |
| -1890                      | 18.90[.744]  |
| -1915                      | 19.15[.754]  |
| -2015                      | 20.15[.793]  |
| -2215                      | 22.15[.872]  |
| -2515                      | 25.15[.990]  |
| -3015                      | 30.15[1.187] |

|                                                                                                                                                                                                                                                                                                                                                                                                                                               |                                                                                                                        |                    |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------|--------------------|
| * PROPRIETARY NOTE<br>THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC. |                                                                                                                        |                    |
|                                                                                                                                                                                                                                                                                                                                                                                                                                               | 520 PARK EAST BLVD, NEW ALBANY, IN 47150<br>PHONE: 812-944-6733 FAX: 812-948-5047<br>e-Mail info@SAMTEC.com code 55322 |                    |
|                                                                                                                                                                                                                                                                                                                                                                                                                                               | DESCRIPTION: BOARD TO BOARD STANDOFF                                                                                   |                    |
| DO NOT SCALE DRAWING                                                                                                                                                                                                                                                                                                                                                                                                                          | DWG. NO.                                                                                                               | SO-XXXX-XX-XX-XX-X |
| SHEET SCALE: 1:0.333333                                                                                                                                                                                                                                                                                                                                                                                                                       | BY: T.NEWTON 12/6/2007                                                                                                 | SHEET 2 OF 6       |





FIG 3  
SO-XXXX-03-01-02-X SHOWN  
(SAME AS -02 LEAD STYLE,  
EXCEPT WHERE STATED)

| TABLE 4                       |              |
|-------------------------------|--------------|
| 03 LEAD STYLE<br>AVAILABILITY |              |
| BOARD<br>STACK<br>HEIGHT      | "C"          |
| -0815                         | 8.15[.321]   |
| -0865                         | 8.65[.341]   |
| -0915                         | 9.15[.360]   |
| -0965                         | 9.65[.380]   |
| -1015                         | 10.15[.400]  |
| -1115                         | 11.15[.439]  |
| -1215                         | 12.15[.478]  |
| -1315                         | 13.15[.518]  |
| -1415                         | 14.15[.557]  |
| -1515                         | 15.15[.597]  |
| -1524                         | 15.24[.600]  |
| -1615                         | 16.15[.636]  |
| -1715                         | 17.15[.675]  |
| -1890                         | 18.90[.744]  |
| -1915                         | 19.15[.754]  |
| -2015                         | 20.15[.793]  |
| -2200                         | 22.00[.866]  |
| -2215                         | 22.15[.872]  |
| -2515                         | 25.15[.990]  |
| -3015                         | 30.15[1.187] |



|                                                                                                                                                                                                                                                                                                                                                                                                                                                            |  |                                                                                                                                                                                                                       |              |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|
| <p>* PROPRIETARY NOTE *</p> <p>THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.</p> |  |  <p>520 PARK EAST BLVD, NEW ALBANY, IN 47150<br/>PHONE: 812-944-6733 FAX: 812-948-5047<br/>e-Mail info@SAMTEC.com code 55322</p> |              |
| DO NOT SCALE DRAWING                                                                                                                                                                                                                                                                                                                                                                                                                                       |  | DESCRIPTION: BOARD TO BOARD STANDOFF                                                                                                                                                                                  |              |
| SHEET SCALE: 3:1                                                                                                                                                                                                                                                                                                                                                                                                                                           |  | DWG. NO. SO-XXXX-XX-XX-XX-X                                                                                                                                                                                           |              |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                            |  | BY: T.NEWTON 12/6/2007                                                                                                                                                                                                | SHEET 3 OF 6 |

-04 LEAD STYLE







FIG 4  
SO-XXXX-04-01-02 SHOWN




RECOMMENDED BOARD  
CUTOUT (PRESS-IN)

| TABLE 5                       |             |
|-------------------------------|-------------|
| 04 LEAD STYLE<br>AVAILABILITY |             |
| BOARD<br>STACK<br>HEIGHT      | "D"         |
| -0165                         | 1.65 [.065] |
| -0175                         | 1.75 [.069] |
| -0310                         | 3.10 [.122] |
| -0318                         | 3.18 [.125] |

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |  |                                                                                                                                 |  |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------------------------------------------------|--|
| <p>* <b>PROPRIETARY NOTE</b> *</p> <p>THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.</p> |  | <p>520 PARK EAST BLVD, NEW ALBANY, IN 47150<br/>PHONE: 812-944-6733 FAX: 812-948-5047<br/>e-Mail info@SAMTEC.com code 55322</p> |  |
| DO NOT SCALE DRAWING                                                                                                                                                                                                                                                                                                                                                                                                                                              |  | DESCRIPTION: BOARD TO BOARD STANDOFF                                                                                            |  |
| SHEET SCALE: 1:0.333333                                                                                                                                                                                                                                                                                                                                                                                                                                           |  | DWG. NO. SO-XXXX-XX-XX-XX-X                                                                                                     |  |
| BY: T.NEWTON 12/6/2007                                                                                                                                                                                                                                                                                                                                                                                                                                            |  | SHEET 4 OF 6                                                                                                                    |  |

-05 LEAD STYLE



SUB-SO-XXXX-05-01-02-X  
(SEE NOTE 8)







FIG 5  
SO-XXXX-05-01-02-X SHOWN  
(SAME AS -02 LEAD STYLE,  
EXCEPT WHERE STATED)


| TABLE 6                       |             |
|-------------------------------|-------------|
| 05 LEAD STYLE<br>AVAILABILITY |             |
| BOARD<br>STACK<br>HEIGHT      | "C"         |
| -0515                         | 5.15[.002]  |
| -0915                         | 9.15[.004]  |
| -1015                         | 10.15[.400] |
| -1115                         | 11.15[.440] |
| -1215                         | 12.15[.492] |
| -1315                         | 13.15[.518] |
| -1415                         | 14.15[.557] |
| -1515                         | 15.15[.597] |
| -1524                         | 15.24[.600] |
| -1615                         | 16.15[.636] |
| -1715                         | 17.15[.675] |
| -1890                         | 18.90[.744] |
| -1915                         | 19.15[.754] |
| -2015                         | 20.15[.793] |
| -2200                         | 22.00[.866] |
| -2215                         | 22.15[.872] |
| -2515                         | 25.15[.990] |

|                                                                                                                                                                                                                                                                                                                                                                                                                                                               |                                                    |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------|
| <p><b>PROPRIETARY NOTE</b></p> <p>THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.</p> |                                                    |
| <p>DO NOT SCALE DRAWING</p> <p>SHEET SCALE: 1:1</p>                                                                                                                                                                                                                                                                                                                                                                                                           | <p><b>DESCRIPTION:</b> BOARD TO BOARD STANDOFF</p> |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                               | <p>DWG. NO. <b>SO-XXXX-XX-XX-XX-X</b></p>          |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                               | <p>BY: T.NEWTON 12/6/2007 SHEET 5 OF 6</p>         |

-06 LEAD STYLE



| TABLE 8                    |            |
|----------------------------|------------|
| 06 LEAD STYLE AVAILABILITY |            |
| BOARD STACK HEIGHT         | "B"        |
| -0375                      | 3.75[.148] |



RECOMMENDED BOARD CUTOUT (M2 x 0.4)

FIG 6  
SO-XXXX-06-03-02-X SHOWN  
(SAME AS -02 LEAD STYLE,  
EXCEPT WHERE STATED)

|                                                                                                                                                                                                                                                                                                                                                                                                                                                               |  |                                                                                                                                                                                                                       |              |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|
| <p><b>PROPRIETARY NOTE</b></p> <p>THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.</p> |  |  <p>520 PARK EAST BLVD, NEW ALBANY, IN 47150<br/>PHONE: 812-944-6733 FAX: 812-948-5047<br/>e-Mail info@SAMTEC.com code 55322</p> |              |
| DO NOT SCALE DRAWING                                                                                                                                                                                                                                                                                                                                                                                                                                          |  | DESCRIPTION: BOARD TO BOARD STANDOFF                                                                                                                                                                                  |              |
| SHEET SCALE: 4:1                                                                                                                                                                                                                                                                                                                                                                                                                                              |  | DWG. NO. SO-XXXX-XX-XX-XX-X                                                                                                                                                                                           |              |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                               |  | BY: T.NEWTON 12/6/2007                                                                                                                                                                                                | SHEET 6 OF 6 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[SO-0865-02-02-01-L-N](#) [SO-2215-03-02-02-L-N](#) [SO-1515-03-02-02-L-N](#)