

DO NOT
SCALE FROM
THIS PRINT

BSW-1XX-X4-X-X-X

No OF POSITIONS
-02 THRU -36 (PER ROW)
LEAD STYLE
-04: C-8-5-X
(STANDARD I/W FORCES)
-24: C-17-5-X
(LOW I/W FORCES)

OPTION
-S: STANDOFFS
(USE BSW-36-X-S,
SEE TABLE 1)
ROW SPECIFICATION
SEE TABLE 1

PLATING SPECIFICATION

-G: 20µ" GOLD IN CONTACT AREA, 3µ" GOLD ON TAIL
-T: MATTE TIN CONTACT AND TAIL (STYLE -04 ONLY)
-S: 30µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
-H: 30µ" HEAVY GOLD IN CONTACT AREA, 3µ" GOLD ON TAIL
(STYLE -04 ONLY)
-L: 10µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL








TABLE 1				
ROW / OPTION	"B"	"C"	"D"	USE BODY
- D	.100 [2.54]	—	.165 [4.19]	BSW-36-D
- S	.100 [2.54]	—	.165 [4.19]	BSW-36-S
*- M	.150 [3.81]	—	.125 [3.18]	BSW-36-M
*- D - S	.100 [2.54]	.15 [3.8]	—	BSW-36-D-S
*- S - S	.100 [2.54]	.15 [3.8]	—	BSW-36-S-S

*=Existing customers only






CONTACT
SCALE 1.5:1
CRITICAL 1 DIMENSION MUST BE VERIFIED AT
BEGINNING, MIDDLE, AND END OF EACH LOT

FINAL ASSEMBLY

- NOTES:
1. Ⓢ REPRESENTS A CRITICAL DIMENSION.
 2. MINIMUM PUSHOUT FORCE: 3lbs.
 3. MAXIMUM ALLOWABLE BOW: T/B .003[.08] INCH/INCH, S/S .008[0.20] INCH/INCH AFTER ASSEMBLY.
 4. "END WALLS" AFTER CUTTING SHOULD BE .023[.58]
 5. MAXIMUM CUT FLASH: .010[.25].
 6. THE IDENTIFICATION SIDE IS TO BE DOWN OR AGAINST THE FORM TOOLING.

POSITION NUMBER LAYOUT



UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.
TOLERANCES ARE:
DECIMALS ANGLES
.XX: ±.01 [.3] 2°
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.051]

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

MATERIAL:
INSULATOR: PET, UL 94 VO, COLOR: BLACK
CONTACT: PHOS BRONZE




DESCRIPTION:
.100 BOTTOM MOUNT SOCKET ASSEMBLY

DWG. NO. BSW-1XX-X4-X-X-X

BY: PURVIS 03/31/1998 SHEET 1 OF 2



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322



FINAL ASSEMBLY

• PROPRIETARY NOTE •
THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:
.100 BOTTOM MOUNT SOCKET ASSEMBLY

DWG. NO. BSW-1XX-X4-X-X-X

BY: PURVIS 03/31/1998 SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[BSW-126-24-S-D](#) [BSW-129-24-S-S](#) [BSW-133-04-S-D](#) [BSW-133-24-S-S](#) [BSW-111-04-L-S](#) [BSW-117-24-L-D](#) [BSW-121-04-L-D](#) [BSW-116-04-L-D](#) [BSW-111-24-S-D](#) [BSW-121-04-T-D](#) [BSW-122-24-G-S](#) [BSW-123-24-L-S](#) [BSW-121-24-S-S](#) [BSW-131-24-S-S](#) [BSW-115-24-L-D](#) [BSW-118-04-L-D](#) [BSW-121-24-S-D](#) [BSW-131-24-S-D](#) [BSW-11-04-G-S](#) [BSW-111-04-L-D](#) [BSW-115-04-L-D](#) [BSW-122-24-L-S](#) [BSW-115-24-G-S](#) [BSW-123-24-S-S](#) [BSW-135-24-S-S](#) [BSW-131-04-S-S](#) [BSW-119-24-S-D](#) [BSW-119-24-S-S](#) [BSW-130-24-S-S](#) [BSW-133-24-S-D](#) [BSW-111-24-L-D](#) [BSW-117-04-L-D](#) [BSW-119-04-L-D](#) [BSW-121-04-L-S](#) [BSW-125-24-L-S](#) [BSW-117-24-G-S](#) [BSW-134-04-S-D](#) [BSW-123-04-S-S](#) [BSW-135-04-S-S](#) [BSW-126-24-G-S](#) [BSW-128-24-S-D](#) [BSW-112-24-L-S](#) [BSW-120-04-L-S](#) [BSW-113-04-L-D](#) [BSW-119-24-L-S](#) [BSW-120-04-L-D](#) [BSW-113-24-L-S](#) [BSW-116-24-L-S](#) [BSW-119-24-L-D](#) [BSW-123-04-L-D](#) [BSW-110-24-G-S](#) [BSW-133-04-S-S](#) [BSW-134-04-S-S](#) [BSW-119-24-G-D](#) [BSW-121-24-G-S](#) [BSW-110-24-L-S](#) [BSW-112-04-L-D](#) [BSW-113-04-L-S](#) [BSW-118-04-L-S](#) [BSW-122-04-L-S](#) [BSW-122-24-L-D](#) [BSW-124-24-L-D](#) [BSW-114-24-L-S](#) [BSW-118-24-L-D](#) [BSW-121-24-L-D](#) [BSW-124-24-L-S](#) [BSW-117-04-L-S](#) [BSW-123-04-L-S](#) [BSW-123-24-L-D](#) [BSW-126-04-L-D](#) [BSW-124-04-L-S](#) [BSW-118-24-G-S](#) [BSW-121-24-G-D](#) [BSW-123-24-G-S](#) [BSW-129-24-S-D](#) [BSW-111-24-L-S](#) [BSW-113-24-L-D](#) [BSW-117-24-L-S](#) [BSW-119-04-L-S](#) [BSW-118-24-L-S](#) [BSW-120-24-L-S](#) [BSW-121-24-L-S](#)