


MICRO BOARD STACKER

(1.27 mm) .050" PITCH • DWM/HDWM SERIES



DWM/HDWM

Mates:

SMS, SLM, RSM

SPECIFICATIONS

Insulator Material:

Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over 50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 °C to +105 °C with Tin

-55 °C to +125 °C with Gold

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.15 mm) .006" max*

*(.004" stencil solution may be available; contact

ipg@samtec.com)

ALSO AVAILABLE

Other Platings
(MOQ Required)

DWM	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	OTHER OPTION
	01 thru 50	Specify LEAD STYLE from chart	-L = 10 μ " (0.25 μ m) Gold on contact, Matte Tin on tail -G = 10 μ " (0.25 μ m) Gold on contact, Gold flash on tail	-S = Single Row -D = Double Row	- "XXX" = Stacker Height Example: -200 = (5.08 mm) .200"	- "XXX" = Polarized Position (Specify position of omitted pin)

OAL	
LEAD STYLE	THROUGH-HOLE
-01	(11.43) .450
-51	(10.41) .410
-52	(10.80) .425
-53	(12.83) .505
-54	(14.10) .555
-55	(15.49) .610
-56	(15.88) .625
-57	(16.51) .650
-58	(17.91) .705
-59	(19.18) .755
-60	(20.96) .825
-61	(26.67) 1.050

HDWM	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	OTHER OPTION
	01 thru 50	Specify LEAD STYLE from chart	-L = 10 μ " (0.25 μ m) Gold on contact, Matte Tin on tail -G = 10 μ " (0.25 μ m) Gold on contact, Gold flash on tail	-S = Single Row -D = Double Row	- "XXX" = Stacker Height Example: -250 = (6.35 mm) .250"	- "XXX" = Polarized Position (Specify position of omitted pin) - SM = Surface Mount (02 thru 40 positions only) - A = Alignment Pin (6 positions minimum -D only) Metal or plastic at Samtec discretion (Not available with -LC) - LC = Locking Clip (5 positions minimum -D only) (Not available with -A) (Manual placement required) - P = Pick & Place Pad

Notes:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

This Series is non-standard, non-returnable.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[DWM-05-56-L-D-415](#) [DWM-50-61-S-S-850](#) [DWM-02-56-L-S-300](#) [DWM-02-56-L-S-400](#) [DWM-02-58-L-S-500](#) [DWM-04-57-G-S-430](#) [DWM-04-58-L-S-500](#) [DWM-05-55-L-S-374](#) [DWM-05-58-L-S-400](#) [DWM-05-60-L-S-605](#) [DWM-06-58-L-S-500](#) [DWM-08-54-L-D-342](#) [DWM-08-61-L-S-450](#) [DWM-10-61-G-S-809](#) [DWM-13-53-L-D-200](#) [DWM-13-53-L-S-215](#) [DWM-15-53-L-S-215](#) [DWM-23-61-G-S-809](#) [DWM-25-58-L-D-400](#) [DWM-31-60-L-D-415](#) [DWM-31-61-L-D-415](#) [DWM-40-60-L-D-585](#) [DWM-44-54-S-D-200](#) [DWM-34-60-L-D-585](#)