


ELEVATED SOCKETS

(2.54 mm) .100" PITCH • ESW/ESQ SERIES



ESW/ESQ

Mates:

TSW, MTSW, EW,
MTLW, TSS, ZSS, TSM,
DW, ZW, HW, TSSH, HTSS

SPECIFICATIONS

Insulator Material:

Black Glass Filled Polyester

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over
50 μ" (1.27 μm) Ni

Operating Temp Range:

-55 °C to +125 °C with Gold

-55 °C to +105 °C with Tin

Current Rating (ESW/TSW):

5.2 A per pin

(2 pins powered)

Current Rating (ESQ/TSW):

5.7 A per pin

(2 pins powered)

Voltage Rating:

515 VAC/728 VDC

Insertion Depth:

(3.68 mm) .145" to

(6.35 mm) .250"

Max Cycles:

100 with 10 μ" (0.25 μm) Au

PROCESSING

Lead-Free Solderable:

No, Lead Wave only

SERIES	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OTHER OPTION
--------	---	------------------	------------	----------------	------------	--------------

ESW
= Solder Tail

01 thru 36

Specify
LEAD
STYLE
from
chart

-F
= Gold flash
on contact,
Matte Tin on tail

-S
= Single Row

-LL
= Locking Lead
(Two leads per
strip crimped.
Not available
with single row
1 or 2 positions)


ESQ
= Square Tail

-D
= Double Row


-T
= Triple Row
(ESQ only)

"XX"
= Polarized

LEAD STYLE			
STANDARD INSERTION FORCE	LOW INSERTION FORCE	A	B
- 12	- 37	(2.29) .090	(11.05) .435
- 13	- 38	(7.36) .290	
- 23	- 48	(4.83) .190	(13.59) .535
- 33	- 58	(2.29) .090	(16.13) .635
- 14	- 39	(12.19) .480	(11.05) .435
- 24	- 49	(9.65) .380	(13.59) .535
- 34	- 59	(7.11) .280	(16.13) .635
- 44	- 69	(4.57) .180	(18.67) .735



APPLICATIONS



*Self
Nesting
Sockets*

(ESQ SERIES)




ALSO AVAILABLE
Contact Samtec

Other Platings

Note:

Some lengths, styles and
options are non-standard,
non-returnable.



PC/104™ J1/P1 "Stackthrough" Connectors	
Standard Insertion Force	ESQ-132-14-G-D
Low Insertion Force	ESQ-132-39-G-D
PC/104™ J1 "Non-Stackthrough" Connectors	
Standard Insertion Force	ESQ-132-12-G-D
Low Insertion Force	ESQ-132-37-G-D
PC/104™ J2/P2 "Stackthrough" Connectors	
Standard Insertion Force	ESQ-120-14-G-D
Low Insertion Force	ESQ-120-39-G-D

PC/104 is a trademark of the PC/104 Consortium.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[ESQ-120-12-S-D](#) [ESQ-132-34-G-D](#) [ESQ-108-34-G-D](#) [ESQ-109-12-G-S](#) [ESQ-105-23-S-D](#) [ESQ-112-33-G-D](#) [ESQ-115-23-G-D](#) [ESQ-103-12-T-S](#) [ESQ-110-33-G-D](#) [ESQ-113-12-G-T](#) [ESQ-105-12-G-D](#) [ESQ-107-12-G-D](#) [ESQ-117-23-S-D](#) [ESQ-132-13-G-D](#) [ESQ-125-13-G-D](#) [ESQ-115-44-S-D-LL](#) [ESQ-106-23-G-S](#) [ESQ-105-44-G-D](#) [ESQ-108-33-G-D](#) [ESQ-113-44-S-D](#) [ESQ-120-13-G-D](#) [ESQ-130-23-G-D](#) [ESQ-120-34-G-D](#) [ESQ-132-14-G-D](#) [ESQ-132-12-S-D](#) [ESQ-120-12-G-D](#) [ESQ-120-14-G-D](#) [ESQ-132-12-G-D](#) [ESQ-120-39-G-D](#) [ESQ-117-33-G-D](#) [ESQ-102-12-G-D](#) [ESQ-105-12-G-S](#) [ESQ-105-13-G-D](#) [ESQ-110-34-G-D](#) [ESQ-120-23-T-D](#) [ESQ-132-24-G-D](#) [ESQ-120-24-G-D](#) [ESQ-120-69-G-D](#) [ESQ-115-12-G-T](#) [ESQ-120-33-G-D](#) [ESQ-101-14-G-D](#) [ESQ-104-14-G-D](#) [ESQ-108-44-G-D](#) [ESQ-102-13-G-D](#) [ESQ-105-33-S-D](#) [ESQ-105-58-S-D](#) [ESQ-104-23-T-S](#) [ESQ-104-37-G-D](#) [ESQ-108-13-T-S](#) [ESQ-105-24-G-D](#) [ESQ-110-37-G-D](#) [ESQ-107-12-L-D-LL](#) [ESQ-108-37-G-S](#) [ESQ-105-23-S-T](#) [ESQ-106-23-L-D](#) [ESQ-105-12-G-D-LL](#) [ESQ-106-12-G-S-LL](#) [ESQ-110-44-G-D-LL](#) [ESQ-117-34-S-D](#) [ESQ-110-14-G-D](#) [ESQ-112-44-S-S](#) [ESQ-120-23-L-D](#) [ESQ-110-14-L-S-LL](#) [ESQ-118-12-T-S](#) [ESQ-103-34-G-D](#) [ESQ-108-44-S-D](#) [ESQ-110-23-T-D](#) [ESQ-117-69-L-D](#) [ESQ-122-33-L-D](#) [ESQ-111-44-G-T](#) [ESQ-117-23-G-D](#) [ESQ-125-12-L-D](#) [ESQ-125-44-S-D](#) [ESQ-130-14-G-D](#) [ESQ-132-14-G-S](#) [ESQ-114-12-G-D](#) [ESQ-117-69-G-T](#) [ESQ-126-24-G-D](#) [ESQ-132-12-G-D-LL](#) [ESQ-116-13-G-D](#) [ESQ-117-14-G-S](#) [ESQ-120-33-L-D-LL](#) [ESQ-118-12-G-D](#) [ESQ-122-34-L-S](#) [ESQ-120-48-L-D](#) [ESQ-125-23-S-T](#) [ESQ-136-39-G-D](#) [ESQ-102-33-L-S](#) [ESQ-105-12-T-S](#) [ESQ-105-44-S-S](#) [ESQ-102-37-G-S](#) [ESQ-103-23-T-D](#) [ESQ-106-14-T-S](#) [ESQ-108-12-L-S](#) [ESQ-104-48-G-S](#) [ESQ-104-44-G-D](#) [ESQ-108-14-G-D](#) [ESQ-104-12-G-D](#) [ESQ-106-33-G-T](#) [ESQ-106-23-G-S-LL](#)