


FLAT FLEXIBLE CABLE (FFC) JUMPER & SOCKET

(0.50 mm) .0197" PITCH • FJH/ZF5S SERIES



FJH

Mates:
ZF5S

SPECIFICATIONS

Conductor:
Tin Plated Copper
Conductor Resistance:
1000 Ω /km max
Current Rating:
1.8 A per pin
(1 pin powered)
Operating Temp Range:
-55 °C to +80 °C
Voltage Rating:
195 VAC


OTHER SOLUTIONS

For 1.00 mm pitch flat flexible cable series, visit:
www.samtec.com?FJ
www.samtec.com?ZF1
www.samtec.com?FC1

FJH	NO. OF POSITIONS	STYLE	LENGTH	STRIP LENGTH
	-10, -15, -20, -25, -30, -40, -43, -50 (Standard sizes)	-D = Double End -R = Reversed End	Length in inches -03.00 = (76.2 mm) 3.00" -06.00 = (152.4 mm) 6.00" -12.00 = (304.8 mm) 12.00" -24.00 = (609.6 mm) 24.00" (Standard Lengths)	-4 = (4.00 mm) .157"

NO. OF POSITIONS	A
-10	(5.50) .217
-15	(8.00) .315
-20	(10.50) .413
-25	(13.00) .512
-30	(15.50) .610
-40	(20.50) .807
-43	(22.00) .866
-50	(25.50) 1.00

Notes:
Stiffener color will be blue or black at Samtec's discretion.
Some sizes, styles and options are non-standard, non-returnable.



-D STYLE

-R STYLE

ZF5S

Mates:
FJH

SPECIFICATIONS

Insulator Material:
Natural LCP
Contact Material:
Phosphor Bronze
Plating:
Sn over 50 μ " (1.27 μ m) Ni
Weld Tab:
Phosphor Bronze
Operating Temp Range:
-55 °C to +105 °C
Current Rating:
1.8 A per pin
(1 pin powered)

PROCESSING

Lead-Free Solderable:
Yes
SMT Lead Coplanarity:
(0.10 mm) .004" max (10-30)
(0.15 mm) .006" max (40-50)*
*(.004" stencil solution may be available; contact ipg@samtec.com)

Note:
Some sizes, styles and options are non-standard, non-returnable.

ZF5S	NO. OF POSITIONS	LEAD STYLE	PLATING OPTION	WT	OPTION
	-10, -15, -20, -25, -30, -40, -43, -50 (Standard sizes)	-01 = Contact Bottom	-T = Matte Tin	-WT = Weld Tab	-K = (3.00 mm) .118" DIA Polyimide Film Pick & Place Pad -TR = Tape & Reel -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks)

ALSO AVAILABLE
Contact Samtec

Vertical
Contact top
Other positions

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

<u>FJH-25-D-06.00-4</u>	<u>FJH-15-D-03.50-4</u>	<u>FJH-06-D-12.00-4</u>	<u>FJH-20-D-08.00-4</u>	<u>FJH-30-D-03.50-4</u>	<u>FJH-10-R-02.50-4</u>
<u>FJH-10-D-06.50-4</u>	<u>FJH-20-R-10.00-4</u>	<u>FJH-15-D-04.80-4</u>	<u>FJH-10-R-07.00-4</u>	<u>FJH-15-R-07.00-4</u>	<u>FJH-30-D-05.12-4</u>
<u>FJH-15-D-08.50-4</u>	<u>FJH-40-D-18.00-4</u>	<u>FJH-24-D-13.19-4</u>	<u>FJH-40-D-16.00-4</u>	<u>FJH-40-D-11.80-4</u>	<u>FJH-10-R-06.50-4</u>
<u>FJH-40-D-06.70-4</u>	<u>FJH-15-R-02.09-4</u>	<u>FJH-40-D-47.25-4</u>	<u>FJH-43-D-02.30-4</u>	<u>FJH-10-D-19.50-4</u>	<u>FJH-15-D-08.66-4</u>
<u>FJH-20-D-02.37-4</u>	<u>FJH-40-D-03.69-4</u>	<u>FJH-43-D-12.00-4</u>	<u>FJH-30-R-03.10-4</u>	<u>FJH-08-D-07.90-4</u>	<u>FJH-12-D-02.00-4</u>
<u>FJH-12-D-03.00-4</u>	<u>FJH-12-R-03.00-4</u>	<u>FJH-18-D-02.00-4</u>	<u>FJH-21-D-05.60-4</u>	<u>FJH-08-D-04.00-4</u>	<u>FJH-18-D-06.00-4</u>
<u>FJH-36-D-06.00-4</u>	<u>FJH-26-D-04.00-4</u>	<u>FJH-18-R-13.80-4</u>	<u>FJH-15-D-99.99-4</u>	<u>FJH-40-R-04.30-4</u>	<u>FJH-40-R-60.00-4</u>
<u>FJH-20-D-26.00-4</u>	<u>FJH-40-R-03.90-4</u>				