

QUAD ROW TERMINAL/SOCKET

(1.27 mm) .050" PITCH • FOLC/MOLC SERIES

MAX
2.6
A m p s

8
G b p s


FOLC
Board Mates:
MOLC

MOLC
Board Mates:
FOLC

SPECIFICATIONS

Insulator Material:
Black Liquid Crystal Polymer
Contact Material (FOLC):
BeCu
Terminal Material (MOLC):
Phosphor Bronze
Plating:
Au or Sn over
50 μ" (1.27 μm) Ni
Current Rating:
2.6 A per pin
(4 pins powered)
Operating Temp Range:
-55 °C to +125 °C
Voltage Rating:
165 VAC/230 VDC
Insertion Depth (FOLC):
(3.30 mm) .130" to
(4.06 mm) .160"
Max Cycles (FOLC):
100

FOLC	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	Q	OPTION	PACKAGING
		20, 25, 30, 35, 40, 45, 50 (Standard sizes)	-01 & -04 = Through-hole -M1 & -M2 = Mixed Technology -L1 & -L4 = Low Insertion Force Through-hole	-L = 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail		-LC = Locking Clip (Manual placement required)	Leave blank for tubes -TR = Tape & Reel (-MX only) -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (-MX only)



LEAD STYLE	C
-01, -M1	(1.91) .075
-04, -M2	(3.04) .120


View complete specifications at: samtec.com?FOLC

PROCESSING

Lead-Free Solderable:
Yes
SMT Lead Coplanarity (MOLC):
(0.10 mm) .004" max (20-25)
(0.15 mm) .006" max (30-50)*
*(.004" stencil solution may be available; contact ipg@samtec.com)


MOLC	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	Q	OPTION	PACKAGING
		20, 25, 30, 35, 40, 45, 50 (Standard sizes)	-'X'1 = Through-hole (Specify from chart) -02 = Surface Mount -M1 = Mixed Technology	-L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail		-LC = Locking Clip (Manual placement required) -P = Pick & Place Pad (-02 only)	Leave blank for tubes -TR = Tape & Reel (-02 & -M1 only) -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (-02 & -M1 only)

APPLICATIONS



LEAD STYLE	MATED HEIGHT*
MOLC	FOLC
-01	(5.97) .235
-11	(7.75) .305
-31	(11.43) .450

*Processing conditions will affect mated height.



LEAD STYLE	A	B
-01	(5.59) .220	(3.38) .133
-11	(7.34) .289	(3.66) .144
-31	(11.05) .435	

View complete specifications at: samtec.com?MOLC

Note:
Some lengths, styles and options are non-standard, non-returnable.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[FOLC-120-04-S-Q-LC](#) [FOLC-150-04-S-Q-LC](#) [FOLC-135-04-L-Q-LC](#) [FOLC-120-01-S-Q-LC](#) [FOLC-125-01-S-Q-LC](#)
[FOLC-120-01-L-Q-LC](#) [FOLC-135-04-S-Q-LC](#) [FOLC-120-01-L-Q](#) [FOLC-130-01-S-Q-LC](#) [FOLC-130-04-S-Q-LC](#) [FOLC-](#)
[125-L1-S-Q-LC](#) [FOLC-130-L1-S-Q-LC](#) [FOLC-135-04-S-Q](#) [FOLC-140-04-S-Q-LC](#) [FOLC-140-L1-S-Q-LC](#) [FOLC-145-](#)
[01-S-Q](#) [FOLC-145-04-S-Q](#) [FOLC-150-L4-S-Q-LC](#) [FOLC-120-04-S-Q](#) [FOLC-135-01-S-Q](#) [FOLC-135-01-S-Q-P](#) [FOLC-](#)
[135-L1-S-Q-LC](#) [FOLC-140-01-S-Q](#) [FOLC-145-01-S-Q-LC](#) [FOLC-135-L1-S-Q](#) [FOLC-145-L1-S-Q](#) [FOLC-120-L4-S-Q-](#)
[LC](#) [FOLC-150-01-S-Q](#) [FOLC-120-01-S-Q](#) [FOLC-120-02-S-Q-LC-P](#) [FOLC-125-04-S-Q-LC](#) [FOLC-140-01-S-Q-LC](#)
[FOLC-140-L4-S-Q-LC](#) [FOLC-150-L1-S-Q-LC](#) [FOLC-150-L2-S-Q-LC](#) [FOLC-140-L1-S-Q](#) [FOLC-150-04-S-Q](#) [FOLC-](#)
[150-L1-S-Q](#) [FOLC-130-L1-S-Q](#) [FOLC-140-04-S-Q](#) [FOLC-145-04-S-Q-LC](#) [FOLC-145-L1-S-Q-LC](#) [FOLC-110-L1-S-Q](#)
[FOLC-120-01-S-Q-P](#) [FOLC-120-04-S-Q-P](#) [FOLC-120-L1-S-Q](#) [FOLC-120-L1-S-Q-LC](#) [FOLC-125-01-S-Q](#) [FOLC-125-](#)
[L1-S-Q](#) [FOLC-115-01-S-Q](#) [FOLC-115-01-S-Q-LC](#) [FOLC-130-04-S-Q](#) [FOLC-150-01-S-Q-LC](#) [FOLC-105-L1-S-Q](#)
[FOLC-135-01-S-Q-LC](#) [FOLC-115-L1-S-Q](#) [FOLC-125-04-S-Q](#) [FOLC-125-01-SM-Q-LC](#) [FOLC-110-04-S-Q-LC](#) [FOLC-](#)
[130-L4-S-Q](#) [FOLC-135-01-SM-Q-LC](#) [FOLC-125-01-SM-Q](#) [FOLC-125-04-SM-Q](#) [FOLC-130-01-L-D](#) [FOLC-130-04-SM-](#)
[Q-LC](#) [FOLC-110-L4-S-Q](#) [FOLC-110-01-S-Q](#) [FOLC-134-04-S-Q](#) [FOLC-130-01-SM-Q](#) [FOLC-105-01-S-Q-LC](#) [FOLC-](#)
[145-L4-S-Q-LC](#) [FOLC-105-01-S-Q](#) [FOLC-120-L4-S-Q](#) [FOLC-115-04-S-Q-LC](#) [FOLC-145-L4-S-Q](#) [FOLC-125-L4-S-Q-](#)
[LC](#) [FOLC-130-L4-S-Q-LC](#) [FOLC-125-L4-S-Q](#) [FOLC-110-04-S-Q](#) [FOLC-135-L4-S-Q-LC](#) [FOLC-140-L4-S-Q](#) [FOLC-](#)
[135-L4-S-Q](#) [FOLC-120-01-SM-Q-LC](#) [FOLC-110-L4-S-Q-LC](#) [FOLC-130-L4-L-Q-LC](#) [FOLC-135-01-L-Q-LC](#) [FOLC-140-](#)
[04-L-Q](#) [FOLC-140-L1-L-Q](#) [FOLC-145-01-L-Q-LC](#) [FOLC-120-L1-L-Q](#) [FOLC-140-01-L-Q](#) [FOLC-150-01-L-Q](#) [FOLC-](#)
[150-04-L-Q](#) [FOLC-125-04-L-Q-LC](#) [FOLC-135-01-L-Q](#) [FOLC-140-01-L-Q-LC](#) [FOLC-120-04-L-Q](#) [FOLC-125-01-L-Q-LC](#)
[FOLC-125-04-L-Q](#) [FOLC-130-04-L-Q-LC](#)