

REVISION AM

DO NOT
SCALE FROM
THIS PRINT

TABLE 1

LEAD STYLE	TERMINAL	"B"	TUBE (SEE NOTE 9)	PLUG
-01	T-1M6-13-X-2	.230 [5.84]	PT-1-24-01-46	TP-12
-01 (W / PAD OPTION)	T-1M6-13-X-2	.230 [5.84]	PT-1-24-05-29	TP-03
-02	T-1M6-30-X-2	.100 [2.54]	PT-1-24-02-29	TP-24
-02 (W / PAD OPTION)	T-1M6-30-X-2	.100 [2.54]	PT-1-24-05-29	TP-03
-03 (W / PAD OPTION)	T-1M6-04-X-2	.125 [3.18]	PT-1-24-04-09	TP-09
-03 (NO OPTIONS)	T-1M6-04-X-2	.125 [3.18]	PT-1-24-02-29	TP-24
-21	N/A	.230 [5.84]	N/A	N/A
-51	T-1M6-13-X-2	.190 [4.83]	PT-1-24-02-29	TP-24
-52	T-1M6-13-X-2	.205 [5.21]	PT-1-24-10-29	TP-24
-52 (W / PAD OPTION)	T-1M6-13-X-2	.205 [5.21]	PT-1-24-05-29	TP-03
-53	T-1M6-05-X-2	.285 [7.24]	PT-1-24-02-29	TP-24
-54 (6-50 POSITION)	T-1M6-15-X-2	.335 [8.51]	PT-1-24-13-29	TP-24
-54 (5 POSITION)	T-1M6-15-X-2	.335 [8.51]	PT-1-24-10-29	TP-24
-55	T-1M6-16-X-2	.390 [9.91]	PT-1-24-10-29	TP-24
-56	T-1M6-16-X-2	.405 [10.29]	PT-1-24-10-29	TP-24
-57	T-1M6-16-X-2	.430 [10.92]	PT-1-24-03-71	TP-24
-58	N/A	.485 [12.32]	N/A	N/A
-59	N/A	.535 [13.59]	N/A	N/A
-60	N/A	.605 [15.37]	N/A	N/A
-53, -54, -55, -56, -57-60 (W / PAD OPTION)	N/A	N/A	PT-1-24-03-71	TP-09

FTR-1XX-XX-XX-S-XX-X-XX

No OF POSITIONS
-02 THRU -40LEAD STYLE
SEE TABLE 1

PLATING SPECIFICATION

(VALUES GIVEN ARE IN MICRO-INCHES)
-G: GOLD, 10 Au / 50 Ni MIN ON CONTACT,
3 Au / 50 Ni MIN ON TAIL
-T: MATTE TIN CONTACT AND TAIL
-S: SELECTIVE, 30 Au / 50 Ni MIN
ON CONTACT, MATTE TIN TAIL
-F: FLASH SELECTIVE, 3 Au / 50 Ni MIN
ON CONTACT, MATTE TIN TAIL
(LEAD STYLE SPEC -01 ONLY)
-SM: SELECTIVE, 30 Au / 50 Ni MIN
ON CONTACT, MATTE TIN TAIL
-TM: MATTE TIN CONTACT AND TAIL
-FM: FLASH SELECTIVE, 3 Au / 50 Ni MIN
ON CONTACT, MATTE TIN TAIL
-L: LIGHT SELECTIVE, 10 Au / 50 Ni MIN
ON CONTACT, MATTE TIN TAIL

ROW SPECIFICATION





-S: SINGLE (USE HTMS-50-S)

PACKAGING
(SEE NOTES 10 & 11)
BLANK: TUBES
-TR: TAPE & REEL
(4 POS MIN)
-FR: FULL REEL QTY TAPE & REEL

PICK & PLACE PAD
-P: PICK & PLACE PAD
(USE PPP-11, SEE FIG 2)

OPTION

-XX: -POLARIZING SPECIFICATION
(XX INDICATES POS TO BE OMITTED)

FIG 1
FTR-1XX-XX-X-S SHOWN

NOTES:

1. Ⓢ REPRESENTS A CRITICAL DIMENSION.
2. MAXIMUM CUT FLASH: .010 [0.25]
3. MINIMUM PUSHOUT FORCE: 2 LB
4. MAXIMUM PIN ROTATION IN BODY: 2°
5. MAXIMUM ALLOWABLE BOW AFTER ASSEMBLY: .005 [0.13] INCH/INCH
6. SHEAR TAILS TO DIMENSION SHOWN.
7. MAXIMUM BURR ALLOWANCE: .003 [0.08]
8. MEASURED AT BEND RADIUS.
9. TUBE POSITIONS -05 THRU -50 ONLY FOR THIS LEAD STYLE.
10. ORDERS WILL BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM
11. ATTACH LABEL TO EACH REEL

TABLE 2	
TERMINAL LENGTH	* "L"
-04	.505 [12.83]
-05	.705 [17.91]
-13	.625 [15.88]
-15	.755 [19.18]
-16	.825 [20.96]
* REF FOR OAL PIN LENGTH	

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS	ANGLES
.XX: ±.01 [.3]	2°
.XXX: ±.005 [.13]	
.XXXX: ±.0020 [.051]	

MATERIAL: DO NOT SCALE DRAWING

INSULATOR: LCP, UL 94 VO
COLOR: BLACK
TERMINAL: PHOS BRONZE

* PROPRIETARY NOTE *

THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 2.5:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
HI-TEMP TERMINAL MICRO-STRIP (SINGLE ROW)
DWG. NO.

FTR-1XX-XX-XX-S-XX-X-XX

BY: BRATCHER 07/10/1995 SHEET 1 OF 2

"N" = USE MEASURED DIMENSION
"Q" = { ("N" - .400 [10.16]) / 2 } ±.020[0.51]




FIG 2
-P: PICK AND PLACE PAD
AVAILABLE ON 08 - 40 POSITIONS ONLY

• PROPRIETARY NOTE •
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING
SHEET SCALE: 2.5:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:
HI-TEMP TERMINAL MICRO-STRIP (SINGLE ROW)
DWG. NO.
FTR-1XX-XX-XX-S-XX-X-XX
BY: BRATCHER 07/10/1995 SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[FTR-108-01-S-S](#) [FTR-108-03-S-S](#) [FTR-140-01-S-S](#) [FTR-103-03-S-S](#) [FTR-106-51-S-S](#) [FTR-102-52-L-S](#) [FTR-103-56-S-S](#) [FTR-115-52-S-S](#) [FTR-104-02-L-S-TR](#) [FTR-109-02-S-S](#) [FTR-109-53-L-S](#) [FTR-115-51-S-S](#) [FTR-116-53-G-S-P](#) [FTR-105-01-S-S](#) [FTR-105-02-L-S-TR](#) [FTR-112-01-S-S](#) [FTR-103-03-L-S](#) [FTR-108-03-S-S-03-P-TR](#) [FTR-135-01-L-S-P-TR](#) [FTR-106-02-G-S](#) [FTR-103-03-G-S](#) [FTR-103-52-L-S](#) [FTR-104-03-G-S](#) [FTR-112-52-G-S](#) [FTR-108-03-S-S-P-TR](#) [FTR-105-01-G-S](#) [FTR-108-03-S-S-02-P-TR](#) [FTR-105-02-L-S](#) [FTR-108-02-S-S-P-TR](#) [FTR-106-01-G-S](#) [FTR-109-53-T-S-P-TR](#) [FTR-104-03-S-S](#) [FTR-108-01-S-S-P-TR](#) [FTR-105-03-G-S](#) [FTR-120-53-S-S-P-TR](#) [FTR-108-52-G-S](#) [FTR-108-52-G-S-P](#) [FTR-108-52-T-S-P](#) [FTR-108-54-G-S](#) [FTR-108-55-G-S](#) [FTR-109-03-S-S](#) [FTR-103-53-S-S](#) [FTR-103-57-T-S](#) [FTR-104-01-T-S](#) [FTR-104-02-S-S](#) [FTR-104-02-T-S](#) [FTR-104-51-S-S](#) [FTR-104-52-S-S](#) [FTR-110-03-S-S](#) [FTR-105-51-G-S](#) [FTR-105-55-T-S](#) [FTR-111-01-S-S](#) [FTR-111-52-T-S](#) [FTR-112-02-S-S](#) [FTR-108-03-S-S-P](#) [FTR-112-52-S-S](#) [FTR-112-53-S-S-P](#) [FTR-112-53-T-S-P](#) [FTR-113-01-T-S](#) [FTR-107-52-G-S](#) [FTR-107-52-S-S](#) [FTR-114-01-S-S](#) [FTR-114-01-S-S-P](#) [FTR-114-01-T-S](#) [FTR-114-02-G-S](#) [FTR-114-02-T-S](#) [FTR-114-03-G-S](#) [FTR-114-03-G-S-P](#) [FTR-114-03-T-S](#) [FTR-114-51-S-S](#) [FTR-114-52-G-S](#) [FTR-110-51-G-S](#) [FTR-110-51-T-S](#) [FTR-110-51-T-S-P](#) [FTR-110-52-G-S-P](#) [FTR-110-52-S-S-P](#) [FTR-110-53-S-S](#) [FTR-110-53-T-S](#) [FTR-110-54-G-S](#) [FTR-110-55-G-S](#) [FTR-110-55-S-S](#) [FTR-113-03-T-S](#) [FTR-114-01-G-S](#) [FTR-116-03-S-S](#) [FTR-112-03-G-S](#) [FTR-112-03-G-S-P](#) [FTR-112-52-G-S-P](#) [FTR-116-55-T-S](#) [FTR-117-01-G-S](#) [FTR-117-52-G-S](#) [FTR-109-53-T-S-P](#) [FTR-110-01-G-S](#) [FTR-110-01-G-S-P](#) [FTR-110-01-S-S](#) [FTR-110-01-S-S-P](#) [FTR-110-01-T-S](#) [FTR-110-02-G-S](#) [FTR-110-02-S-S](#) [FTR-110-02-T-S](#) [FTR-118-52-G-S](#)