

(4.00 mm) .1575"

IJ5C-08-0600-S-D-NUS-1

IJ5C-04-0400-S-D-NUS-1

IJ5C SERIES

50 Ω HIGH ISOLATION RF CABLE ASSEMBLY

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?IJ5C

Insulator Material:

Black LCP

Contact Material:

Copper Alloy

Pin Material:

Copper Alloy

Dielectric Material:

Black LCP

Plating:

Au over 50 μ" (1.27 μm) Ni

Operating Temp Range:

-40 °C to +90 °C

RoHS Compliant: Yes

Cable (-1):
Conductor Size:

26 AWG,

(0.48 mm) .019" dia.

Conductor Material:

Silver Plated Copper

Insulator Diameter:

(1.27 mm) .050"

Insulator Material:

Foamed FEP

Shield Material:

Silver Plated Copper

Jacket Material:

FEP

Jacket Diameter:

(1.80 mm) .071"

Bend Radius:

3.175 mm

Impedance:

50 Ω

Current Rating: 2.5 A

RoHS Compliant: Yes

Cable (-2):
Conductor Size:

26 AWG,

(0.51 mm) .020" dia.

Conductor Material:

Silver and Copper

Insulator Diameter:

(1.52 mm) .060"

Insulator Material:

PTFE

Shield Material:

Silver Plated Copper Wire

Jacket Material:

FEP

Jacket Diameter:

(2.54 mm) .100"

Bend Radius:

12.7 mm

Impedance:

50 Ω

Current Rating: 5 A DC

RoHS Compliant: Yes

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Note:
This Series is non-standard,
non-returnable.

Mates with:
IP5

**EDGE
RATE[®]**
 CONTACT

Single or
Double Ended

High-performance
26 AWG
coax cable

Positive latching
system

1, 2, 4, 6 or 8
Positions

1 Meter Cable Assembly	Frequency
Insertion Loss = 3 dB	9.5 GHz / 19.0 Gbps
Return Loss = 15 dB	2.2 GHz / 4.4 Gbps
Isolation = 60 dB	3.1 GHz / 6.2 Gbps

Performance and complete test data available at www.samtec.com?IJ5C or contact sig@samtec.com

IJ5C**NO. OF
POSITIONS****ASSEMBLED
LENGTH****PLATING
OPTION****END
OPTION****END 2
OPTION****CABLE
TYPE**

-01, -02,
-04, -06, -08

—"XXXX"
= Assembled
Length
in millimeters
-0100 to -1000
(100 mm) 3.94"
minimum

-S
= 30 μ"
(0.76 μm)
Gold on
contact

-S
= Single
Ended

-D
= Double
Ended



-NUS
= Notch up,
straight
P1 to P1

-NDS
= Notch
down,
straight
P1 to PN

-1
= CTB-2650F-01
cable

-2
= RG 316 cable

NO. OF POSITIONS	A
-01	(20.87) .822
-02	(24.87) .979
-04	(32.87) 1.294
-06	(40.87) 1.609
-08	(48.87) 1.924



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[IJ5C-02-1000-S-D-NUS](#) [IJ5C-02-1000-S-D-NUS-1](#) [IJ5C-02-1000-S-D-NUS-2](#) [IJ5C-02-0300-S-D-NUS-1](#) [IJ5C-04-0240-S-S-1](#) [IJ5C-04-0458-S-D-NUS-2](#) [IJ5C-08-0300-S-D-NUS-1](#) [IJ5C-04-0150-S-D-NUS-1](#) [IJ5C-06-0100-S-D-NUS-1](#) [IJ5C-06-0152-S-D-NUS-1](#) [IJ5C-04-0200-S-S-1](#) [IJ5C-04-0610-S-S-1](#) [IJ5C-06-0150-S-D-NUS-1](#) [IJ5C-08-0250-S-D-NUS-1](#) [IJ5C-02-1000-S-S-1](#) [IJ5C-02-1000-S-S-2](#) [IJ5C-06-0153-S-S-1](#) [IJ5C-06-0300-S-D-NUS-1](#) [IJ5C-06-0450-S-D-NUS-1](#) [IJ5C-06-0610-S-S-1](#) [IJ5C-02-0100-S-S-1](#) [IJ5C-02-0500-S-D-NUS-2](#) [IJ5C-02-0150-S-D-NUS-1](#) [IJ5C-04-0500-S-S-2](#) [IJ5C-08-0254-S-D-NUS-1](#) [IJ5C-08-0500-S-S-1](#) [IJ5C-08-0500-S-S-2](#) [IJ5C-02-0400-S-S-1](#) [IJ5C-04-0127-S-D-NUS-1](#) [IJ5C-08-0150-S-D-NUS-1](#) [IJ5C-08-1000-S-S-1](#) [IJ5C-02-0458-S-D-NUS-1](#) [IJ5C-02-0300-S-S-1](#) [IJ5C-04-0100-S-S-1](#) [IJ5C-01-0100-S-D-NUS](#) [IJ5C-04-0400-S-D-NUS-2](#) [IJ5C-08-0500-S-D-NUS-2](#) [IJ5C-08-0100-S-S-1](#) [IJ5C-08-0200-S-S-1](#) [IJ5C-08-1000-S-D-NUS-2](#) [IJ5C-04-0600-S-D-NUS-1](#) [IJ5C-04-0914-S-D-NDS-2](#) [IJ5C-04-1000-S-S-2](#) [IJ5C-04-0102-S-D-NUS-1](#) [IJ5C-04-0508-S-D-NUS-1](#) [IJ5C-02-0250-S-D-NUS-1](#) [IJ5C-06-0500-S-S-2](#) [IJ5C-04-0406-S-D-NUS-1](#) [IJ5C-02-0115-S-D-NUS-1](#) [IJ5C-02-0500-S-S-2](#) [IJ5C-08-0457-S-D-NUS-2](#) [IJ5C-08-0610-S-D-NUS-2](#) [IJ5C-02-0610-S-S-2](#) [IJ5C-02-0800-S-D-NUS-2](#) [IJ5C-04-0400-S-S-1](#) [IJ5C-08-1397-S-D-NUS-1](#) [IJ5C-08-2000-S-S-2](#) [IJ5C-04-0508-S-D-NUS-2](#) [IJ5C-08-0600-S-S-1](#) [IJ5C-04-0600-S-D-NDS-2](#) [IJ5C-01-0500-S-S-1](#) [IJ5C-04-0500-S-D-NUS-2](#) [IJ5C-04-2020-S-S-2](#) [IJ5C-02-0914-S-S-2](#) [IJ5C-04-0600-S-S-2](#) [IJ5C-02-1500-S-S-1](#) [IJ5C-02-0171-S-D-NUS-1](#) [IJ5C-08-0150-S-D-NUS-2](#) [IJ5C-08-2000-S-S-1](#) [IJ5C-02-0320-S-D-NUS-1](#) [IJ5C-06-0600-S-S-2](#)