


TIGER CLAW™ SOCKET STRIP

(2.00 mm) .0787" PITCH • MMS SERIES

8
G b p s



MMS

Board Mates:

TMMH, TMM, MTMM, MMT,
TW, LTMM, ZLTMM, TSH

Cable Mates:

TCMD

SPECIFICATIONS

Insulator Material:

Black LCP

Contact Material:

Phosphor Bronze

Plating:

Sn or Au over

50 μ " (1.27 μ m) Ni

Current Rating (MMS/TMM):

3.9 A per pin

(2 pins powered)

Operating Temp Range:

-55 °C to +125 °C with Gold

-55 °C to +105 °C with Tin

Insertion Depth:

DH = (2.13 mm) .084" to

(2.79 mm) .110"

SH = (2.13 mm) .084"

minimum or pass-through

Top Entry DV/SV =

(2.13 mm) .084" to

(4.32 mm) .170"

Bottom Entry DV/SV =

(4.27 mm) .168" minimum

(Plus board)

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.15 mm) .006" max*

*(.004" stencil solution
may be available; contact
ipg@samtec.com)

ALSO AVAILABLE

MOQ Required

Alignment Pin (-DV only)

Locking clips and Through-hole
pass-through options




Other platings

Note:

Some lengths, styles and
options are non-standard,
non-returnable.

MMS	- 1	NO. PINS PER ROW	- 01	PLATING OPTION	-	ROW OPTION	-	OPTION
-----	-----	---------------------	------	-------------------	---	---------------	---	--------

02 thru 40



-F
= Gold flash on contact,
Matte Tin on tail

-L
= 10 μ " (0.25 μ m)
Gold contact,
Matte Tin on tail





-SV
= Single
Vertical

-SH
= Single
Horizontal

-DV
= Double
Vertical




-DH
= Double
Horizontal

-“XX”
= Polarized
Position



MMS	- 1	NO. PINS PER ROW	- 02	PLATING OPTION	-	ROW OPTION	-	OTHER OPTION
-----	-----	---------------------	------	-------------------	---	---------------	---	-----------------

02 thru 40



-F
= Gold flash
on contact,
Matte Tin on tail

-L
= 10 μ " (0.25 μ m)
Gold contact,
Matte Tin on tail

-SV
= Single
Vertical

-SH
= Single
Horizontal

-DV
= Double
Vertical

-DH
= Double
Horizontal

-“XX”
= Polarized Position





-K
= (5.50 mm) .217" DIA
Polyimide Film
Pick & Place Pad
(3 positions min.)
(-SV & -DV only)

-M
= Metal Pick & Place Pad
(4 positions min.)
(-DV only)

-P
= Plastic Pick & Place Pad
(4 positions min.)
(-SV & -DV only)

-TR
= Tape & Reel

-FR
= Full Reel
Tape & Reel
(must order max.
quantity per reel;
contact Samtec for
quantity breaks)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[MMS-104-02-F-DV-P](#) [MMS-104-02-L-DV-P](#) [MMS-104-02-L-SV-P](#) [MMS-104-02-S-DV-P](#) [MMS-104-02-F-SV-P](#)