

OPTICAL PATCH CABLE AND ADAPTOR

FOPC	END 1	END 2	CABLE LENGTH	FIBERS	CONSTRUCTION
	-01 = MTP Male	-01 = MTP Male	-003 = 3 Meters	-12, -24	-01 = 3 mm Round Jacket
	-02 = MTP Female	-02 = MTP Female	-010 = 10 Meters		
			-100 = 100 Meters (Other lengths available as custom parts)		
					 12 FIBER
			 -01-01-XXX-12-01		
			 -02-02-XXX-24-01		 24 FIBER

SPECIFICATIONS

Compliant Specifications:
TIA-604-5-D (FOCIS 5)
TIA-568-C.3
IEC-61754-7-1

View complete specifications at: samtec.com?FOPC

OPA	PORTS	KEY	FLANGE
	-S = Single	-1 = Opposed	-F = Full
	-D = Double	-2 = Aligned	
	 -S	 -1	
	 -D	 -2	

SPECIFICATIONS

Compliant Specifications:
TIA-604-5-D (FOCIS 5)
IEC-61754-7
Recommended Panel Thickness:
(1.75 mm) .069"
(The OPA can be installed with any panel thickness but mounting hardware is needed for any thickness that is not (1.75 mm) .069". Contact the Optics Group at FireFly@samtec.com for questions about panel thickness and mounting hardware.)

View complete specifications at: samtec.com?OPA

Notes:
Some lengths, styles and options are non-standard, non-returnable

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[OPA-S-1-F](#) [OPA-D-1-F](#) [OPA-D-2-F](#) [OPA-S-2-F](#)