


(1.00 mm) .0394" PITCH • SINGLE ROW DISCRETE WIRE SOCKET




SERIES	PINS PER ROW	WIRE GAUGE	PLATING OPTION	ASSEMBLED LENGTH	OPTION
S1SS = Single Row PVC Cable	-02, -03, -05, -07, -10 -15, -20 (Standard sizes)	-28 = 28 AWG -28C = 28 AWG Color Coded Cable (S1SS only) -30 = 30 AWG -30C = 30 AWG Color Coded Cable (S1SS only)	-GF = 3 μ" (0.07 μm) Gold on contact and tail	-"XX.XX" = Assembled Length in Inches (45.72 mm) 01.80" min.	(Required Callout) -L = Single Ended With Latch -L1 = Double Ended Latch down, straight (Pin 1 to Pin 1) -L3 = Double Ended Latch up, straight (Pin 1 to Pin N) -S = Single Ended No Latch -D-NUS = Double Ended No Latch, "N" up, straight -D-NDs = Double Ended No Latch, "N" down, straight
S1SS(T) Board Mates: T1M Cable Mates: T1SS(T), T1PS(T)					

S1SS CABLE COLOR CODING	
PIN	COLOR
1	BROWN
2	RED
3	ORANGE
4	YELLOW
5	GREEN
6	BLUE
7	VIOLET
8	GRAY
9	WHITE
10	BLACK
ETC	REPEAT

SPECIFICATIONS

Insulator Material:
Nylon, White (with latch)
Black, LCP (without latch)
Contact Material:
Phosphor Bronze
Plating:
Au over 50 μ" (1.27 μm) Ni
Operating Temp Range (S1SS(T)/T1M):
-10 °C to +85 °C (PVC)
-40 °C to +125 °C
(*Teflon™ Fluoropolymer)
Current Rating (28 AWG):
2.7 A per pin (1 pin powered)
Voltage Rating:
250 VAC/353 VDC
Wire: 28 or 30 AWG



*Teflon™ is a trademark of The Chemours Company FC, LLC used under license by Samtec.

Note:
Teflon™ Fluoropolymer cable is intended for crimp only. Contact Samtec for solderable cable applications.

View complete specifications at: samtec.com?S1SS & [samtec.com?S1SS\(T\)](http://samtec.com?S1SS(T))

SERIES	NO. OF POSITIONS	LATCH	SERIES	01	PLATING
ISS1 = Single Row Body	-02, -03, -05, -07, -10, -15, -20	(Leave blank for no latch) -L = Positive Latch	CC09R = Contact, Full Reel (25,000 Parts per Reel) CC09M = Contact, Mini Reel (5,000 Parts per Reel)		-GF = 3 μ" (0.07 μm) Gold contact and tail

TOOLING

Hand Tool: CAT-HT-309-2830-12

Clamp for mounting hand tool: CAT-HT-MNT-01

Mini Applicator: CAT-MC-309-2830-XX-01

Note:
Some lengths, styles and options are non-standard, non-returnable.

View complete specifications at: samtec.com?ISS1, samtec.com?CC09R & samtec.com?CC09M

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[S1SS-20-28-GF-07.50-L1](#)