


RUGGED TIGER EYE™ SYSTEMS

(2.00 mm) .0787" PITCH




FEATURES & BENEFITS

- Rugged Tiger Eye™ contact system for high-reliability
- Wide range of stack heights (SMM/TMM Series)
- Right-angle mating headers available
- Optional metal latching, screw downs, weld tabs and locking clips
- Surface mount or through-hole
- Discrete wire assemblies available in 24-30 AWG PVC or Teflon® wire; contact.asp@samtec.com for custom solutions



Optional strain relief
and variety of
wiring options



Components
(ISD2/CC81) &
tooling available:
samtec.com/tooling

KEY SPECIFICATIONS (S2M/T2M)


PITCH	STACK HEIGHTS	TOTAL PINS	INSULATOR MATERIAL	CONTACT MATERIAL	PLATING	OPERATING TEMP RANGE	CURRENT RATING	MAX CYCLES
2.00 mm	6 & 7 mm	10 - 60	Black LCP	BeCu (S2M) Phosphor Bronze (T2M)	Au or Sn over 50 μ" (1.27 μm) Ni	-55 °C to +125 °C	3.8 A (T2M) 2.6 A (S2M (2 pins powered)	100 with 10 μ" (0.25 μm) Au

(2.00 mm) .0787" PITCH • HIGH-RELIABILITY CABLE INTERCONNECTS

SERIES	1	NO. OF POSITIONS	LEAD STYLE	PLATING OPTION	D	OPTIONS	PACKAGING
S2M Socket		05, 07, 10, 15, 20, 25, 30 (Per Row)	-01 = Through-hole -02 = Surface Mount	-F = Gold flash on contact, Matte Tin on tail -L = 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail		-K = (5.50 mm) .217" DIA Polyimide film Pick & Place Pad (-02 only) -LC = Locking Clip (Manual placement required) (-02 only) -DS = Screw Down (N/A with -LC) (mates with -T2M-DS)	Leave blank for tube packaging -TR = Tape & Reel (-02 only) -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (-02 only)

S2M
Board Mates:
T2M
Cable Mates:
T2SD






View complete specifications at: samtec.com?S2M


SERIES	1	NO. OF POSITIONS	01	PLATING OPTION	D	TAIL OPTION	OTHER OPTIONS	PACKAGING
T2M Header		05, 07, 10, 15, 20, 25, 30 (Per Row)		-L = 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail		-TH = Through-hole -RA = Right-angle -SM = Surface Mount	-WT = Weld Tab (S2SD & S2SDT, -SR/-DR required mate) -DS = Screw Down (N/A with -RA) (mates with -S2M-DS, S2SD/S2SDT -SS/-DS option) -K = (7.50 mm) .295" DIA Polyimide film Pick & Place Pad (-SM only)	Leave blank for tube packaging -TR = Tape & Reel (-SM only) -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (-SM only)

T2M
Board Mates:
S2M
Cable Mates:
S2SD, S2SDT





MATED HEIGHT



Note: Some lengths, styles and options are non-standard, non-returnable.

View complete specifications at: samtec.com?T2M

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[S2M-115-01-L-D](#) [S2M-107-01-L-D](#) [S2M-125-01-L-D](#) [S2M-110-01-L-D](#) [S2M-105-01-L-D](#) [S2M-120-01-L-D](#) [S2M-125-02-F-D-DS](#) [S2M-120-02-L-D-LC-K-TR](#) [S2M-130-01-F-D](#) [S2M-130-01-L-D](#) [S2M-130-01-S-D](#) [S2M-130-02-F-D-LC](#) [S2M-105-02-F-D-LC](#) [S2M-110-01-F-D](#) [S2M-115-01-S-D](#) [S2M-115-02-F-D-LC](#) [S2M-120-02-L-D-LC](#) [S2M-105-01-F-D](#) [S2M-107-01-S-D](#) [S2M-107-02-F-D](#) [S2M-110-02-F-D-LC-K-TR](#) [S2M-110-02-L-D-K-TR](#) [S2M-110-02-L-D](#) [S2M-110-02-L-D-K](#) [S2M-115-02-S-D-LC](#) [S2M-120-01-F-D](#) [S2M-120-01-S-D](#) [S2M-110-02-L-D-LC](#) [S2M-115-01-F-D](#) [S2M-115-02-L-D-LC-K-TR](#) [S2M-120-02-L-D-K-TR](#) [S2M-125-02-L-D](#) [S2M-125-02-L-D-K-TR](#) [S2M-130-02-L-D](#) [S2M-107-02-F-D-K-TR](#) [S2M-105-01-S-D](#) [S2M-105-02-F-D-K](#) [S2M-110-02-S-D-LC](#) [S2M-105-02-L-D-LC](#) [S2M-107-02-L-D](#) [S2M-110-02-F-D](#) [S2M-115-02-L-D-LC](#) [S2M-115-02-S-D](#) [S2M-120-02-F-D-LC](#) [S2M-125-02-L-D-K](#) [S2M-125-02-L-D-LC](#) [S2M-130-02-S-D](#) [S2M-110-01-S-D](#) [S2M-115-02-L-D](#) [S2M-120-02-S-D](#) [S2M-125-01-S-D](#) [S2M-110-02-F-D-LC](#) [S2M-110-02-S-D-K-TR](#) [S2M-115-02-L-D-K-TR](#) [S2M-130-02-L-D-LC-K](#) [S2M-105-02-F-D-TR](#) [S2M-105-02-L-D](#) [S2M-105-02-L-D-K](#) [S2M-107-02-S-D](#) [S2M-125-01-F-D](#) [S2M-105-02-F-D](#) [S2M-105-02-F-D-K-TR](#) [S2M-105-02-L-D-K-TR](#) [S2M-105-02-S-D](#) [S2M-107-01-F-D](#) [S2M-107-02-F-D-LC](#) [S2M-107-02-L-D-K-TR](#) [S2M-110-02-F-D-K](#) [S2M-105-02-S-D-LC](#) [S2M-107-02-L-D-LC](#) [S2M-110-02-F-D-K-TR](#) [S2M-110-02-S-D](#) [S2M-120-02-L-D-K](#) [S2M-130-02-L-D-LC](#) [S2M-120-02-L-D](#) [S2M-125-02-S-D](#) [S2M-106-02-S-D-DS](#) [S2M-120-01-F-D-DS](#) [S2M-120-01-L-D-DS](#) [S2M-105-02-L-D-LC-TR](#) [S2M-107-02-S-D-DS](#) [S2M-107-01-L-D-DS](#) [S2M-108-01-F-D](#) [S2M-110-02-L-D-TR](#) [S2M-120-02-S-D-LC](#) [S2M-125-01-L-D-DS](#) [S2M-105-02-S-D-LC-K-TR](#) [S2M-105-02-S-D-LC-TR](#) [S2M-106-02-F-D](#) [S2M-116-01-L-D](#) [S2M-104-02-L-D-K-TR](#) [S2M-105-01-L-D-DS](#) [S2M-110-01-L-D-DS](#) [S2M-110-02-L-D-DS](#) [S2M-110-02-L-D-LC-TR](#) [S2M-125-02-L-D-DS](#) [S2M-130-02-L-D-DS](#) [S2M-115-02-L-D-LC-TR](#) [S2M-105-02-S-D-K-TR](#) [S2M-115-01-L-D-DS](#)