






DO NOT
SCALE FROM
THIS PRINT



- USB-B-S-X-X-TH-X-XX
- TYPE
-B
 - CONFIGURATION
-S: SINGLE
 - PLATING SPECIFICATION
-F: 3μ" SELECTIVE GOLD IN MATTE AREA, MATTE TIN ON TAIL.
-S: 30μ" SELECTIVE GOLD IN MATTE AREA, MATTE TIN ON TAIL.
 - OPTIONS
-TR: TAPE & REEL (LEAVE BLANK FOR TRAY PACKAGING)
E&I OPTION
-R: RoHS COMPLIANT (SEE NOTE 2)
 - TERMINATION
-TH: THRU HOLE
 - COLOR
-B: BLACK
-W: WHITE



RECOMMENDED PCB LAYOUT

- NOTES:
- Ⓢ REPRESENTS A CRITICAL DIMENSION.
 - ALL PARTS ARE RoHS COMPLIANT WITH OR WITHOUT -R.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. TOLERANCES ARE: DECIMALS ANGLES X.X: ±0.3 [.01] X.XX: ±0.20 [.008] X.XXX: ±0.051 [.0020]		PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.	
MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 2:1 INSULATOR: PBT, UL94-V0 CONTACT: PHOSPHOR BRONZE SHELL: STEEL; NICKEL PLATED		DESCRIPTION: USB TYPE B RIGHT ANGLE THRU HOLE DWG. NO. USB-B-S-X-X-TH-X-XX BY: B.HARPENAU 2/06/06 SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[USB-B-S-F-W-TH-R-TR](#)