

TCS08-08-D-02.00-01-N-R

(2.00 mm) .0787"

TCS08 SERIES

# TIGER EYE™ IDC SOCKET CABLE

## Mates with:

TMM, TMMH, STMM,  
MMT, TW, MTMM, EHT,  
ETMM (-SR), ZSTMM

## SPECIFICATIONS

For complete specifications  
see [www.samtec.com/TCS08](http://www.samtec.com/TCS08)

### Insulator Material:

Black Glass Filled Polyester

### Contact:

BeCu

### Plating:

Au or Sn over 50 μ" (1.27 μm) Ni

### Wire:

28 AWG 7/36 Stranded,

Tinned, Copper with

Gray PVC Insulator

### Current Rating (TCS08/STMM):

2.8 A per pin

(2 pins powered)

### Operating Temp Range:

-40 °C to +105 °C

### Lead Size Accepted:

(0.48 mm) .019" to

(0.53 mm) .021"

### Insertion Depth:

(2.87 mm) .113" to

(3.17 mm) .125"

### RoHS Compliant:

Yes

## RECOGNITIONS

For complete scope of  
recognitions see  
[www.samtec.com/quality](http://www.samtec.com/quality)



## ALSO AVAILABLE (MOQ Required)





- Other sizes
- Other platings

## POLARIZING KEY



Specify PK-01-07 for polarizing key  
(Available in wheels of six each).

Also polarizes SMM  
Series socket strips.



**Note:**  
TCS08 Series assemblies are  
non-standard, non-returnable.




Specify "XX" as position  
number. Same position  
will be polarized on  
both ends.




Breakout starts with Number 1  
lead indicated by brown wire or  
red stripe. Shown on top side.







## EJECTOR HEADERS & LOCKING CLIPS



See TMM Series.



See EHT Series.



Due to technical progress, all designs, specifications and components are subject to change without notice.

[WWW.SAMTEC.COM](http://WWW.SAMTEC.COM)

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[TCSD-17-D-07.88-01-P01-R](#)