


QUAD ROW SMT TERMINAL & SOCKET

(1.27 mm) .050" PITCH • TOLC/SOLC SERIES



TOLC
Mates:
SOLC

SOLC
Mates:
TOLC

SPECIFICATIONS

Insulator Material:
Black Liquid Crystal Polymer
Contact Material:
Phosphor Bronze
Plating:
Au over 50 μ " (1.27 μ m) Ni
Current Rating:
2.4 A per pin
(6 adjacent pins powered)
Operating Temp Range:
-55 °C to +125 °C
Insertion Depth (SOLC):
(1.68 mm) .066" to
(3.61 mm) .142" with
(0.38 mm) .015" wipe
Max Cycles (SOLC):
100+

PROCESSING

Lead-Free Solderable:
Yes
SMT Lead Coplanarity:
(0.10 mm) .004" max (05-35)
(0.15 mm) .006" max (40-50)*
*(.004" stencil solution
may be available; contact
ipg@samtec.com)

TOLC	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	Q	OTHER OPTION
------	---	------------------	------------	----------------	---	--------------

05, 10, 15, 20, 25,
30, 35, 40, 45, 50
(Standard Sizes)

Specify
LEAD
STYLE
from
chart

-F
= Gold flash
on contact,
Gold flash
on tail

-L
= 10 μ "
(0.25 μ m)
Gold on
contact,
Gold flash
on tail


-A
= Alignment Pin
(N/A with -LC)

-LC
= Locking Clip
(N/A with -A)
(Manual
placement required)





-K
= (9.00 mm) .354" DIA
Polyimide film
Pick & Place Pad

-TR
= Tape & Reel

-FR
= Full Reel Tape & Reel
(must order max.
quantity per reel;
contact Samtec for
quantity breaks)



LEAD STYLE	A	MATED HEIGHT
-02	(5.59) .220	(6.35) .250
-12	(7.24) .285	(8.00) .315
-22	(9.25) .364	(10.00) .394
-32	(11.23) .442	(12.00) .472



-A OPTION

-LC OPTION

SOLC	1	NO. PINS PER ROW	02	PLATING OPTION	Q	OTHER OPTION
------	---	------------------	----	----------------	---	--------------

05, 10, 15, 20, 25,
30, 35, 40, 45, 50
(Standard Sizes)

-F
= Gold flash
on contact,
Gold flash
on tail

-L
= 10 μ " (0.25 μ m)
Gold on contact,
Gold flash
on tail

-A
= Alignment Pin
(N/A with -LC)





-LC
= Locking Clip
(N/A with -A)
(Manual
placement required)

-K
= (7.00 mm) .276" DIA
Polyimide film
Pick & Place Pad

-P
= Pick & Place Pad

-TR
= Tape & Reel

-FR
= Full Reel Tape & Reel
(must order max.
quantity per reel;
contact Samtec for
quantity breaks)



-A OPTION

-LC OPTION

-P OPTION

ALSO AVAILABLE

MOQ Required

Other sizes
Other platings

Note:
Some lengths, styles and
options are non-standard,
non-returnable.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[TOLC-120-22-L-Q-A](#) [TOLC-115-02-S-Q-A-K-TR](#) [TOLC-110-02-L-Q-A](#) [TOLC-125-02-L-Q-A](#) [TOLC-115-02-S-Q-A](#)
[TOLC-130-02-L-Q-A](#) [TOLC-105-02-L-Q-A](#) [TOLC-120-02-S-Q-A-K-TR](#) [TOLC-125-02-S-Q-A](#) [TOLC-130-02-S-Q-LC](#)
[TOLC-135-02-L-Q-LC](#) [TOLC-150-32-S-Q-A](#) [TOLC-140-02-L-Q-LC](#) [TOLC-120-02-L-Q-A](#) [TOLC-125-12-L-Q-A](#) [TOLC-](#)
[130-12-S-Q-LC](#) [TOLC-130-32-F-Q-K](#) [TOLC-135-22-L-Q-LC](#) [TOLC-135-22-S-Q-K](#) [TOLC-145-22-F-Q-A-K-TR](#) [TOLC-](#)
[150-02-F-Q-A-K](#) [TOLC-150-22-S-Q-A-K](#) [TOLC-105-02-L-Q-LC](#) [TOLC-110-02-S-Q-K](#) [TOLC-110-02-S-Q-K-TR](#) [TOLC-](#)
[115-02-F-Q-LC-K](#) [TOLC-115-02-L-Q-A](#) [TOLC-115-32-L-Q-LC](#) [TOLC-120-22-L-Q](#) [TOLC-120-32-F-Q-A-TR](#) [TOLC-125-](#)
[12-S-Q-A-PL-TR](#) [TOLC-130-12-L-Q-A](#) [TOLC-130-22-F-Q](#) [TOLC-135-12-F-Q-A-K](#) [TOLC-135-22-F-Q-A-K](#) [TOLC-140-](#)
[32-F-Q-A-K](#) [TOLC-135-02-L-Q](#) [TOLC-135-22-S-Q-K-TR](#) [TOLC-135-32-S-Q-A-K](#) [TOLC-140-02-S-Q-A-PL-TR](#) [TOLC-](#)
[145-02-S-Q-K](#) [TOLC-145-12-L-Q-A](#) [TOLC-150-02-S-Q-K](#) [TOLC-150-02-S-Q-PL](#) [TOLC-105-02-L-Q](#) [TOLC-110-02-S-](#)
[Q-TR](#) [TOLC-115-02-L-Q-A-K](#) [TOLC-115-32-L-Q-TR](#) [TOLC-120-22-S-Q-A](#) [TOLC-120-22-S-Q-LC-K-TR](#) [TOLC-130-22-](#)
[S-Q-A-K-TR](#) [TOLC-140-22-S-Q-LC-K-TR](#) [TOLC-145-22-S-Q-LC-K](#) [TOLC-135-02-F-Q-K](#) [TOLC-130-32-S-Q-A-K](#)
[TOLC-135-02-L-Q-K](#) [TOLC-135-02-S-Q-A-K](#) [TOLC-135-22-F-Q-A-K-TR](#) [TOLC-140-22-S-Q-A-K](#) [TOLC-150-12-S-Q-A-](#)
[K-TR](#) [TOLC-145-02-S-Q-LC](#) [TOLC-145-12-S-Q-A](#) [TOLC-150-02-S-Q-PL-TR](#) [TOLC-105-02-F-Q-LC](#) [TOLC-105-02-S-](#)
[Q-K](#) [TOLC-110-02-S-Q-LC](#) [TOLC-115-02-L-Q-A-K-TR](#) [TOLC-115-32-L-Q-A](#) [TOLC-115-32-S-Q-A-K-TR](#) [TOLC-115-](#)
[32-S-Q-A-TR](#) [TOLC-125-12-L-Q-A-K](#) [TOLC-125-12-L-Q-LC-K-TR](#) [TOLC-125-22-F-Q](#) [TOLC-130-12-F-Q-A](#) [TOLC-](#)
[135-02-S-Q-LC-K](#) [TOLC-135-12-F-Q-A-TR](#) [TOLC-140-22-S-Q-LC-K](#) [TOLC-140-32-S-Q-A-K-TR](#) [TOLC-145-22-S-Q-A-](#)
[K-TR](#) [TOLC-145-22-S-Q-LC-K-TR](#) [TOLC-145-32-F-Q-A](#) [TOLC-150-22-S-Q-TR](#) [TOLC-150-32-S-Q-A-K](#) [TOLC-110-12-](#)
[S-Q-LC-PL](#) [TOLC-110-22-S-Q-A-K](#) [TOLC-110-02-S-Q-A-K-TR](#) [TOLC-115-02-S-Q-A-PL-TR](#) [TOLC-120-02-S-Q-LC-K-](#)
[TR](#) [TOLC-105-32-S-Q-K-TR](#) [TOLC-110-02-L-Q-K-TR](#) [TOLC-115-02-F-Q-A-K-TR](#) [TOLC-115-32-S-Q-A-K](#) [TOLC-120-](#)
[02-F-Q-LC-K](#) [TOLC-120-02-F-Q-LC-TR](#) [TOLC-110-22-S-Q-A-TR](#) [TOLC-110-32-F-Q](#) [TOLC-115-12-S-Q-A-K-TR](#)
[TOLC-120-02-L-Q-A-K](#) [TOLC-120-02-S-Q-K](#) [TOLC-125-32-F-Q-K](#)