



TSSH-120-01-L-DH

TSSH SERIES

SHROUDED .025" SQ POST HEADERS

Important Note:
This Series will only mate
with SSW, SSQ & SSM Series

Yes

IPG@samtec.com)

RV
FILE NO. F11594

SSM TSSH

HORIZONTAL

- Other platings

Note:
Some lengths, styles and options are non-standard, non-returnable.

TSSH	1	NO. PINS PER ROW	01	PLATING OPTION	ROW OPTION	OTHER OPTION
05, 10, 15, 20, 25, 30, 34 (-D-RA, -DH) 05, 10, 15, 20, 25, 30, 35, 36 (-D, -DV)				-L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail -T = Matte Tin		-A = Alignment Pin (N/A with -LC)
-D-RA = Double Row Right-angle Pin Through-hole				-DH = Double Row Horizontal Pin Surface Mount		-LC = Locking Clip (-DV only) (N/A with -A) (Manual placement required)
-D = Double Row Vertical Pin Through-hole				-DV = Double Row Vertical Pin Surface Mount		-P = Plastic Pick & Place Pad (-DH only) 5 pos. min
						-TR = Tape & Reel 5 to 25 positions (-DH & -DV only)
						-FR = Full Reel Tape & Reel (must order max. quantity per reel; Contact Samtec for quantity breaks) 5 to 25 positions (-DH & -DV only)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[TSSH-110-01-L-D-RA](#)