


NOTES:

1. FOR USE WITH COMMSCOPE 77538 & BELDEN 1855A & 1865A CABLES.
2. FOR CABLING INSTRUCTIONS SEE 3-661-1.
3. FOR CRIMPING USE DIE KTH-2025.
4. CENTER CONTACT, 1-6690-7M9Y, AND K-GRIP SLEEVE 1-33983-1M06 SUPPLIED UNASSEMBLED.
5. INTERFACE PER MIL-STD-348, FIG. 301-1 (AS APPLICABLE).
6. MATERIAL SPECIFICATIONS:
INSULATOR: PTFE PER ASTM D4894.
GASKET: SILICONE RUBBER PER ZZ-R765.
SPRING WASHER AND OUTER CONTACT: BERYLLIUM COPPER PER ASTM B196.
ALL OTHER METAL PARTS: BRASS PER ASTM B16.
7. FINISH SPECIFICATIONS:
CENTER CONTACT: GOLD PER MIL-G-45204
SPRING WASHER: SILVER PER QQ-S-365
ALL OTHER METAL PARTS: NICKEL PER QQ-N-290

8. ELECTRICAL SPECIFICATIONS:
IMPEDANCE: 75 OHMS
WORKING VOLTAGE: 500 VOLTS RMS
FREQUENCY RANGE: DC - 12 GHz
RETURN LOSS: -30dB MAX TO 3.0 GHz
-20dB MAX TO 6.0 GHz
9. COMPLIANT TO 3G/6G/12G SDI SMPTE REQUIREMENTS.
10. MARK PACKAGE: KINGS 2065-11-9.

REV	DESCRIPTION	BY DATE	APPD
K	ER066126	JL 12/20/16	DCAM



CATALOG P/N: 2065-11-9

PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM] TOLERANCES: DECIMAL: .XX [XX] ± .01 [0.3] XXX [XXX] ± .005 [0.13] XXXX [XXXX] ± .000X ANGLES: ± 2° SCALE: 4:1				 by WINCHESTER Winchester Electronics Corporation 159 Park Road Ext Suite 104 Middlebury, Connecticut 06762					
CUSTOMER SALES DRAWING				 THIRD ANGLE		75 OHM BNC PLUG FOR BELDEN 1855A OR EQUIVALENT CABLE (ROHS)			
DRAWN 04/09/2015		DATE 04/09/2015		APPROVED MAR		DATE 07/28/2015			
APPROVED YA		DATE 04/09/2015		APPROVED XXX		DATE XX/XX/XX		A SD2065-11-9	
				SHT 1		OF 1		REV K	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Winchester Interconnect:](#)

[2065-11-9](#)