





	1	2	3	4	5	6	7	8	9
	REV.	REMARK	DATE	SIGN.					
F	<p><b>MATERIAL:</b>  CONTACT PIN: PHOSPHOR BRONZE SELECTIVE 10u" GOLD OVER NICKEL PLATED.  GROUND PIN: COPPER WIRE, TIN PLATED  METAL BODY: ZINC DIE CASTING, NICKEL PLATED  MAIN BODY: VALOX, UL94V-0  CENTER PLASTIC: POLYPROYLENE, UL94V-0  SPRING CLIP: PHOSPHOR BRONZE, TIN PLATED</p>								
E	<p><b>ELECTRICAL:</b>  OPERATING VOLTAGE: 500 VOLTS RMS  CONTACT RESISTANCE: 3.0 MILLIOHMS MAX. (GOLD)  FREQUENCY RANGE: 0~1 GHZ  DIELECTRIC WITHSTANDING VOLTAGE: 1500 VOLTS (VAC)  INSULATION RESISTANCE: 5000 MEGAOHMS MIN.  IMPEDANCE NOM.: 50 OHM  TEMPERATURE RANGE: -55°C TO +105°C</p>								
D	<p><b>MECHANICAL:</b>  DURABILITY: 500 CYCLES</p>								
C	   								
B	<p>(DIMENSIONING) PCB HOLE CONFIGURATION</p> <p>PANEL CUTOUT</p>								
A	Bomar Interconnect		DESC.	DUAL BNC RIGHT ANGLE 50 OHM		APPROVED	CHECKED	DESIGNED	TOLERANCE
			P/N	364A2595		BB	SO	BB	SCALE
			CUSTOMER P/N						1 = 1
									UNIT mm
									DATE 09/03/03
									DWG NO: UDBN\R01A13B

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Winchester Interconnect:](#)

[364A2595](#)