


DASH NO.	M CODE	MADE FROM
----------	--------	-----------

SD

PART NO. 1764-1

REVISIONS	
ISSUE	CHANGES
4	CN 37385 C REDRAWN JW 11/10/97
5	CN 37511 C JW 12/05/97
6	CN 38551 C TML 05/06/02
7	CN 38727 E BDH 11/27/02
8	CN 38925 E JLA 09/11/03
K	ER12813 DRK 12/10/08



NOTES:

- MATERIALS:  
INSULATOR: HIGH DENSITY POLYETHYLENE, ASTM-D4976, NATURAL.  
O-RINGS: SILICONE RUBBER, A-A-59588.  
LOCKWASHER: PHOSPHOR BRONZE.  
ALL OTHER PARTS: BRASS, ASTM-B16
- FINISHES:  
CENTER CONTACT: GOLD PLATE PER ASTM-B488.  
ALL OTHER METAL PARTS: KINGS TARNISH RESISTANT FINISH (TR-5)
- ELECTRICAL CHARACTERISTICS:  
NOMINAL IMPEDANCE: NON-CONSTANT  
VOLTAGE RATING: 20 KVDC  
INSULATION RESISTANCE: 10<sup>6</sup> MEGOHMS.
- LEAKAGE MAY NOT EXCEED 10x-7 CC/SEC. OF TRACER GAS AT ATMOSPHERIC PRESSURE.


UNLESS OTHERWISE SPECIFIED

- ALL DIMENSIONS IN INCHES [MILLIMETERS].
- TOLERANCES:  

.XXX ±.004	.XX ±.010
[.XXX ±.10]	[.XX ±.25]

 FRACTIONS: X/Y ±.010 [.25]      ANGLES: ± 1°

○ CRITICAL DIMENSIONS



CUSTOMER SALES DRAWING

SCALE 3:1

APPROX SURFACE AREA

USED ON

REF:

20 KV HV, RECEPTACLE BULKHEAD MOUNT

DRAWN	IDE	DATE	12/18/72
DESIGN	MG	DATE	12/20/72
APPR.	FDH	DATE	11/17/97

**KINGS**  
by WINCHESTER ELECTRONICS

Winchester Electronics  
62 Barnes Industrial  
Road North  
Wallingford, CT 06492

B  
SIZE

SD1764-1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Winchester Interconnect:](#)

[1764-1](#)