


REVISIONS	
ISSUE	CHANGES

SCALE: N.T.S.

S-D

USED ON:

REF:



NOTES:

1. FOR USE WITH BELDEN 8233 CABLE,

HEX SIZES (ACROSS FLATS)				DIE WIDTH		DIE WIDTH	
A	B	C	D	F	G	H	I
.074	—	—	.384	—	.400	.093	—

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS  $\pm .010$
2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX.
3. PLACE DECIMALS  $\pm .004$
3. NO FILLETS PERMITTED.
4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
5. ALL DIMENSIONS PRIOR TO PLATING.
6. ALL PLATING IN ACCORDANCE WITH KER 10004.
- T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES.

S-D

**SKINGS**  
ELECTRONICS CO. INC.  
TUCUMCUM, NEW YORK 10901

KTH-2040

CRIMP DIE

DRAWN: CHC	DATE: 22 JUL 87
APPR:	DATE:

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Winchester Interconnect:](#)

[KTH-2040](#)